


MM	IN
.010	.0004
.020	.0008
.030	.0012
.040	.0016
.050	.0020
.060	.0024
.070	.0028
.080	.0032
.090	.0036
.100	.0040
.110	.0044
.120	.0048
.130	.0052
.140	.0056
.150	.0060
.160	.0064
.170	.0068
.180	.0072
.190	.0076
.200	.0080

TSE 1034

356-5307



RATINGS AT 12V DC	
IGN CIRCUIT	10 AMPS
START	5

- NOTE
1. SHAFT O-RING SEALED TO CASE
 2. TERM INSUL GASKET SEALED
 3. ALL STEEL PARTS PLATED 11T W/DIC-50M, PL DIP OR CAL 11
 4. APPLICABLE SAE STANDARD OR RECOMMENDED PRACTICE SAE J259

METRIC

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRV D	SCALE	DATE DRAWN
									CF	11-20-78		1:1	1-10-66
				G	LEN # 60139	3/1/00	KF	FINISH					DATE BLUEPRINT
				F	CADU Y 125239	12/18/92	14						
				E	HOUSING	8-17-82	13	TOLERANCES					
				D	REDRAWN	11-8-78	R	FRACTIONAL ±					
								DECIMAL ±.25					
3 POS IGNITION & START SW													956-5307

CH-188 (4-78)