



#	DESCRIPTION	PART #
A	2-POSITION	882-839-2
B	3-POSITION	882-839-3
C	4-POSITION	882-839-4
D	5-POSITION	882-839-5

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [ ] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
◎	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			

METRIC COMPONENT

COPIES TO		MATERIAL SPEC		FINISH		SCALE		FULL	
LTR	DATE	REVISION	CHK	APD	DRW	OPL	DATE	DATE	DATE
A	02/17/11	501708ERA-RELEASED	OPL		02/17/11				
B	04/29/11	502164ECA-CHANGE THICKNESS FROM 2.38 TO 2.30	OPL						
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)		UP TO	OVER	UP TO	OVER	UP TO	OVER	UP TO	OVER
DIMENSION		0.5 - 3	3 - 6	6 - 30	30 - 120	120 - 400			
TOLERANCE		+0.05	+0.05	±0.1	±0.15	±0.2			
3RD ANGLE PROJECTION		TITLE							
BUS BAR FOR FLEX MEGA HOLDER		MATERIAL SPEC: COPPER C1100							
FINISH: TIN-PLATED		SCALE: FULL							
DATE: 02/17/11		SUPER DR							
DATE:		FINISH GOOD WT							
DATE:		GRAMS/PIECE							
REVISION		DRAWING NO. 882-839-0							
LITTELFUSE		DES. PLAINES, ILLINOIS 60016							