





THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	ECN #519740 INITIAL RELEASE	12/14/2000	DPS
	B	ECN #01100 PART CHANGE	02/14/2001	DPS
	C	ECN #09266 WAS 0.269 DIA	04/23/2009	DPS
	D	ECO #520819 UPDATE "CH" BRAND MARKING	05/23/2019	J. LI



- NOTES
1. ALL STEEL PARTS PLATED
  2. ALL DIMENSIONS ARE REFERENCE ONLY
  3. LOCK OUT BRACKET, LEVER, TWO MOUNTING SCREWS & INSTRUCTION SHEET SHIPPED IN PLASTIC BAG
  4. FOR USE WITH 7.00mm DIAMETER LOCK SHANK



INTERPRET DRAWING TO ANSI/ASME Y14.5-1994.				
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL			
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL			
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
DIMENSION; MM TOLERANCES UNLESS OTHERWISE SPECIFIED ONE PLACE DECIMAL ± 0.5                      THREE PLACES DECIMAL ± 0.100 TWO PLACES DECIMAL ± 0.20                      ANGULAR ± 2°				
-	NAME	DATE	 <b>Expertise Applied   Answers Delivered</b>	
DRAWN	J. LI	05/23/2019		
CHECKED	-	-		
	-	-		
			TITLE	
FORM NO: CVP-PE40-0004 REV A			<b>LOCK OUT KIT FOR MASTER DISCONNECT SW</b>	
THIRD ANGLE PROJECTION				
	SIZE B	DWG. NO. 24505-01	REV. D	
DO NOT SCALE DRAWING		SCALE 1:1		SHEET 2 OF 9