


MM	IN
0.25	.010
0.76	.030
1.01	.040
1.57	.062
1.52	.059
2.03	.080
2.28	.090
3.55	.140
4.82	.190
9.14	.360
9.39	.370
15.74	.620

46.98	1.850
46.99	1.850
3.04	.120
13.66	.538

COLE-HERSEE CO.
 NPM

956-3125



RATING AT 12V DC	
ACC	30 AMPS
IGN	10 AMPS
START	10 AMPS

METRIC

- NOTES:**
1. TERMINAL INSULATOR GASKET SEALED.
 2. SHUTTER TYPE SEAL ON LOCK FACE.
 - *3. START LOCK-OUT FEATURE; SWITCH MUST GO TO "OFF" POSITION BEFORE START CIRCUIT CAN BE RE-ENERGIZED.
 4. APPLICABLE SAE STANDARD OR RECOMMENDED PRACTICE SAE J259.
 - (D) 5 ALL STEEL PARTS PLATED

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRV D	SCALE	956-3122 LESS O-RINGS & GND CIRCUIT	DATE DRAWN
				D	NO ADDS/25039	12/20/90	SH	---	KPC	RF		1:1		10-26-76
				C	ECN 25189	8/13/76	JW	FINISH	COLE-HERSEE COMPANY BOSTON, MASS. 02127, U.S.A.					DATE BLUEPRINT
				B	16.02/22457	6-5-84	WJ	---						
				A	HOUSING	813-82	CR	TOLERANCES	3-POSITION IGN. & START SWITCH					956-3125
E	ECN 40137	3/1/00	MA	15 JUL	11 2 16	TY	FRACTIONAL ±							
								DECIMAL ±.25						