





THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.


REVISIONS					
REV.	DESCRIPTION	DATE	GCF / ECR	DESIGNED	APPROVED
A	Initial release	21-Jun-22		L.Dal Molin	M.Tinto




SCALE 1:2



Fixing holes



Electrical diagram



CHARACTERISTICS AND PRESCRIPTIONS

- Nominal tension: 24V
- Max continuos operating current: 300A
- Highest load 1000A for 5sec.
- M10 nut torque: 20 ± 2 Nm
- M6 screw torque: 8 ± 1 Nm

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.							
linear dimensions							
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000	
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3	
angle (for range of lengths)							
up to 10		>10 50	>50 120	>120 400			
±1°30'		±1°	±0°30'		±0°15'		
	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL						
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL						
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE						
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS						
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE						
NAME		DATE		 Littelfuse® Expertise Applied Answers Delivered			
DRAWN	L. Bisognin		21-Jun-22				
CHECKED	-		-				
	-		-				
FORM NO: CVP-PE40-0013 REV A		TITLE					
FIRST ANGLE PROJECTION		IGC-MARINE MANUAL 24V (ON/OFF)					
		SIZE: A3	DWG. NO. OL-08080800	OUTLINE REV. A			
DO NOT SCALE DRAWING		SCALE 1:1			SHEET 1 OF 1		