IXYS


HiPerFET™ Power MOSFETs

N-Channel Enhancement Mode
Avalanche Rated, High dv/dt, Low t_{rr}


	V_{DSS}	I_{D25}	$R_{DS(on)}$
IXFK 90 N 20	**200 V**	**90 A**	**23 mΩ**
IXFN 100 N 20	**200 V**	**100 A**	**23 mΩ**
IXFN 106 N 20	**200 V**	**106 A**	**20 mΩ**

$t_{rr} \leq$ 200 ns

TO-264 AA



miniBLOC, SOT-227 B (IXFN)
E153432



G = Gate D = Drain
S = Source TAB = Drain

Either Source terminal at miniBLOC can be used as Main or Kelvin Source

Symbol	Test Conditions	Maximum Ratings IXFK	IXFN	IXFN
		90N20	100N20	106N20
V_{DSS}	T_J = 25°C to 150°C	200	200	200 V
V_{DGR}	T_J = 25°C to 150°C; R_{GS} = 1 MΩ	200	200	200 V
V_{GS}	Continuous	±20	±20	20 V
V_{GSM}	Transient	±30	±30	20 V
I_{D25}	T_C = 25°C, Chip capability	90 ①	100	106 A
I_{D80}	T_C = 80°C, limited by external leads	76	-	A
I_{DM}	T_C = 25°C, pulse width limited by T_{JM}	360	400	424 A
I_{AR}	T_C = 25°C	50	50	A
E_{AR}	T_C = 25°C	30	30	30 mJ
dv/dt	$I_S \leq I_{DM}$, di/dt ≤ 100 A/μs, $V_{DD} \leq V_{DSS}$, $T_J \leq$ 150°C, R_G = 2 Ω	5	5	5 V/ns
P_D	T_C = 25°C	500	520	W
T_J		-55 ... +150		°C
T_{JM}			150	°C
T_{stg}		-55 ... +150		°C
T_L	1.6 mm (0.063 in) from case for 10 s	300	-	°C
V_{ISOL}	50/60 Hz, RMS t = 1 min	-	2500	V~
	$I_{ISOL} \leq$ 1 mA t = 1 s	-	3000	V~
M_d	Mounting torque	0.9/6	1.5/13	Nm/lb.in.
	Terminal connection torque	-	1.5/13	Nm/lb.in.
Weight		10	30	g

Symbol	Test Conditions		Characteristic Values (T_J = 25°C, unless otherwise specified) min.	typ.	max.	
V_{DSS}	V_{GS} = 0 V, I_D = 1 mA		200			V
$V_{GH(th)}$	$V_{DS} = V_{GS}$, I_D = 8 mA		2		4	V
I_{GSS}	V_{GS} = ±20 V_{DC}, V_{DS} = 0				±200	nA
I_{DSS}	V_{DS} = 0.8 • V_{DSS}	T_J = 25°C			400	μA
	V_{GS} = 0 V	T_J = 125°C			2	mA
$R_{DS(on)}$	V_{GS} = 10 V, I_D = 0.5 • I_{D25}					
	Pulse test, t ≤ 300 μs,	IXFK90N20			0.023	Ω
	duty cycle d ≤ 2 %	IXFN100N20			0.023	Ω
		IXFN106N20			0.020	Ω

Features
- International standard packages
- JEDEC TO-264 AA, epoxy meet UL 94 V-0, flammability classification
- miniBLOC with Aluminium nitride isolation
- Low $R_{DS(on)}$ HDMOS™ process
- Rugged polysilicon gate cell structure
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
- Fast intrinsic Rectifier

Applications
- DC-DC converters
- Synchronous rectification
- Battery chargers
- Switched-mode and resonant-mode power supplies
- DC choppers
- Temperature and lighting controls
- Low voltage relays

Advantages
- Easy to mount
- Space savings
- High power density

IXYS reserves the right to change limits, test conditions, and dimensions.

92804H (7/97)


© 2000 IXYS All rights reserved

Symbol	Test Conditions	Characteristic Values (T_J = 25°C, unless otherwise specified) min.	typ.	max.	
g_{fs}	V_{DS} = 10 V; I_D = 0.5 • I_{D25}, pulse test		60		S
C_{iss}	V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz		9000		pF
C_{oss}			1600		pF
C_{rss}			590		pF
$t_{d(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25} R_G = 1 Ω (External),		30		ns
t_r			80		ns
$t_{d(off)}$			75		ns
t_f			30		ns
$Q_{g(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25}		380		nC
Q_{gs}			70		nC
Q_{gd}			190		nC
R_{thJC}	TO-264 AA			0.25	K/W
R_{thCK}	TO-264 AA		0.15		K/W
R_{thJC}	miniBLOC, SOT-227 B			0.24	K/W
R_{thCK}	miniBLOC, SOT-227 B		0.05		K/W

Source-Drain Diode


Symbol	Test Conditions		Characteristic Values (T_J = 25°C, unless otherwise specified) min.	typ.	max.	
I_S	V_{GS} = 0 V	IXFK90N20			90	A
		IXFN100N20			100	A
		IXFN106N20			106	A
I_{SM}	Repetitive; pulse width limited by T_{JM}	IXFK90N20				
		IXFN100N20			360	A
		IXFN106N20			424	A
V_{SD}	I_F = 100 A, V_{GS} = 0 V, Pulse test, t ≤ 300 μs, duty cycle d ≤ 2 %				1.5	V
t_{rr}	I_F = 50 A, -di/dt = 100 A/μs, V_R = 100 V				200	ns
Q_{RM}				3		μC
I_{RM}				38		A

TO-264 AA Outline



Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.82	5.13	.190	.202
A1	2.54	2.89	.100	.114
A2	2.00	2.10	.079	.083
b	1.12	1.42	.044	.056
b1	2.39	2.69	.094	.106
b2	2.90	3.09	.114	.122
c	0.53	0.83	.021	.033
D	25.91	26.16	1.020	1.030
E	19.81	19.96	.780	.786
e	5.46 BSC		.215 BSC	
J	0.00	0.25	.000	.010
K	0.00	0.25	.000	.010
L	20.32	20.83	.800	.820
L1	2.29	2.59	.090	.102
P	3.17	3.66	.125	.144
Q	6.07	6.27	.239	.247
Q1	8.38	8.69	.330	.342
R	3.81	4.32	.150	.170
R1	1.78	2.29	.070	.090
S	6.04	6.30	.238	.248
T	1.57	1.83	.062	.072

miniBLOC, SOT-227 B



M4 screws (4x) supplied

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	31.50	31.88	1.240	1.255
B	7.80	8.20	0.307	0.323
C	4.09	4.29	0.161	0.169
D	4.09	4.29	0.161	0.169
E	4.09	4.29	0.161	0.169
F	14.91	15.11	0.587	0.595
G	30.12	30.30	1.186	1.193
H	38.00	38.23	1.496	1.505
J	11.68	12.22	0.460	0.481
K	8.92	9.60	0.351	0.378
L	0.76	0.84	0.030	0.033
M	12.60	12.85	0.496	0.506
N	25.15	25.42	0.990	1.001
O	1.98	2.13	0.078	0.084
P	4.95	5.97	0.195	0.235
Q	26.54	26.90	1.045	1.059
R	3.94	4.42	0.155	0.174
S	4.72	4.85	0.186	0.191
T	24.59	25.07	0.968	0.987
U	-0.05	0.1	-0.002	0.004

© 2000 IXYS All rights reserved

IXYS MOSFETS and IGBTs are covered by one or more of the following U.S. patents:
4,835,592 4,881,106 5,017,508 5,049,961 5,187,117 5,486,715
4,850,072 4,931,844 5,034,796 5,063,307 5,237,481 5,381,025

Fig. 1 Output Characteristics




Fig. 2 Input Admittance




Fig. 3 $R_{DS(on)}$ vs. Drain Current




Fig. 4 Temperature Dependence of Drain to Source Resistance




Fig. 5 Drain Current vs. Case Temperature





Fig. 6 Temperature Dependence of Breakdown and Threshold Voltage



© 2000 IXYS All rights reserved

Fig.7 Gate Charge Characteristic Curve




Fig.8 Capacitance Curves




Fig.9 Source Current vs. Source to Drain Voltage





Fig.10 Transient Thermal Impedance



© 2000 IXYS All rights reserved



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.