



1. FUSEHOLDER IS SPLASHED-WATERPROOF ACCORDING TO CLASS IP-64 AS DEFINED IN DIN 40050 BLATT 9 DATE FEB. 1975.



NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

BILL OF MATERIAL	
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES	
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.	
	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

METRIC
COMPONENT

COPIES TO			MATL SPEC										PA66 GF 30%												
1	9	18	FINISH																						
2	10	19																							
3	12	20																							
4	13	21	DRW	RLDJ		DATE		06/23/11		SCALE		1:1													
5	14	23	CHK			DATE				SUPER DR															
6	15	33																							
7	16	43	APPD			DATE				FINISH GOOD WT															
8	17	53											GRAMS/PIECE												
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-fH)																									
DIMENSION			0.5 - 3		UP TO OVER		3 - 6		UP TO OVER		6 - 30		UP TO OVER		30 - 120		UP TO OVER		120 - 400						
TOLERANCE			±0.05		±0.05		±0.05		±0.1		±0.15		±0.2		±0.2		±0.2		±0.2						
3RD ANGLE PROJECTION			TITLE										SPLASH-PROOF MAXI FUSEHOLDER												
																									
			REVISION			C			DRAWG. NO.			OL-01520003U													
LIPA CITY, BATANGAS, PHILIPPINES																									