







REVISIONS			
ZONE	REV.	DESCRIPTION	DATE
	A	PER EC#510230: INITIAL RELEASE	3/5/2014
			J. KAUFMAN

- NOTES:
- DRAWING SHOWN WITH FUSES INSTALLED, FUSE LOADING CONFIGURATION DEPENDANT
 - ALL STUDS TO BE STAINLESS STEEL WITH ROLLED THREADS
 - ALL BUS BARS TO BE TIN PLATED COPPER
 - WEIGHT: 0.86 LB
 - RECCOMENDED TORQUE VALUES:
 - MIDI FUSES - 3 N-m(27 IN-LB)
 - RECOMMENDED INPUT TERMINAL STUD NUT TORQUE - 20 N-m(15 FT-LB)
 - RECOMMENDED OUTPUT TERMINAL STUD NUT TORQUE - 20 N-m(15 FT-LB)
 - DRAWING SHOWN WITHOUT OPTIONAL LABEL, LABEL LOCATED ON OUTSIDE OF COVER
 - INCLUDED HARDWARE (TO BE INSTALLED AT LESS THAN 300 RPM);
 - M8x1.25 18-8 STAINLESS STEEL 4X
 - CONNECTOR HOUSING: FCI APEX 2.8MM FEMALE 4-WAY
FCI P/N: 54200409
 - MATERIAL:
HOUSING: GLASS FILLED NYLON 94V-0 COVER: PC 94V-0
 - MIN/MAX TEMPERATURE RATING: OPESRATIONAL: -40C~100C NON-OPERATIONAL: -55C~125C
 - MAX CURRENT INPUT: 350 AMPS



PART NUMBER	FUSE A PN	FUSE B PN	FUSE C PN	FUSE D PN	FUSE 1 PN	FUSE 2 PN	FUSE 3 PN
880073100	0287010.PXS	0287015.PXS	0287020.PXS	0287020.PXS	0498050.M	0498030.M	0498030.M

DIMENSIONS ARE IN MM.

DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI / ASME Y14.5M-1994

THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

DRAWN	J. LIU	DATE	3/5/2014
CHECKED	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

THIRD ANGLE PROJECTION

Expertise Applied | Answers Delivered

425 Sequoia Drive Bellingham, WA 98226

Phone (360)738-9010 Fax (360)738-0372

PDM XT Series

SIZE C DWG. NO. OL-880073000 REV. A

SCALE 1:2 SHEET 1 OF 1