
IXYS

HiPerFET™ Power MOSFETs Single Die MOSFET

IXFN 36N100

V_{DSS} = 1000V
I_{D25} = 36A
$R_{DS(on)}$ = 0.24Ω


N-Channel Enhancement Mode
Avalanche Rated, High dv/dt, Low t_{rr}



Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 150°C	1000	V
V_{DGR}	T_J = 25°C to 150°C; R_{GS} = 1 MΩ	1000	V
V_{GS}	Continuous	±20	V
V_{GSM}	Transient	±30	V
I_{D25}	T_C = 25°C, Chip capability	36	A
I_{DM}	T_C = 25°C, pulse width limited by T_{JM}	144	A
I_{AR}	T_C = 25°C	36	A
E_{AR}	T_C = 25°C	64	mJ
E_{AS}	T_C = 25°C	4	J
dv/dt	$I_S \le I_{DM}$, di/dt ≤ 100 A/μs, $V_{DD} \le V_{DSS}$, $T_J \le 150°C$, R_G = 2 Ω	5	V/ns
P_D	T_C = 25°C	700	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
V_{ISOL}	50/60 Hz, RMS t = 1 min $I_{ISOL} \le$ 1 mA t = 1 s	2500 3000	V~ V~
M_d	Mounting torque Terminal connection torque	1.5/13 1.5/13	Nm/lb.in. Nm/lb.in.
Weight		30	g

Symbol	Test Conditions	Characteristic Values (T_J = 25°C, unless otherwise specified) min.	typ.	max.	
V_{DSS}	V_{GS} = 0 V, I_D = 3 mA	1000			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 8 mA	3.0		5.5	V
I_{GSS}	V_{GS} = ±20 V_{DC}, V_{DS} = 0			±200	nA
I_{DSS}	$V_{DS} = V_{DSS}$, V_{GS} = 0 V; T_J = 25°C			100	μA
	$V_{DS} = V_{DSS}$, V_{GS} = 0 V; T_J = 125°C			2	mA
$R_{DS(on)}$	V_{GS} = 10 V, $I_D = 0.5 \bullet I_{D25}$ Pulse test, t ≤ 300 μs, duty cycle d ≤ 2 %			0.24	Ω

miniBLOC, SOT-227 B (IXFN)
E153432



G = Gate D = Drain
S = Source TAB = Drain

Either Source terminal at miniBLOC can be used as Main or Kelvin Source

Features
- International standard packages
- miniBLOC, with Aluminium nitride isolation
- Low $R_{DS\ (on)}$ HDMOS™ process
- Rugged polysilicon gate cell structure
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
- Fast intrinsic Rectifier


Applications
- DC-DC converters
- Battery chargers
- Switched-mode and resonant-mode power supplies
- DC choppers
- Temperature and lighting controls

Advantages
- Easy to mount
- Space savings
- High power density

© 2003 IXYS All rights reserved

Symbol	Test Conditions	Characteristic Values (T_J = 25°C, unless otherwise specified) min.	typ.	max.	
g_{fs}	V_{DS} = 15 V; I_D = 0.5 • I_{D25}, pulse test	18	40		S
C_{iss}	V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz		9200		pF
C_{oss}			1200		pF
C_{rss}			300		pF
$t_{d(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25} R_G = 1 Ω (External),		41		ns
t_r			55		ns
$t_{d(off)}$			110		ns
t_f			30		ns
$Q_{g(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25}		380		nC
Q_{gs}			65		nC
Q_{gd}			185		nC
R_{thJC}				0.18	K/W
R_{thCK}			0.05		K/W

miniBLOC, SOT-227 B



M4 screws (4x) supplied

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	31.50	31.88	1.240	1.255
B	7.80	8.20	0.307	0.323
C	4.09	4.29	0.161	0.169
D	4.09	4.29	0.161	0.169
E	4.09	4.29	0.161	0.169
F	14.91	15.11	0.587	0.595
G	30.12	30.30	1.186	1.193
H	38.00	38.23	1.496	1.505
J	11.68	12.22	0.460	0.481
K	8.92	9.60	0.351	0.378
L	0.76	0.84	0.030	0.033
M	12.60	12.85	0.496	0.506
N	25.15	25.42	0.990	1.001
O	1.98	2.13	0.078	0.084
P	4.95	5.97	0.195	0.235
Q	26.54	26.90	1.045	1.059
R	3.94	4.42	0.155	0.174
S	4.72	4.85	0.186	0.191
T	24.59	25.07	0.968	0.987
U	-0.05	0.1	-0.002	0.004

Source-Drain Diode

Symbol	Test Conditions	Characteristic Values (T_J = 25°C, unless otherwise specified) min.	typ.	max.	
I_S	V_{GS} = 0 V			36	A
I_{SM}	Repetitive; pulse width limited by T_{JM}			144	A
V_{SD}	I_F = I_S, V_{GS} = 0 V, Pulse test, t ≤ 300 µs, duty cycle d ≤ 2 %			1.3	V
t_{rr}	I_F = I_S, -di/dt = 100 A/µs, V_R = 100 V T_J = 25°C		180		ns
	T_J = 125°C		330		ns
Q_{RM}	T_J = 25°C		2		µC
I_{RM}			8		A

IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,881,106 5,017,508 5,049,961 5,187,117 5,486,715 6,306,728B1 6,259,123B1 6,306,728B1 4,850,072 4,931,844 5,034,796 5,063,307 5,237,481 5,381,025 6,404,065B1 6,162,665 6,534,343




Figure 1. Output Characteristics at 25°C




Figure 2. Output Characteristics at 125°C




Figure 3. $R_{DS(on)}$ normalized to 0.5 I_{D25} value vs. I_D




Figure 4. $R_{DS(on)}$ normalized to 0.5 I_{D25} value vs. T_J




Figure 5. Drain Current vs. Case Temperature




Figure 6. Admittance Curves

© 2003 IXYS All rights reserved




Figure 7. Gate Charge




Figure 8. Capacitance Curves




Figure 9. Forward Voltage Drop of the Intrinsic Diode




Figure 10. Transient Thermal Resistance

IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,881,106 5,017,508 5,049,961 5,187,117 5,486,715 6,306,728B1 6,259,123B1 6,306,728B1 4,850,072 4,931,844 5,034,796 5,063,307 5,237,481 5,381,025 6,404,065B1 6,162,665 6,534,343



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.