

	58328-32	SPDT	ON 1 & 2	OFF	ON 2 & 3	BLACK	1,2,3, 4 & 6					L	CLEAR	RED	12VDC	12VDC	3			
	58328-31	SPDT	ON 1 & 2	OFF	ON 2 & 3	BLACK	1,2,3, 4 & 6					L	CLEAR	GREEN	12VDC	12VDC	3			
	58328-30	SPDT	ON 1 & 2	OFF	ON 2 & 3	BLACK	1,2,3, 4 & 6					L	CLEAR	AMBER	12VDC	12VDC	3			
	58328-29	SPDT	ON 1 & 2	OFF	ON 2 & 3	BLACK	1,2,3, 4 & 6					L	AMBER	RED	12VDC	12VDC	3			
	58328-28	SPDT	ON 1 & 2	OFF	ON 2 & 3	BLACK	1,2,3, 4 & 6					L	AMBER	GREEN	12VDC	12VDC	3			
	58328-27	SPDT	ON 1 & 2	OFF	ON 2 & 3	BLACK	1,2,3, 4 & 6					L	AMBER	CLEAR	12VDC	12VDC	3			
	58328-26	SPDT	ON 1 & 2	OFF	ON 2 & 3	BLACK	1,2,3 & 4					L	RED	RED	12VDC	12VDC	4			
	58328-25	SPDT	ON 1 & 2	OFF	ON 2 & 3	BLACK	1,2,3 & 4					L	GREEN	GREEN	12VDC	12VDC	4			
	58328-24	SPDT	ON 1 & 2	OFF	ON 2 & 3	BLACK	1,2,3, 4 & 6					L	CLEAR	CLEAR	12VDC	12VDC	3			
	58328-23	SPDT	ON 1 & 2	OFF	ON 2 & 3	BLACK	1,2,3, 4 & 6					L	AMBER	AMBER	12VDC	12VDC	3			
	58328-22	SPDT	ON 1 & 2	NONE	ON 2 & 3	BLACK	1,2,3 & 4					M	GREEN	RED	12VDC	12VDC	4			
	58328-21	SPDT	ON 1 & 2	NONE	ON 2 & 3	BLACK	1,2,3 & 4					M	CLEAR	RED	12VDC	12VDC	4			
	58328-20	SPDT	ON 1 & 2	NONE	ON 2 & 3	BLACK	1,2,3 & 4					M	CLEAR	GREEN	12VDC	12VDC	4			
	58328-19	SPDT	ON 1 & 2	NONE	ON 2 & 3	BLACK	1,2,3 & 4					M	AMBER	RED	12VDC	12VDC	4			
	58328-18	SPDT	ON 1 & 2	NONE	ON 2 & 3	BLACK	1,2,3 & 4					M	AMBER	GREEN	12VDC	12VDC	4			
	58328-17	SPDT	ON 1 & 2	NONE	ON 2 & 3	BLACK	1,2,3 & 4					M	AMBER	CLEAR	12VDC	12VDC	4			
PT NO	TYPE OF SW	POS A	POS B	POS C	ROCKER COLOR	TERMINAL LOCATION	IMPRINT #1	IMPRINT #2	IMPRINT LOCATION	IMPRINT COLOR	LENS LOCATION	LENS 1	LENS 2	LENS 1	LENS 2	LAMP SCHEM	BUS BARS			
		ROCKER POSITION		LENS COLOR								LAMP VOLTAGE								
							<b>Tolerances</b> Unless otherwise specifically noted, the following are default tolerances: * 2-place Decimal Dimensions +/- .02" * 3-place Decimal Dimensions +/- .005" * Angular Dimensions +/- 1.0 Deg. * Metric: Refer to equivalent English Dimension Tolerance >>> NOTE: All tolerances are Non-Cumulative. <<<  <b>Dimensional Units</b> All dimensions are expressed in inches except those shown in brackets (xxx) are expressed in millimeters  "REF." or an Asterisk (*) = Non-Toleranced Reference Dimension, shown for clarification purposes only.  Used On or Ref.: Scale: <b>1:1</b>			<b>PROPRIETARY INFORMATION</b> This Engineering Drawing, and the information contained herein, is proprietary to Cole Hersee Company and may not be disclosed, re-produced, or in any other way transferred or communicated to any other party without the express written consent of an authorized representative of Cole Hersee Company.  <b>DESIGN CONTROL</b> It is the responsibility of the individual using / referencing this drawing to assure that the noted design revision level agrees with the revision level of the Controlled Document (Master Drawing). This is a NON-CONTROLLED DOCUMENT unless otherwise specifically noted.  DO NOT SCALE - Dimensional variation may occur during printing / reproduction.  Drawn By: <b>MJT</b> Date Drawn: <b>2/7/95</b>			<b>Key for Special Characteristics:</b>  Critical Characteristic, relating to Safety and/or Regulatory Compliance  Significant Characteristic relating to Process Control (SPC)  Control Dimension relating to Form - Fit - Function as defined by Cole Hersee Company and/or the Customer  (Note that the identification of any Characteristics as being "Special" does not alter the requirement that ALL specified dimensions & tolerances must be met.)  Responsible Engineer: <b>Pg. 3 of 6</b>			<b>Cole Hersee Co.</b> 20 Old Colony Ave., South Boston, MA, 02127 Phn: 617-268-2100 Web: www.colehersee.com  <b>Description:</b>  <b>ROCKER SWITCH</b>  <b>Drawing / Part No.:</b>  <b>58328-CHART</b>  <b>Current Rev.</b>  <b>SEE PG 1</b>				