








- NOTES:
1. MATERIALS:
BASE/COVER: BLACK FR30
BUS BAR: C1100 5% PLATED
STUD: STEEL ZN/Fe ALLOY PLATED
BOTTOM CAP: BLUE PA66
LATCH: YELLOW POM
 2. MAX. MAIN INPUT: 400A
 3. OPERATING TEMPERATURE RANGE: -40°C TO 85°C
 4. M8 MOUNTING TORQUE: 10±2 Nm
 5. MAX. WIRE SIZE: 105 sqmm OR AWG 4/0.



LTR	DATE	REVISION	CHK	APD
A	26/Jun/18	519497GCC-NEW RELEASE	FYUE	

7	873-716	COVER	1	EA
6	883-088	LATCH	2	EA
5	882-869-5	BUS BAR	5	EA
4	888-967	BASE	1	EA
3	908-067	M8 STUD	4	EA
2	908-068	M10 STUD	1	EA
1	883-094	BOTTOM CAP	2	EA
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
⊙	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
COPIES TO		MATEL SPEC		
1	9	18	SEE NOTE	
2	10	19	FINISH	
3	12	20	SEE NOTE	
4	13	21	DRW	FYUE
5	14	23	DATE	26/Jun/18
6	15	33	CHK	DATE
7	16	43	APPD	DATE
8	17	53	FINISH GOOD WT	
GRAMS/PIECE				
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-TH)				
DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120
TOLERANCE	±0.1	±0.1	±0.2	±0.3
3RD ANGLE PROJECTION	TITLE			
UNSEALED 4-WAY ZCASE FUSE BOX				
Littelfuse				
REVISION/DRWG. NO.			OUTLINE	
A			OFHZ0001Z	
DES PLAINES, ILLINOIS 60014				

METRIC
ASSEMBLY

LITTELFUSE
DES PLAINES, ILLINOIS 60014

REVISION/DRWG. NO.
A OFHZ0001Z

OUTLINE

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED