




REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO #5300217, NEW RELEASE, DSILVA	2/23/2023	S. CASTILLO




SECTION A-A

- NOTES:
- MATERIAL: COVER/HOUSING: POLYETHYLENE, BLACK
BUS BAR: COPPER
TETHER: TPE
SCREWS/WASHES/BOLTS: STAINLES STEEL
GASKET: SICLON RUBBER
 - FUSE ASSEMBLY TORQUE: 5-7Nm USING M5 BOLT & LOCK WASHER
10-12Nm USING M8 BOLT & LOCK WASHER
 - ALL FUSE MUST NO EXCEED 70% OF RATED CURRENT
 - MAX. MAIN INPUT: 240A
 - OPERATING TEMPERATURE RANGE: -40°C TO + 120°C
 - ADJUST CABLE GASKET AFTER FIX THE THE CABLE ON BOLT FOR HIGH SEALING PERFORMANCE
 - M8 MOUNTING TORQUE: 10-12 Nm

NO.	COMPONENT NO.	COMPONENT NAME	QTY	U										
DIMENSION: MM TOLERANCES UNLESS OTHERWISE SPECIFIED														
ONE PLACE DECIMAL ± 0.5 TWO PLACES DECIMAL ± 0.20					THREE PLACES DECIMAL ± 0.100 ANGULAR ± 2°									
DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.														
PER CHNPD20-008 PROCEDURE		FIT/ FUNCTION CRITICAL CHARACTERISTICS												
		SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL												
	CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE												
		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS												
	CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE												
<table><tr><td>NAME</td><td>DATE</td></tr><tr><td>D.SILVA</td><td>1/8/2023</td></tr><tr><td>S.CASTILLO</td><td>2/23/2023</td></tr><tr><td>-</td><td>-</td></tr><tr><td>-</td><td>-</td></tr></table>		NAME	DATE	D.SILVA	1/8/2023	S.CASTILLO	2/23/2023	-	-	-	-	Littelfuse Expertise Applied Answers Delivered		
NAME	DATE													
D.SILVA	1/8/2023													
S.CASTILLO	2/23/2023													
-	-													
-	-													
FORM NO. CVP-PE40-0005 REV B THIRD ANGLE PROJECTION		TITLE SEAL KIT, LTX PDM Acc												
		SIZE C	DWG. NO. OL-07981003ZXS	REV. A										
DO NOT SCALE DRAWING		SCALE 1:1		SHEET 1 OF 2										



THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.




DAE
AELF723
07981001ZXS
01/0001-13
Made in China

Max. Input Current: 240A
M8 (MEGA) Torque: 10-12Nm
M5 (MIDI) Torque: 5-7Nm

LASER TRACKING NO. AREA



8	-	SEAL KIT	1	EA
7	-	BREATH VENT	1	EA
6	-	BIG BASE	1	EA
5	-	BUS BAR	1	EA
4	-	COVER GASKET	1	EA
3	-	INSIDE LABEL	1	EA
2	873-680	TETHER	1	EA
1	-	COVER	1	EA
NO.	COMPONENT NO.	DESCRIPTION	QTY/M	U/M

DIMENSION: MM TOLERANCES UNLESS OTHERWISE SPECIFIED							
ONE PLACE DECIMAL ± 0.5		THREE PLACES DECIMAL ± 0.100					
TWO PLACES DECIMAL ± 0.20		ANGULAR ± 2°					
DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.							
PER CHNPD20-008 PROCEDURE		FIT/ FUNCTION CRITICAL CHARACTERISTICS					
	<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL					
	CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE					
		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS					
	CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE					
DRAWN	NAME	DATE	 Littelfuse® Expertise Applied Answers Delivered				
	D.SILVA	1/8/2023					
CHECKED	S.CASTILLO	2/23/2023					
-	-	-					
-	-	-	TITLE				
-	-	-					
FORM NO. CVP-PE40-0005 REV B			SEAL KIT, LTX PDM Acc				
THIRD ANGLE PROJECTION							
			SIZE	DWG. NO.	OL-07981003ZXS	REV. A	
DO NOT SCALE DRAWING			SCALE 1:1				
						SHEET 2 OF 2	