

THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.		
PART NUMBER	DESCRIPTION	NOTES
178.4265.0002	HOLDER FOR FLR (ATO) PCB 42V	-

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO #5300044. INITIAL RELEASED. DSILVA.	4/21/2022	L.ARGIL


- NOTES:
- MATERIAL:
 - HOLDER: THERMOPLASTIC
 - DFK3 CONTACTS: COPPER ALLOY

2	-	DFK3 TERMINALS	2	EA
1	-	HOLDER	1	EA
NO.	COMPONENT NO.	COMPONENT NAME	QTY	U
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)				
.5 to 3	>3 to 6	>6 to 30	>30 to 120	>120 to 400
±0.10	±0.10	±0.20	±0.30	±0.50
DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.				
PER CHNFPD20-008 PROCEDURE	●	FIT/ FUNCTION CRITICAL CHARACTERISTICS		
	<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL		
	CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE		
	(ST)	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
PER CHNFPD20-008 PROCEDURE	CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		
		NAME	DATE	
	DRAWN	DSILVA	4/13/2022	
	CHECKED	-	-	
FORM NO. CVP-PE40-0005 REV B THIRD ANGLE PROJECTION				
DO NOT SCALE DRAWING		SCALE 5:1	SHEET 1 OF 1	



Expertise Applied | Answers Delivered

TITLE PCB FUSEHOLDER 42V 4 PINS EACH



SIZE C DWG. NO. OUTLINE OL-178.4265.0000 REV. A