





THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO #5300036. INITIAL RELEASE. DSILVA.	3/8/2022	L.ARGIL



NOTES:


- MATERIAL:
 - BASE: NYLON66
 - BUSBAR: COPPER ALLOY
 - COVER: THERMOPLASTIC VULCANIZATE (TPV)
 - M5 STUDS: M5X0.8 STEEL ALLOY, ZINC PLATING
 - HEX NUTS: M5X.8 STAINLESS STEEL
 - WASHERS: SPLIT, M5 CARBON STEEL
- M5 STUD TORQUE: 10 NM MINIMUM
- MOUNTING TAB TORQUE: 10 NM MINIMUM USING M4 HARDWARE
- MAX FLASH: 0.2mm

2	-	MIDI FLEX HOLDER SA	2	EA
1	882-267-002	2 POSITION BUS BAR	1	EA
NO.	COMPONENT NO.	COMPONENT NAME	QTY	UM

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)														
.5 to 3	>3 to 6	>6 to 30	>30 to 120	>120 to 400										ANGLE
±0.10	±0.10	±0.20	±0.30	±0.50										NONE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES

PER CH-NPD20-0008 PROCEDURE	●	FIT/ FUNCTION CRITICAL CHARACTERISTICS
	<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL
	CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
	ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE	

NAME		DATE		 Littelfuse® Expertise Applied Answers Delivered	
DRAWN	DSILVA	2/2/2022			
CHECKED	-	-			
	-	-			
FORM NO: CVP-PE40-0003 REV B				TITLE FLEX-MIDI FUSE HOLDER 2 POSITION ASSY (NO FUSE)	
THIRD ANGLE PROJECTION					
		SIZE B	DWG. NO. OUTLINE	OL-04982001ZXFC	REV. A
DO NOT SCALE DRAWING			SCALE 1:1		SHEET 1 OF 1