




CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED











NOTES:
1. MATERIAL:
   BASE: UL94V-0 GLASS FILLED NYLON
   STUDS: M5
   NUTS: ZINC-PLATED NYLOCK NUT
2. TORQUE RATING: 5±1 Nm
3. FUSE RATING: 30-200A
4. WIRE SIZE: 14-4 AWG (2.5mm²-20mm²)
5. TEMPERATURE RATING: -40°C TO 125°C

PACKAGING NOTES:
1. PARTS ARE PACKED 50 PC PER BAG, 10 BAGS PER BOX.

METRIC
ASSEMBLY

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

BILL OF MATERIAL

MATL SPEC

FINISH

COPIES TO: 1 9 18 / 2 10 19 / 3 12 20 / 4 13 21 / 5 14 23 / 6 15 33 / 7 16 43 / 8 17 53

	DATE	SCALE
DRW OPL	05/16/11	1:1
CHK	DATE	SUPER DR
APPD	DATE	FINISH GOOD WT GRAMS/PIECE

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)

	UP TO 3	OVER 3 - UP TO 6	OVER 6 - UP TO 30	OVER 30 - UP TO 120	OVER 120 - UP TO 400
DIMENSION	±0.1	±0.1	±0.2	±0.3	±0.5
TOLERANCE	±0.1	±0.1	±0.2	±0.3	±0.5

3RD ANGLE PROJECTION

TITLE
BASE FOR MIDI INLINE HOLDER, W/M5 BOLTS

Littelfuse
DES PLAINES, ILLINOIS 60016

REVISION A
DRWG. NO. OL-498921-2
OUTLINE

LTR	DATE	REVISION	CHK	APD
A	05/16/11	502090ERA-RELEASE OPL		

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [ ] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

◎ DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE

ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS

CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE