

注释：我们正在更新系统，您可能会注意到遗失/过时的数据。在此过渡时期，请参考您的合规证书或在<https://www.ul.com/about/locations>上联系客服中心。


## Switches, Industrial Control Certified for Canada - Component

### COMPANY

#### LITTELFUSE INC

8755 W Higgins Rd, Suite 500  
Chicago, IL 60631 United States

E47258

Marking: Company name or trademark  ,  , model designation, and the Recognized Component

Mark for Canada 

Note: For additional marking information, refer to the [Guide Information Page](#).

*View model for additional information*

**Industrial control switches,** Model(s): [HE721B2430](#)

**Industrial Control Switches,** Model(s): [HE3321A](#), [HE3321A0400](#), [HE3321A0440](#), [HE3321A1200](#), [HE3321A2400](#), [HE3321A2440](#), [HE3321A6262](#), [HE3321A6376](#), [HE3321A6645](#), [HE3321A6788](#), [HE3321A6889](#), [HE3321C](#), [HE3321E](#), [HE3321C0400](#), [HE3321C0500](#), [HE3321C1200](#), [HE3321C2400](#), [HE3321C6675](#), [HE3321E1200](#), [HE3321E5940](#), [HE3321E5941](#), [HE3321E5942](#), [HE3351A](#), [HE3351A0500](#), [HE3351A1200](#), [HE3351A2400](#), [HE3351A6282](#), [HE3351A6706](#), [HE3351A6886](#), [HE3351A6887](#), [HE3361A0540](#), [HE3621A](#), [HE3621A0500](#), [HE3621A0510](#), [HE3621A0540](#), [HE3621A0550](#), [HE3621A1200](#), [HE3621A1210](#), [HE3621A1250](#), [HE3621A2400](#), [HE3621A2410](#), [HE3621A6012](#), [HE3621A6684](#), [HE3621A6685](#), [HE3621A6685](#), [HE3621A6786](#), [HE3621A6847](#), [HE3621A6849](#), [HE3621A6849](#), [HE3621A6854](#), [HE3621B0500](#), [HE3651A](#), [HE3671A](#), [HE3671A0500](#), [HE3671A0510](#), [HE3671A1200](#), [HE721A0500](#), [HE721A0510](#), [HE721A0520](#), [HE721A0530](#), [HE721A0540](#), [HE721A1200](#), [HE721A1201](#), [HE721A1210](#), [HE721A1220](#), [HE721A1230](#), [HE721A1240](#), [HE721A2400](#), [HE721A2405](#), [HE721A2406](#), [HE721A2410](#), [HE721A2415](#), [HE721A2430](#), [HE721A5025](#), [HE721A5166](#), [HE721A5265](#), [HE721A6022](#), [HE721A6202](#), [HE721A6732](#), [HE721B0500](#), [HE721B0510](#), [HE721B0530](#), [HE721B0540](#), [HE721B0550](#), [HE721B1200](#), [HE721B1210](#), [HE721B1220](#), [HE721B2410](#), [HE721B2430](#), [HE721B6134](#), [HE721B6139](#), [HE721B6201](#), [HE721C0500](#), [HE721C0510](#), [HE721C0520](#), [HE721C0530](#), [HE721C0540](#), [HE721C1200](#), [HE721C1210](#), [HE721C1230](#), [HE721C1250](#), [HE721C2400](#), [HE721C2410](#), [HE721C2430](#), [HE721C2440](#), [HE721C2450](#), [HE721C6657](#), [HE721C6729](#), [HE721C6791](#), [HE721C6868](#), [HE721E0510](#), [HE721E1200](#), [HE721E1210](#), [HE721E1230](#), [HE721E2400](#), [HE721E2410](#), [HE721E5313](#), [HE721R0500](#), [HE721R0510](#), [HE721R1210](#), [HE721R2410](#), [HE722A0500](#), [HE722A0510](#), [HE722A0530](#), [HE722A0600](#), [HE722A0610](#), [HE722A1200](#), [HE722A1210](#), [HE722A1250](#), [HE722A2400](#), [HE722A2410](#), [HE722A6425](#), [HE751A0500](#), [HE751A0510](#), [HE751A1200](#), [HE751A1210](#), [HE751A2400](#), [HE751A2410](#)

**Industrial Control Switches,** Model(s): [DCN](#) followed by H or L, followed by S, C, R, M, H, J, or D, followed by 400, followed by P or N, followed by A, B, C, D, E, F, G, or H, followed by 24 or 48.

**Industrial Control Switches,** Model(s): [DCN](#) followed by L, followed by R, followed by 100, followed by P, Q, N or M, followed by B, followed by 12, 24, 48 or XX (X is a number), followed by -XX (X is a number).

**Industrial Control Switches,** Model(s): [DCN](#) followed by H, followed by R, followed by 100, 50, followed by P, Q, N or M, followed by F, followed by 12, 24, 48 or XX (X is a number), followed by -XX (X is a number).

**Industrial Control Switches**, Model(s): DCN followed by H, followed by R, followed by 300, 250, 200, 150, followed by P, Q, N or M, followed by F, followed by A or XX (X is a number), followed by -XX (X is a number).

**Industrial Control Switches**, Model(s): DCN followed by L, followed by R, followed by 200, followed by P, Q, N or M, followed by B, followed by 12, 24, 48, 60 or XX (X is a number), followed by -XX (X is a number).

**Industrial Control Switches**, Model(s): DCN followed by H, followed by R, followed by 40, 30, 20, followed by P, Q, N or M, followed by F, followed by 12, 24, 48 or XX (X is a number), followed by -XX (X is a number).

**Industrial Control Switches**, Model(s): Types HE72 f/b 1 or 2, f/b A, B or C, f/b 05, 12 or 24, f/b letters and/or numbers

**Industrial controls switches**, Model(s): MITI-3VI

**Magnetic reed relays**, Model(s): HE321A0400, HE321A0440, HE321A0500, HE321A0540, HE321A1200, HE321A1240, HE321A2400, HE321A2440, HE321A5014, HE321B0400, HE321B0440, HE321B0500, HE321B0540, HE321B1200, HE321B1240, HE321B2400, HE321B2440, HE331A0500, HE331A0540, HE331A1200, HE331A1240, HE331A2400, HE331A2440, HE3321A0400(\*), HE3321A0440(\*), HE3321A0470(\*), HE3321A0500(\*), HE3321A0540(\*), HE3321A0570(\*), HE3321A1200(\*), HE3321A1240(\*), HE3321A1270(\*), HE3321A2400(\*), HE3321A2440(\*), HE3321A2470(\*), HE3321B0400(\*), HE3321B0440(\*), HE3321B0470(\*), HE3321B0500(\*), HE3321B0540(\*), HE3321B0570(\*), HE3321B1200(\*), HE3321B1240(\*), HE3321B1270(\*), HE3321B2400(\*), HE3321B2440(\*), HE3321B2470(\*), HE3321C0400(\*), HE3321C0440(\*), HE3321C0470(\*), HE3321C0500(\*), HE3321C0540(\*), HE3321C0570(\*), HE3321C1200(\*), HE3321C1240(\*), HE3321C1270(\*), HE3321C2400(\*), HE3321C2440(\*), HE3321C2470(\*), HE3321E0400(\*), HE3321E0440(\*), HE3321E0470(\*), HE3321E0500(\*), HE3321E0540(\*), HE3321E0570(\*), HE3321E1200(\*), HE3321E1240(\*), HE3321E1270(\*), HE3321E2400(\*), HE3321E2440(\*), HE3321E2470(\*), HE3331A0400(\*), HE3331A0440(\*), HE3331A0470(\*), HE3331A0500(\*), HE3331A0540(\*), HE3331A0570(\*), HE3331A1200(\*), HE3331A1240(\*), HE3331A1270(\*), HE3331A2400(\*), HE3331A2440(\*), HE3331A2470(\*), HE3331B0400(\*), HE3331B0440(\*), HE3331B0470(\*), HE3331B0500(\*), HE3331B0540(\*), HE3331B0570(\*), HE3331B1200(\*), HE3331B1240(\*), HE3331B1270(\*), HE3331B2400(\*), HE3331B2440(\*), HE3331B2470(\*), HE3331C0400(\*), HE3331C0440(\*), HE3331C0470(\*), HE3331C0500(\*), HE3331C0540(\*), HE3331C0570(\*), HE3331C1200(\*), HE3331C1240(\*), HE3331C1270(\*), HE3331C2400(\*), HE3331C2440(\*), HE3331C2470(\*), HE3331E0400(\*), HE3331E0440(\*), HE3331E0470(\*), HE3331E0500(\*), HE3331E0540(\*), HE3331E0570(\*), HE3331E1200(\*), HE3331E1240(\*), HE3331E1270(\*), HE3331E2400(\*), HE3331E2440(\*), HE3331E2470(\*), HE3351A0400(\*), HE3351A0440(\*), HE3351A0470(\*), HE3351A0500(\*), HE3351A0540(\*), HE3351A0570(\*), HE3351A1200(\*), HE3351A1240(\*), HE3351A1270(\*), HE3351A2400(\*), HE3351A2440(\*), HE3351A2470(\*), HE3351B0400(\*), HE3351B0440(\*), HE3351B0470(\*), HE3351B0500(\*), HE3351B0540(\*), HE3351B0570(\*), HE3351B1200(\*), HE3351B1240(\*), HE3351B1270(\*), HE3351B2400(\*), HE3351B2440(\*), HE3351B2470(\*), HE3351C0400(\*), HE3351C0440(\*), HE3351C0470(\*), HE3351C0500(\*), HE3351C0540(\*), HE3351C0570(\*), HE3351C1200(\*), HE3351C1240(\*), HE3351C1270(\*), HE3351C2400(\*), HE3351C2440(\*), HE3351C2470(\*), HE3351E0400(\*), HE3351E0440(\*), HE3351E0470(\*), HE3351E0500(\*), HE3351E0540(\*), HE3351E0570(\*), HE3351E1200(\*), HE3351E1240(\*), HE3351E1270(\*), HE3351E2400(\*), HE3351E2440(\*), HE3351E2470(\*), HE3361A0400(\*), HE3361A0440(\*), HE3361A0470(\*), HE3361A0500(\*), HE3361A0540(\*), HE3361A0570(\*), HE3361A1200(\*), HE3361A1240(\*), HE3361A1270(\*), HE3361A2400(\*), HE3361A2440(\*), HE3361A2470(\*), HE3361B0400(\*), HE3361B0440(\*), HE3361B0470(\*), HE3361B0500(\*), HE3361B0540(\*), HE3361B0570(\*), HE3361B1200(\*), HE3361B1240(\*), HE3361B1270(\*), HE3361B2400(\*), HE3361B2440(\*), HE3361B2470(\*), HE3361C0400(\*), HE3361C0440(\*), HE3361C0470(\*), HE3361C0500(\*), HE3361C0540(\*), HE3361C0570(\*), HE3361C1200(\*), HE3361C1240(\*), HE3361C1270(\*), HE3361C2400(\*), HE3361C2440(\*), HE3361C2470(\*), HE3361E0400(\*), HE3361E0440(\*), HE3361E0470(\*), HE3361E0500(\*), HE3361E0540(\*), HE3361E0570(\*), HE3361E1200(\*), HE3361E1240(\*), HE3361E1270(\*), HE3361E2400(\*), HE3361E2440(\*), HE3361E2470(\*), HE341A0500, HE341A0540, HE341A1200, HE341A1240, HE341A2400, HE341A2440, HE351A0500, HE351A0540, HE351A1200, HE351A1240, HE351A2400, HE351A2440, HE361A0500, HE361A0540, HE361A1200, HE361A1240, HE361A2400, HE361A2440, HE361A5010, HE421A5069, HE421A5181, HE421A5182, HE421A5183, HE421A5258, HE421A5259, HE421A5260, HE421A5318, HE421A5328, HE421A5376, HE421A5390, HE421A5391, HE421A6221, HE422B5449, HE451A5393, HE461A0504, HE461A1204, HE461A2404, HE561-A5050, HE561-B5051

**Magnetic reed relays, "HE Series"**, Model(s): HE3621A+, HE3621B+, HE3651A+, HE3651B+, HE3671A+, HE3671B+

**Open type reed relays for use in electronic data processing equipment, office appliances and business equipment**, Model(s): HE722A+, HE751A+

**Reed relays, for use in electronic data processing equipment, office appliances and business equipment, open type**, Model(s): HE721A, HE721B, HE721C, HE721E, HE721R

**Reed switches**, Model(s): BASE-14, DRR-129, DRS-50, MITI-3V1, MRPR-1, MRPR-2, MRPR-20, MRPR-3, MRPR-8

**Reed switches,** Model(s): DRS-DTHx where x may be numbers or letters.

**Reed switches,** Model(s): FLEX-14x where x may be numbers or letters

**Reed switches,** Model(s): MACD-14x where x may be numbers or letters

**Reed switches,** Model(s): MARR-2x where x may be numbers or letters

**Reed switches,** Model(s): MARR-5x where x may be numbers or letters

**Reed switches,** Model(s): MASM-14x where x may be numbers or letters

**Reed switches,** Model(s): MATE-12x where x may be numbers or letters

**Reed switches,** Model(s): MDCG-4x where x may be numbers or letters

**Reed switches,** Model(s): MDRR-6x where x may be numbers or letters.

**Reed switches,** Model(s): MDRR-DTx where x may be numbers or letters

**Reed switches,** Model(s): MDSM-10Bx where x may be numbers or letters.

**Reed switches,** Model(s): MDSM-4Bx where x may be numbers or letters

**Reed switches,** Model(s): MDSM-4Rx where x may be numbers or letters

**Reed switches,** Model(s): MDSM-7Bx where x may be numbers or letters

**Reed switches,** Model(s): MDSM-7Rx where x may be numbers or letters

**Reed switches,** Model(s): MDSM-DTBx where x may be numbers or letters

**Reed switches,** Model(s): MDSM-DTRx where x may be numbers or letters

**Reed switches,** Model(s): MDSR-10Rx where x may be numbers or letters.

**Reed switches,** Model(s): MDSR-10x where x may be numbers or letters.

**Reed switches,** Model(s): MDSR-4x where x may be numbers or letters

**Reed switches,** Model(s): MDSR-7x where x may be numbers or letters

**Reed switches,** Model(s): MISM-3V1x, where x can be a letters or a numbers

**Reed switches,** Model(s): MITI-7x and MISM-7x, where x can be letters or numbers

**Reed switches,** Model(s): MLRR-2x where x may be numbers or letters.

**Reed switches,** Model(s): MLRR-3x where x may be numbers or letters.

**Reed switches,** Model(s): MLRR-4x where x may be numbers or letters

**Reed switches,** Model(s): MLSM-3Bx where x may be numbers or letters.

**Reed switches,** Model(s): MLSM-3Rx where x may be numbers or letters.

**Reed switches,** Model(s): MLSM-4Bx where x may be numbers or letters

**Reed switches,** Model(s): MLSR-4Rx where x may be numbers or letters

**Reed switches**, Model(s): MVSR-20x where x may be numbers or letters

**Reed Switches**, Model(s): HA15-2x where x may be numbers or letters.

(\*) - Last four digits may be replaced by 5000 to 9999 incl.

(\*)

+ - Followed by 0000 through 9999.

+

Last Updated on 2023-12-11

---

并不是所有出现在本数据库中的公司名称和产品都满足了UL 跟踪检验服务的要求。只有带有 UL 标志的产品，才应该被视为经过UL认证，并满足UL跟踪检验服务的要求。注意查看产品上的标志。

UL 允许在线认证目录中所含材料的复制遵循以下条件：1.指南信息、装配、构造、设计、系统和/或认证（文件）必须在不篡改任何数据（或图纸）的情况下完整且无误性地呈现。2.“经 UL 允许从在线认证目录转载”声明必须出现在所摘取材料的邻近位置。此外，转载材料必须包含以下格式的版权声明： "©2024 UL LLC."