
IXYS


HiPerFAST™ IGBTs C2-Class High Speed w/ Diode

IXGA16N60C2D1
IXGP16N60C2D1
IXGH16N60C2D1


V_{CES} = 600V
I_{C110} = 16A
$V_{CE(sat)}$ ≤ 3.0V
$t_{fi(typ)}$ = 33ns




TO-263 AA (IXGA)



TO-220AB (IXGP)



TO-247 (IXGH)



G = Gate C = Collector
E = Emitter Tab = Collector

Symbol	Test Conditions	Maximum Ratings	
V_{CES}	T_J = 25°C to 150°C	600	V
V_{CGR}	T_J = 25°C to 150°C, R_{GE} = 1MΩ	600	V
V_{GES}	Continuous	±20	V
V_{GEM}	Transient	±30	V
I_{C25}	T_C = 25°C	40	A
I_{C110}	T_C = 110°C	16	A
I_{F110}	T_C = 110°C	11	A
I_{CM}	T_C = 25°C, 1ms	100	A
SSOA (RBSOA)	V_{GE} = 15V, T_J = 125°C, R_G = 22Ω Clamped Inductive load	I_{CM} = 32 $V_{CE} \le V_{CES}$	A
P_C	T_C = 25°C	150	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
M_d	Mounting Torque (TO-220 & TO-247)	1.13/10	Nm/lb.in.
F_C	Mounting Force (TO-263)	10..65 / 2.2..14.6	N/lb.
T_L	Maximum Lead Temperature for Soldering	300	°C
T_{SOLD}	1.6mm (0.062 in.) from Case for 10s	260	°C
Weight	TO-263	2.5	g
	TO-220	3.0	g
	TO-247	6.0	g

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
$V_{GE(th)}$	I_C = 250μA, V_{CE} = V_{GE}	3.0		5.5	V
I_{CES}	V_{CE} = V_{CES}, V_{GE} = 0V			25	μA
	T_J = 125°C			1	mA
I_{GES}	V_{CE} = 0V, V_{GE} = ±20V			±100	nA
$V_{CE(sat)}$	I_C = 12A, V_{GE} = 15V, Note1			3.0	V
	T_J = 125°C		1.8		V

Features

- Optimized for Low Switching Losses
- Square RBSOA
- Anti-Parallel Ultra Fast Diode
- International Standard Packages

Advantages

- High Power Density
- Low Gate Drive Requirement

Applications

- Power Inverters
- UPS
- Motor Drives
- SMPS
- PFC Circuits
- Battery Chargers
- Welding Machines
- Lamp Ballasts

© 2010 IXYS CORPORATION, All Rights Reserved

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	I_C = 12A, V_{CE} = 10V, Note 1	8			S
C_{ies}	V_{CE} = 25V, V_{GE} = 0V, f = 1MHz		657		pF
C_{oes}			72		pF
C_{res}			22		pF
$Q_{g(on)}$	I_C = 12A, V_{GE} = 15V, V_{CE} = 0.5 • V_{CES}		25		nC
Q_{ge}			5		nC
Q_{gc}			13		nC
$t_{d(on)}$	**Inductive load, T_J = 25°C**		16		ns
t_{ri}	I_C = 12A, V_{GE} = 15V		17		ns
E_{on}	V_{CE} = 400V, R_G = 22Ω		0.16		mJ
$t_{d(off)}$	Note 2		75		ns
t_{fi}			33		ns
E_{off}			0.09	0.16	mJ
$t_{d(on)}$	**Inductive load, T_J = 125°C**		16		ns
t_{ri}	I_C = 12A, V_{GE} = 15V		18		ns
E_{on}	V_{CE} = 400V, R_G = 22Ω		0.27		mJ
$t_{d(off)}$	Note 2		115		ns
t_{fi}			100		ns
E_{off}			0.27		mJ
R_{thJC}				0.83	°C/W
R_{thCK}	TO-220		0.50		°C/W
	TO-247		0.21		°C/W

Reverse Diode (FRED)

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
V_F	I_F = 10A, V_{GE} = 0V, Note 1			3.0	V
	T_J = 125°C		1.7		V
I_{RM}	I_F = 12A, V_{GE} = 0V,		2.5		A
t_{rr}	$-di_F/dt$ = 100A/μs, V_R = 100V, T_J = 125°C		110		ns
t_{rr}	I_F = 1A, V_{GE} = 0V, $-di_F/dt$ = 100A/μs, V_R = 30V		30		ns
R_{thJC}				2.5	°C/W


Notes:

1. Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.
2. Switching times & energy losses may increase for higher V_{CE}(Clamp), T_J or R_G.

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,850,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2 7,005,734 B2 7,063,975 B2 7,071,537 7,157,338B2


TO-263 (IXGA) Outline



1. Gate
2. Collector
3. Emitter
4. Collector
   Bottom Side

Dim.	Millimeter		Inches	
	Min.	Max.	Min.	Max.
A	4.06	4.83	.160	.190
b	0.51	0.99	.020	.039
b2	1.14	1.40	.045	.055
c	0.40	0.74	.016	.029
c2	1.14	1.40	.045	.055
D	8.64	9.65	.340	.380
D1	8.00	8.89	.280	.320
E	9.65	10.41	.380	.405
E1	6.22	8.13	.270	.320
e	2.54	BSC	.100	BSC
L	14.61	15.88	.575	.625
L1	2.29	2.79	.090	.110
L2	1.02	1.40	.040	.055
L3	1.27	1.78	.050	.070
L4	0	0.13	0	.005


TO-220 (IXGP) Outline



Pins: 1 - Gate 2 - Collector
3 - Emitter

SYM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	.170	.190	4.32	4.83
b	.025	.040	0.64	1.02
b1	.045	.065	1.15	1.65
c	.014	.022	0.35	0.56
D	.580	.630	14.73	16.00
E	.390	.420	9.91	10.66
e	.100 BSC		2.54 BSC	
F	.045	.055	1.14	1.40
H1	.230	.270	5.85	6.85
J1	.090	.110	2.29	2.79
k	0	.015	0	0.38
L	.500	.550	12.70	13.97
L1	.110	.230	2.79	5.84
ØP	.139	.161	3.53	4.08
Q	.100	.125	2.54	3.18

TO-247 (IXGH) AD Outline



1 = Gate
2 = Collector
3 = Emitter

SYM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	.185	.209	4.7	5.3
A_1	.087	.102	2.2	2.54
A_2	.059	.098	2.2	2.6
b	.040	.055	1.0	1.4
b_1	.065	.084	1.65	2.13
b_2	.113	.123	2.87	3.12
C	.016	.031	.4	.8
D	.819	.845	20.80	21.46
E	.610	.640	15.75	16.26
e	.215 BSC		5.45 BSC	
L	.780	.800	19.81	20.32
L1		.177		4.50
ØP	.140	.144	3.55	3.65
Q	.212	.244	5.4	6.2
R	.170	.216	4.32	5.49
S	.242 BSC		6.15 BSC	

© 2010 IXYS CORPORATION, All Rights Reserved

Fig. 1. Output Characteristics @ T_J = 25ºC




Fig. 2. Extended Output Characteristics @ T_J = 25ºC




Fig. 3. Output Characteristics @ T_J = 125ºC




Fig. 4. Dependence of $V_{CE(sat)}$ on Junction Temperature




Fig. 5. Collector-to-Emitter Voltage vs. Gate-to-Emitter Voltage





Fig. 6. Input Admittance



IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

Fig. 7. Transconductance




Fig. 8. Gate Charge




Fig. 9. Capacitance




Fig. 10. Reverse-Bias Safe Operating Area





Fig. 11. Maximum Transient Thermal Impedance



© 2010 IXYS CORPORATION, All Rights Reserved

Fig. 12. Inductive Switching Energy Loss vs. Gate Resistance




Fig. 13. Inductive Switching Energy Loss vs. Collector Current




Fig. 14. Inductive Switching Energy Loss vs. Junction Temperature




Fig. 15. Inductive Turn-off Switching Times vs. Gate Resistance




Fig. 16. Inductive Turn-off Switching Times vs. Collector Current





Fig. 17. Inductive Turn-off Switching Times vs. Junction Temperature



IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

Fig. 18. Inductive Turn-on Switching Times vs. Gate Resistance




Fig. 19. Inductive Turn-on Switching Times vs. Collector Current





Fig. 20. Inductive Turn-on Switching Times vs. Junction Temperature



© 2010 IXYS CORPORATION, All Rights Reserved



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.