


## Polar™ HiPerFET™ Power MOSFET


## IXFH69N30P IXFT69N30P

$$\begin{aligned} V_{DSS} &= 300V \\ I_{D25} &= 69A \\ R_{DS(on)} &\leq 49m\Omega \\ t_{rr} &\leq 200ns \end{aligned}$$


N-Channel Enhancement Mode  
Avalanche Rated  
Fast Intrinsic Diode



TO-247 (IXFH)



TO-268 (IXFT)



G = Gate      D = Drain  
S = Source    Tab = Drain

| Symbol     | Test Conditions                                                          | Maximum Ratings |                  |
|------------|--------------------------------------------------------------------------|-----------------|------------------|
| $V_{DSS}$  | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$                          | 300             | V                |
| $V_{DGR}$  | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$ , $R_{GS} = 1M\Omega$    | 300             | V                |
| $V_{GSS}$  | Continuous                                                               | $\pm 20$        | V                |
| $V_{GSM}$  | Transient                                                                | $\pm 30$        | V                |
| $I_{D25}$  | $T_C = 25^\circ\text{C}$                                                 | 69              | A                |
| $I_{DM}$   | $T_C = 25^\circ\text{C}$ , Pulse Width Limited by $T_{JM}$               | 200             | A                |
| $I_A$      | $T_C = 25^\circ\text{C}$                                                 | 69              | A                |
| $E_{AS}$   | $T_C = 25^\circ\text{C}$                                                 | 1.5             | J                |
| $dV/dt$    | $I_S \leq I_{DM}$ , $V_{DD} \leq V_{DSS}$ , $T_J \leq 150^\circ\text{C}$ | 20              | V/ns             |
| $P_D$      | $T_C = 25^\circ\text{C}$                                                 | 500             | W                |
| $T_J$      |                                                                          | -55 to +150     | $^\circ\text{C}$ |
| $T_{JM}$   |                                                                          | +150            | $^\circ\text{C}$ |
| $T_{stg}$  |                                                                          | -55 to +150     | $^\circ\text{C}$ |
| $T_L$      | 1.6mm (0.063in) from Case for 10s                                        | 300             | $^\circ\text{C}$ |
| $T_{SOLD}$ | Plastic Body for 10s                                                     | 260             | $^\circ\text{C}$ |
| $M_d$      | Mounting Torque (TO-247)                                                 | 1.13/10         | Nm/lb.in.        |
| Weight     | TO-247                                                                   | 6               | g                |
|            | TO-268                                                                   | 4               | g                |

| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified) | Characteristic Values |      |               |
|--------------|-----------------------------------------------------------------------------|-----------------------|------|---------------|
|              |                                                                             | Min.                  | Typ. | Max.          |
| $BV_{DSS}$   | $V_{GS} = 0V$ , $I_D = 250\mu A$                                            | 300                   |      | V             |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 4mA$                                             | 2.5                   |      | 5.0 V         |
| $I_{GSS}$    | $V_{GS} = \pm 20V$ , $V_{DS} = 0V$                                          |                       |      | $\pm 100$ nA  |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$ , $V_{GS} = 0V$<br>$T_J = 125^\circ\text{C}$             |                       |      | 25 $\mu A$    |
|              |                                                                             |                       |      | 250 $\mu A$   |
| $R_{DS(on)}$ | $V_{GS} = 10V$ , $I_D = 0.5 \cdot I_{D25}$ , Note 1                         |                       |      | 49 m $\Omega$ |

### Features

- International Standard Packages
- Fast Intrinsic Diode
- Avalanche Rated
- Low  $R_{DS(ON)}$  and  $Q_G$
- Low Package Inductance

### Advantages

- High Power Density
- Easy to Mount
- Space Savings

### Applications

- DC-DC Converters
- Battery Chargers
- Switch-Mode and Resonant-Mode Power Supplies
- DC Choppers
- AC and DC Motor Drives
- Uninterrupted Power Supplies
- High Speed Power Switching Applications


| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified)                                                                 | Characteristic Values |      |                        |
|--------------|---------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|------|------------------------|
|              |                                                                                                                                             | Min.                  | Typ. | Max.                   |
| $g_{fs}$     | $V_{DS} = 10\text{V}$ , $I_D = 0.5 \cdot I_{D25}$ , Note 1                                                                                  | 30                    | 48   | S                      |
| $C_{iss}$    | $V_{GS} = 0\text{V}$ , $V_{DS} = 25\text{V}$ , $f = 1\text{MHz}$                                                                            |                       | 4960 | pF                     |
| $C_{oss}$    |                                                                                                                                             |                       | 760  | pF                     |
| $C_{rss}$    |                                                                                                                                             |                       | 190  | pF                     |
| $t_{d(on)}$  | <b>Resistive Switching Times</b><br>$V_{GS} = 10\text{V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = 69\text{A}$<br>$R_G = 4\Omega$ (External) |                       | 25   | ns                     |
| $t_r$        |                                                                                                                                             |                       | 25   | ns                     |
| $t_{d(off)}$ |                                                                                                                                             |                       | 75   | ns                     |
| $t_f$        |                                                                                                                                             |                       | 27   | ns                     |
| $Q_{g(on)}$  | $V_{GS} = 10\text{V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = 34.5\text{A}$                                                                 |                       | 156  | nC                     |
| $Q_{gs}$     |                                                                                                                                             |                       | 32   | nC                     |
| $Q_{gd}$     |                                                                                                                                             |                       | 79   | nC                     |
| $R_{thJC}$   | TO-247                                                                                                                                      |                       | 0.21 | $0.25^\circ\text{C/W}$ |
| $R_{thCS}$   |                                                                                                                                             |                       |      | $^\circ\text{C/W}$     |

## Source-Drain Diode

| Symbol   | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified)                             | Characteristic Values |      |        |
|----------|---------------------------------------------------------------------------------------------------------|-----------------------|------|--------|
|          |                                                                                                         | Min.                  | Typ. | Max.   |
| $I_S$    | $V_{GS} = 0\text{V}$                                                                                    |                       |      | 69 A   |
| $I_{SM}$ | Repetitive, Pulse Width Limited by $T_{JM}$                                                             |                       |      | 270 A  |
| $V_{SD}$ | $I_F = I_S$ , $V_{GS} = 0\text{V}$ , Note 1                                                             |                       |      | 1.5 V  |
| $t_{rr}$ | $I_F = 25\text{A}$ , $-di/dt = 100\text{A}/\mu\text{s}$ ,<br>$V_R = 100\text{V}$ , $V_{GS} = 0\text{V}$ |                       | 100  | 200 ns |
| $Q_{RM}$ |                                                                                                         |                       | 500  | nC     |

Note 1. Pulse test,  $t \leq 300\mu\text{s}$ , duty cycle,  $d \leq 2\%$ .


## TO-247 (IXFH) Outline



Terminals: 1 - Gate 2 - Drain  
3 - Source Tab - Drain

| Dim.           | Millimeter |       | Inches |       |
|----------------|------------|-------|--------|-------|
|                | Min.       | Max.  | Min.   | Max.  |
| A              | 4.7        | 5.3   | .185   | .209  |
| A <sub>1</sub> | 2.2        | 2.54  | .087   | .102  |
| A <sub>2</sub> | 2.2        | 2.6   | .059   | .098  |
| b              | 1.0        | 1.4   | .040   | .055  |
| b <sub>1</sub> | 1.65       | 2.13  | .065   | .084  |
| b <sub>2</sub> | 2.87       | 3.12  | .113   | .123  |
| C              | .4         | .8    | .016   | .031  |
| D              | 20.80      | 21.46 | .819   | .845  |
| E              | 15.75      | 16.26 | .610   | .640  |
| e              | 5.20       | 5.72  | 0.205  | 0.225 |
| L              | 19.81      | 20.32 | .780   | .800  |
| L <sub>1</sub> |            | 4.50  |        | .177  |
| ØP             | 3.55       | 3.65  | .140   | .144  |
| Q              | 5.89       | 6.40  | 0.232  | 0.252 |
| R              | 4.32       | 5.49  | .170   | .216  |
| S              | 6.15       | BSC   | .242   | BSC   |

## TO-268 (IXFT) Outline



Terminals: 1 - Gate 2 - Drain  
3 - Source Tab - Drain

| SYM            | INCHES |      | MILLIMETERS |       |
|----------------|--------|------|-------------|-------|
|                | MIN    | MAX  | MIN         | MAX   |
| A              | .193   | .201 | 4.90        | 5.10  |
| A <sub>1</sub> | .106   | .114 | 2.70        | 2.90  |
| A <sub>2</sub> | .001   | .010 | 0.02        | 0.25  |
| b              | .045   | .057 | 1.15        | 1.45  |
| b <sub>2</sub> | .075   | .083 | 1.90        | 2.10  |
| C              | .016   | .026 | 0.40        | 0.65  |
| C <sub>2</sub> | .057   | .063 | 1.45        | 1.60  |
| D              | .543   | .551 | 13.80       | 14.00 |
| D <sub>1</sub> | .488   | .500 | 12.40       | 12.70 |
| E              | .624   | .632 | 15.85       | 16.05 |
| E <sub>1</sub> | .524   | .535 | 13.30       | 13.60 |
| e              | .215   | BSC  | 5.45        | BSC   |
| H              | .736   | .752 | 18.70       | 19.10 |
| L              | .094   | .106 | 2.40        | 2.70  |
| L <sub>1</sub> | .047   | .055 | 1.20        | 1.40  |
| L <sub>2</sub> | .039   | .045 | 1.00        | 1.15  |
| L <sub>3</sub> | .010   | BSC  | 0.25        | BSC   |
| L <sub>4</sub> | .150   | .161 | 3.80        | 4.10  |

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

|                                                                                  |           |           |           |           |              |              |              |              |              |             |
|----------------------------------------------------------------------------------|-----------|-----------|-----------|-----------|--------------|--------------|--------------|--------------|--------------|-------------|
| IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: | 4,835,592 | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665    | 6,404,065 B1 | 6,683,344    | 6,727,585    | 7,005,734 B2 | 7,157,338B2 |
|                                                                                  | 4,850,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123 B1 | 6,534,343    | 6,710,405 B2 | 6,759,692    | 7,063,975 B2 |             |
|                                                                                  | 4,881,106 | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728 B1 | 6,583,505    | 6,710,463    | 6,771,478 B2 | 7,071,537    |             |







**Fig. 1. Output Characteristics @  $T_J = 25^\circ\text{C}$** 

**Fig. 2. Extended Output Characteristics @  $T_J = 25^\circ\text{C}$** 

**Fig. 3. Output Characteristics @  $T_J = 125^\circ\text{C}$** 

**Fig. 4.  $R_{DS(on)}$  Normalized to  $I_D = 34.5\text{A}$  Value vs. Junction Temperature**

**Fig. 5.  $R_{DS(on)}$  Normalized to  $I_D = 34.5\text{A}$  Value vs. Drain Current**

**Fig. 6. Maximum Drain Current vs. Case Temperature**


Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Forward Voltage Drop of Intrinsic Diode




Fig. 10. Gate Charge




Fig. 11. Capacitance




Fig. 12. Forward-Bias Safe Operating Area





Fig. 12. Maximum Transient Thermal Impedance





---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).