
HiPerFET™ Power MOSFETs

	V_{DSS}	I_{D25}	$R_{DS(on)}$
IXFK 73 N 30	300 V	73 A	45 mΩ
IXFN 73 N 30	300 V	73 A	45 mΩ

$t_{rr} \leq 200$ ns


N-Channel Enhancement Mode
Avalanche Rated, High dv/dt, Low t_{rr}

TO-264 AA (IXFK)



miniBLOC, SOT-227 B (IXFN)

E153432



G = Gate D = Drain
S = Source TAB = Drain

Either Source terminal at miniBLOC can be used as Main or Kelvin Source

Symbol	Test Conditions	Maximum Ratings IXFK	IXFN	
V_{DSS}	T_J = 25°C to 150°C	300	300	V
V_{DGR}	T_J = 25°C to 150°C; R_{GS} = 1 MΩ	300	300	V
V_{GS}	Continuous	±20	±20	V
V_{GSM}	Transient	±30	±30	V
I_{D25}	T_C = 25°C	73	73	A
I_{DM}	T_C = 25°C, pulse width limited by T_{JM}	292	292	A
I_{AR}	T_C = 25°C	40	40	A
E_{AR}	T_C = 25°C	30	30	mJ
dv/dt	$I_S \leq I_{DM}$, di/dt ≤ 100 A/μs, $V_{DD} \leq V_{DSS}$, $T_J \leq 150$°C, R_G = 2 W	5	5	V/ns
P_D	T_C = 25°C	500	520	W
T_J		-55 ... +150		°C
T_{JM}			150	°C
T_{stg}		-55 ... +150		°C
T_L	1.6 mm (0.063 in) from case for 10 s	300	-	°C
V_{ISOL}	50/60 Hz, RMS t = 1 min	-	2500	V~
	$I_{ISOL} \leq$ 1 mA t = 1 s	-	3000	V~
M_d	Mounting torque	0.9/6	1.5/13	Nm/lb.in.
	Terminal connection torque	-	1.5/13	Nm/lb.in.
Weight		10	30	g

Symbol	Test Conditions (T_J = 25°C, unless otherwise specified)	Characteristic Values min.	typ.	max.	
V_{DSS}	V_{GS} = 0 V, I_D = 1 mA	300			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 8 mA	2		4	V
I_{GSS}	V_{GS} = ±20 V_{DC}, V_{DS} = 0			±200	nA
I_{DSS}	V_{DS} = 0.8 V_{DSS} T_J = 25°C			400	uA
	V_{GS} = 0 V T_J = 125°C			2	mA
$R_{DS(on)}$	V_{GS} = 10 V, I_D = 0.5 I_{D25} Pulse test, t ≤ 300 μs, duty cycle d ≤ 2 %			45	mΩ

Features

- International standard packages
- JEDEC TO-264 AA, epoxy meet UL94 V-0, flammability classification
- miniBLOC with Aluminium nitride isolation
- Low $R_{DS(on)}$ HDMOS™ process
- Rugged polysilicon gate cell structure
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
- Fast intrinsic Rectifier

Applications

- DC-DC converters
- Synchronous rectification
- Battery chargers
- Switched-mode and resonant-mode power supplies
- DC choppers
- Temperature and lighting controls
- Low voltage relays

Advantages

- Easy to mount
- Space savings
- High power density


© 2001 IXYS All rights reserved

Symbol	Test Conditions (T_J = 25°C, unless otherwise specified)	Characteristic Values min.	typ.	max.	
g_{fs}	V_{DS} = 10 V; I_D = 0.5 I_{D25}, pulse test		50		S
C_{iss}	V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz		9000		pF
C_{oss}			1500		pF
C_{rss}			580		pF
$t_{d(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 V_{DSS}, I_D = 0.5 I_{D25} R_G = 1 Ω (External),		30		ns
t_r			80		ns
$t_{d(off)}$			100		ns
t_f			50		ns
$Q_{g(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 V_{DSS}, I_D = 0.5 I_{D25}		360		nC
Q_{gs}			60		nC
Q_{gd}			180		nC
R_{thJC}	TO-264 AA			0.25	K/W
R_{thCK}	TO-264 AA		0.15		K/W
R_{thJC}	miniBLOC, SOT-227 B			0.24	K/W
R_{thCK}	miniBLOC, SOT-227 B		0.05		K/W

Source-Drain Diode


Symbol	Test Conditions (T_J = 25°C, unless otherwise specified)	Characteristic Values min.	typ.	max.	
I_S	V_{GS} = 0 V			73	A
I_{SM}	Repetitive; pulse width limited by T_{JM}			292	A
V_{SD}	I_F = 100 A, V_{GS} = 0 V, Pulse test, t ≤ 300 µs, duty cycle d ≤ 2 %			1.5	V
t_{rr}	I_F = I_S, -di/dt = 100 A/µs, V_R = 100 V			200	ns
Q_{RM}			2		µC
I_{RM}			40		A

TO-264 AA Outline



Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.82	5.13	.190	.202
A1	2.54	2.89	.100	.114
A2	2.00	2.10	.079	.083
b	1.12	1.42	.044	.056
b1	2.39	2.69	.094	.106
b2	2.90	3.09	.114	.122
c	0.53	0.83	.021	.033
D	25.91	26.16	1.020	1.030
E	19.81	19.96	.780	.786
e	5.46 BSC		.215 BSC	
J	0.00	0.25	.000	.010
K	0.00	0.25	.000	.010
L	20.32	20.83	.800	.820
L1	2.29	2.59	.090	.102
P	3.17	3.66	.125	.144
Q	6.07	6.27	.239	.247
Q1	8.38	8.69	.330	.342
R	3.81	4.32	.150	.170
R1	1.78	2.29	.070	.090
S	6.04	6.30	.238	.248
T	1.57	1.83	.062	.072

miniBLOC, SOT-227 B



M4 screws (4x) supplied

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	31.50	31.88	1.240	1.255
B	7.80	8.20	0.307	0.323
C	4.09	4.29	0.161	0.169
D	4.09	4.29	0.161	0.169
E	4.09	4.29	0.161	0.169
F	14.91	15.11	0.587	0.595
G	30.12	30.30	1.186	1.193
H	38.00	38.23	1.496	1.505
J	11.68	12.22	0.460	0.481
K	8.92	9.60	0.351	0.378
L	0.76	0.84	0.030	0.033
M	12.60	12.85	0.496	0.506
N	25.15	25.42	0.990	1.001
O	1.98	2.13	0.078	0.084
P	4.95	5.97	0.195	0.235
Q	26.54	26.90	1.045	1.059
R	3.94	4.42	0.155	0.174
S	4.72	4.85	0.186	0.191
T	24.59	25.07	0.968	0.987
U	-0.05	0.1	-0.002	0.004

IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETS and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,881,106 5,017,508 5,049,961 5,187,117 5,486,715 4,850,072 4,931,844 5,034,796 5,063,307 5,237,481 5,381,025

Fig. 1 Output Characteristics




Fig. 2 Input Admittance




Fig. 3 $R_{DS(on)}$ vs. Drain Current




Fig. 4 Temperature Dependence of Drain to Source Resistance




Fig. 5 Drain Current vs. Case Temperature





Fig. 6 Temperature Dependence of Breakdown and Threshold Voltage



© 2001 IXYS All rights reserved

Fig.7 Gate Charge Characteristic Curve




Fig.8 Capacitance Curves




Fig.9 Source Current vs. Source to Drain Voltage





Fig.10 Transient Thermal Impedance



IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETS and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,881,106 5,017,508 5,049,961 5,187,117 5,486,715 4,850,072 4,931,844 5,034,796 5,063,307 5,237,481 5,381,025



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.