
IXYS

PolarHV™ Power MOSFET

N-Channel Enhancement Mode
Fast Recovery Diode
Avalanche Rated


IXFH 16N80P
IXFT 16N80P
IXFV 16N80P
IXFV 16N80PS

V_{DSS} = 800 V
I_{D25} = 16 A
$R_{DS(on)}$ ≤ 600 mΩ
t_{rr} ≤ 250 ns




Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 150°C	800	V
V_{DGR}	T_J = 25°C to 150°C; R_{GS} = 1 MΩ	800	V
V_{GSS}	Continuous	±30	V
V_{GSM}	Transient	±40	V
I_{D25}	T_C = 25°C	16	A
I_{DM}	T_C = 25°C, pulse width limited by T_{JM}	40	A
I_{AR}	T_C = 25°C	8	A
E_{AR}	T_C = 25°C	30	mJ
E_{AS}	T_C = 25°C	1.0	J
dv/dt	$I_S \le I_{DM}$, di/dt ≤ 100 A/µs, $V_{DD} \le V_{DSS}$ $T_J \le$ 150°C, R_G = 5 Ω	10	V/ns
P_D	T_C = 25°C	460	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
T_L	1.6 mm (0.062 in.) from case for 10 s	300	°C
T_{SOLD}	Plastic body for 10 s	260	°C
M_d	Mounting torque (TO-247)	1.13/10	Nm/lb.in.
F_C	Mounting force (PLUS220)	11..65/2.5..15	N/lb
Weight	TO-247	6.0	g
	TO-268	5.0	g
	PLUS220 & PLUS220SMD	4.0	g


TO-247 (IXFH)




TO-268 (IXFT)



PLUS220 (IXFV)



PLUS220SMD (IXFV...S)



G = Gate D = Drain
S = Source TAB = Drain

Symbol	Test Conditions (T_J = 25°C, unless otherwise specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0 V, I_D = 250 µA	800			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 4 mA	3.0		5.0	V
I_{GSS}	V_{GS} = ±30 V, V_{DS} = 0 V			±100	nA
I_{DSS}	$V_{DS} = V_{DSS}$ V_{GS} = 0 V T_J = 125°C			25 250	µA µA
$R_{DS(on)}$	V_{GS} = 10 V, $I_D = 0.5\ I_{D25}$ Pulse test, t ≤ 300 µs, duty cycle d ≤ 2 %			600	mΩ

Features
- Fast Recovery diode
- Unclamped Inductive Switching (UIS) rated
- International standard packages
- Low package inductance
  - easy to drive and to protect

Advantages
- Easy to mount
- Space savings
- High power density

© 2006 IXYS All rights reserved

Symbol	Test Conditions (T_J = 25°C, unless otherwise specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	V_{DS} = 20 V; I_D = 0.5 I_{D25}, pulse test	9	16		S
C_{iss}	V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz		4600		pF
C_{oss}			330		pF
C_{rss}			23		pF
$t_{d(on)}$	V_{GS} = 10 V, V_{DS} = V_{DSS}, I_D = 0.5 I_{D25} R_G = 5 Ω (External)		27		ns
t_r			32		ns
$t_{d(off)}$			75		ns
t_f			29		ns
$Q_{g(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 V_{DSS}, I_D = 0.5 I_{D25}		71		nC
Q_{gs}			21		nC
Q_{gd}			23		nC
R_{thJC}				0.27	°C/W
R_{thCS}	(TO-247)		0.21		°C/W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C, unless otherwise specified)	Characteristic Values Min.	Typ.	Max.	
I_S	V_{GS} = 0 V			16	A
I_{SM}	Repetitive			48	A
V_{SD}	I_F = I_S, V_{GS} = 0 V, pulse test			1.5	V
t_{rr}	I_F = 25A, -di/dt = 100 A/µs		150	250	ns
I_{RM}	V_R = 100V; V_{GS} = 0 V		7		A
Q_{RM}			0.7		µC

IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETs and IGBTs are covered by one or moreof the following U.S. patents: 4,835,592 4,850,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2 7,005,734 B2 7,063,975 B2 7,071,537

Fig. 1. Output Characteristics @ 25ºC




Fig. 2. Extended Output Characteristics @ 25ºC




Fig. 3. Output Characteristics @ 125ºC




Fig. 4. $R_{DS(on)}$ Normalized to I_D = 8A Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to I_D = 8A Value vs. Drain Current





Fig. 6. Maximum Drain Current vs. Case Temperature



© 2006 IXYS All rights reserved

Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Forward Voltage Drop of Intrinsic Diode




Fig. 10. Gate Charge




Fig. 11. Capacitance






Fig. 12. Maximum Transient Thermal Resistance




IXYS reserves the right to change limits, test conditions, and dimensions.

TO-247 AD (IXFH) Outline




Dim.	Millimeter		Inches	
	Min.	Max.	Min.	Max.
A	4.7	5.3	.185	.209
A_1	2.2	2.54	.087	.102
A_2	2.2	2.6	.059	.098
b	1.0	1.4	.040	.055
b_1	1.65	2.13	.065	.084
b_2	2.87	3.12	.113	.123
C	.4	.8	.016	.031
D	20.80	21.46	.819	.845
E	15.75	16.26	.610	.640
e	5.20	5.72	0.205	0.225
L	19.81	20.32	.780	.800
L1		4.50		.177
ØP	3.55	3.65	.140	.144
Q	5.89	6.40	0.232	0.252
R	4.32	5.49	.170	.216
S	6.15 BSC		242 BSC	

TO-268 (IXFT) Outline




SYM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	.193	.201	4.90	5.10
A1	.106	.114	2.70	2.90
A2	.001	.010	0.02	0.25
b	.045	.057	1.15	1.45
b2	.075	.083	1.90	2.10
C	.016	.026	0.40	0.65
C2	.057	.063	1.45	1.60
D	.543	.551	13.80	14.00
D1	.488	.500	12.40	12.70
E	.624	.632	15.85	16.05
E1	.524	.535	13.30	13.60
e	.215 BSC		5.45 BSC	
H	.736	.752	18.70	19.10
L	.094	.106	2.40	2.70
L1	.047	.055	1.20	1.40
L2	.039	.045	1.00	1.15
L3	.010 BSC		0.25 BSC	
L4	.150	.161	3.80	4.10

PLUS220 (IXFV) Outline



SYM	INCHES		MILLIMETER	
	MIN	MAX	MIN	MAX
A	.169	.185	4.30	4.70
A1	.028	.035	0.70	0.90
A2	.098	.118	2.50	3.00
b	.035	.047	0.90	1.20
b1	.080	.095	2.03	2.41
b2	.054	.064	1.37	1.63
c	.028	.035	0.70	0.90
D	.551	.591	14.00	15.00
D1	.512	.539	13.00	13.70
E	.394	.433	10.00	11.00
E1	.331	.346	8.40	8.80
e	.100BSC		2.54 BSC	
L	.512	.551	13.00	14.00
L1	.118	.138	3.00	3.50
L2	.035	.051	0.90	1.30
L3	.047	.059	1.20	1.50

PLUS220SMD (IXFV_S) Outline



SYM	INCHES		MILLIMETER	
	MIN	MAX	MIN	MAX
A	.169	.185	4.30	4.70
A1	.028	.035	0.70	0.90
A2	.098	.118	2.50	3.00
A3	.000	.010	0.00	0.25
b	.035	.047	0.90	1.20
b1	.080	.095	2.03	2.41
b2	.054	.064	1.37	1.63
c	.028	.035	0.70	0.90
D	.551	.591	14.00	15.00
D1	.512	.539	13.00	13.70
E	.394	.433	10.00	11.00
E1	.331	.346	8.40	8.80
e	.200BSC		5.08 BSC	
L	.209	.228	5.30	5.80
L1	.118	.138	3.00	3.50
L2	.035	.051	0.90	1.30
L3	.047	.059	1.20	1.50
L4	.039	.059	1.00	1.50

© 2006 IXYS All rights reserved



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.