

PAL Fuses - 2938 Series

32 V DC

RoHS

Specifications

Voltage Rating:	32 V DC
Current Cycling:	24°C
Operating Temperature Range:	-40°C to +125°C
Complies with	JASO 0612



PAL Fuses - 2938 Series

Description

Many Japanese automakers use 2938 Series Auto Link PAL fuses as original equipment. These 32 V cartridge fuses withstand extreme temperatures while protecting circuits for alternators and starters. During tests, each of the 2938 Series PAL fuses met its performance requirements when receiving 50 % of its ampere rating for 10 000 cycles when current flowed for 5 minutes and was shut off for 10 minutes. The tests were conducted while the temperature of the bolt-down cartridge fuse was 24 °C.

Features & Benefits

- Color coding indicates ampere rating
- Transparent covers make it easier to see when fuses blow
- Snap securely onto terminals

Applications

- Cars made in Japan and the United States

Ordering Information

Part Number	Package Size
02938xxx.H	100
02938xxx.U	500
02938xxx.MXJ	1000

PAL Fuses - 2938 Series

32 V DC


Ratings

Part Number	Current Rating (A)	Body Color
0293820._	20	LIGHT BLUE
0293830._	30	PINK
0293840._	40	GREEN
0293850._	50	RED
0293860._	60	YELLOW
0293870._	70	BROWN
0293880._	80	BLACK

(Average Initial Measurements)

Dimensions

Dimensions in mm



PAL Fuses - 2938 Series

32 V DC

Time-Current Characteristics

% of Rating	Opening Time Min / Max (s)
110	14,400
200	5 / 100
350	0.2 / 7
600	0.040 / 1