

# CONTINUOUS DUTY SOLENOIDS

6-32V DC • 65-200A • Uncoated or PVC-Coated



## Specifications Overview

<b>Voltage Ratings:</b>	6, 12, 24, or 36V DC
<b>Max Continuous Current:</b>	65, 85, or 200A
<b>Circuitry:</b>	Single Pole Single Throw (SPST)
<b>Contact Form:</b>	Normally Open
<b>Contact Terminals:</b>	Copper or Silver
<b>Operating Temp:</b>	-40° to +85°C
<b>Battery Terminals:</b>	5/16 - 24 (35 in-lbs / 4.0 Nm)
<b>Coil Studs:</b>	10-32 (15 in-lbs / 1.7 Nm)

## Description

Minimizes arcing and contact oxidation, maintains high performance. Universal use with part numbers available to handle loads up to 200A.


PVC Coated option available for a more environmentally-sealed product. Coated solenoids withstand moisture and dust to IP66.

Where vehicle vibration is a problem, we recommend the 24213-01 in which the internal windings are potted for added protection of coil leads and studs.

## Web Resources

Download 2D prints and technical resources at:  
[littelfuse.com/solenoids](http://littelfuse.com/solenoids)

## Electrical Schematic



## Mechanical Specifications


- SPST Normally open contacts.
- Plated steel housing. Hexnuts and washers included.
- Large (power circuit) battery studs; copper 5/16" -24 thread.
- Small (control circuit) coil studs; steel 10-32 thread.
- Bracket mounting holes 5/16 X 19/32" (7.9 X 15.1mm) on 2 13/64" centers (56.0mm).
- Available with PVC coated exterior or Potted Coil interiors for harsh environments or vibration resistance.
- Caution: Never unscrew the inner hexnuts on the studs. These keep the stud and inner wiring in place.

## Ordering Information

See chart on page 2

Datasheet Replaces Hotfeed Number D-500

# CONTINUOUS DUTY SOLENOIDS



A



B



C



D



E

## Ordering Information

PART NUMBERS			VOLTAGE	AMPS	INSULATED / GROUNDED	CIRCUITRY	FORM / CONTACTS	CONTACT MATERIAL	PVC COATED	UL LISTED	POTTED COIL	IMAGE	DIAGRAM	NOTES		
BULK	BOXED	RETAIL														
24080	24080-BX	-	36	85	Insulated	SPST	NO	Copper				A	1			
24080-01	-	-		65	Insulated	SPST	NO	Copper		•			A	1	Intermittent rating: 125A Make, 65A Break 10 sec on, 30 min off - UL Requirement	
24200	24200-BX	-		110	Insulated	SPST	NO	Copper					A	Refer to 2D Print	Momentary switch, latching solenoid	
24008	24008-BX	-		120	Insulated	SPST	NO	Copper					A		Special spring for stronger contact return force	
24008-03	-	-		120	Insulated	SPST	NO	Copper					A		Components shipped unassembled	
24063	24063-BX	-		85	Insulated	SPST	NO	Silver					A	1		
24063-08	24063-08-BX	-		24	85	Insulated	SPST	NO	Copper	•	•		B	1		
24214	24214-BX	-			200	Insulated	SPST	NO	Silver					A	1	
24107	24107-BX	-			85	Insulated	SPST	NO	Copper					C	2	
24124	24124-BX	-			85	Grounded	SPST	NO	Copper					C	4	
24524-10D	-	-	100		Insulated	SPST	NO	Copper				Refer to 2D Print	Refer to 2D Print			
24037	24037-BX	-	12	750	Grounded	SPST	NO	Copper				C	4			
24044	24044-BX	-		750	Grounded	SPST	NO	Copper					D	4		
24047	24047-BX	-		750	Insulated	SPST	NO	Copper					A	1		
24059	24059-BX	24059-BP		85	Insulated	SPST	NO	Copper					A	1		
24059-08	24059-08-BX	24059-08-BP		65	Insulated	SPST	NO	Copper		•			A	1	Intermittent rating: 750A Make, 100A Break 10 sec on, 30 min off - UL Requirement	
24106-07	-	-		85	Grounded	SPST	NO	Copper					C	4	P/N, Date Code, Voltage ink stamped on surface	
24115	24115-BX	-		85	Insulated	SPST	NO	Copper					C	3		
24117	24117-BX	-		Insulated	SPST	NO	Copper	•					B	1		
24117-01	24117-01-BX	24117-01-BP		Insulated	SPST	NO	Copper	•					B	1		
24213	24213-BX	24213-BP		200	Insulated	SPST	NO	Silver					A	1		
24213-01	-	-	200	Insulated	SPST	NO	Silver			•		B	1	IP66		
24213-03	-	-	200	Insulated	SPST	NO	Silver	•				B	1	Black PVC Coating • IP66		
24106	24106-BX	-	85	Grounded	SPST	NO	Copper					C	4			
24082	24082-BX	-	85	Grounded	SPST	NO	Copper					D	4	Curved Bracket		
24420	24420-BX	24420-BP	35	Insulated	SPST	NO	Copper	•	•			E	5			
24097	24097-BX	-	6	85	Insulated	SPST	NO	Copper				A	1			