
# IXYS

## Polar™ HiPerFET™ Power MOSFET


## IXFA7N100P
## IXFP7N100P
## IXFH7N100P

$V_{DSS}$ = 1000V
$I_{D25}$ = 7A
$R_{DS(on)}$ ≤ 1.9Ω


N-Channel Enhancement Mode
Avalanche Rated
Fast Intrinsic Rectifier





**TO-263 (IXFA)**




**TO-220 (IXFP)**




**TO-247 (IXFH)**




G = Gate D = Drain
S = Source Tab = Drain

| Symbol | Test Conditions | Maximum Ratings | |
|---|---|---|---|
| $V_{DSS}$ | $T_J$ = 25°C to 150°C | 1000 | V |
| $V_{DGR}$ | $T_J$ = 25°C to 150°C, $R_{GS}$ = 1MΩ | 1000 | V |
| $V_{GSS}$ | Continuous | ±30 | V |
| $V_{GSM}$ | Transient | ±40 | V |
| $I_{D25}$ | $T_C$ = 25°C | 7 | A |
| $I_{DM}$ | $T_C$ = 25°C, Pulse Width Limited by $T_{JM}$ | 18 | A |
| $I_A$ | $T_C$ = 25°C | 7 | A |
| $E_{AS}$ | $T_C$ = 25°C | 300 | mJ |
| dv/dt | $I_S \le I_{DM}$, $V_{DD} \le V_{DSS}$, $T_J \le 150°C$ | 10 | V/ns |
| $P_D$ | $T_C$ = 25°C | 300 | W |
| $T_J$ | | -55 ... +150 | °C |
| $T_{JM}$ | | 150 | °C |
| $T_{stg}$ | | -55 ... +150 | °C |
| $T_L$ | Maximum Lead Temperature for Soldering | 300 | °C |
| $T_{SOLD}$ | Plastic Body for 10s | 260 | °C |
| $F_C$ | Mounting Force (TO-263) | 10..65 / 2.2..14.6 | N/lb |
| $M_d$ | Mounting Torque (TO-220 & TO-247) | 1.13 / 10 | Nm/lb.in |
| Weight | TO-263 | 2.5 | g |
| | TO-220 | 3.0 | g |
| | TO-247 | 6.0 | g |

| Symbol | Test Conditions ($T_J$ = 25°C, Unless Otherwise Specified) | Characteristic Values Min. | Typ. | Max. | |
|---|---|---|---|---|---|
| $BV_{DSS}$ | $V_{GS}$ = 0V, $I_D$ = 250μA | 1000 | | | V |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$, $I_D$ = 1mA | 3.0 | | 6.0 | V |
| $I_{GSS}$ | $V_{GS}$ = ±30V, $V_{DS}$ = 0V | | | ±100 | nA |
| $I_{DSS}$ | $V_{DS} = V_{DSS}$, $V_{GS}$ = 0V | | | 15 | μA |
| | $T_J$ = 125°C | | | 1 | mA |
| $R_{DS(on)}$ | $V_{GS}$ = 10V, $I_D = 0.5 \bullet I_{D25}$, Note 1 | | | 1.9 | Ω |

### Features

- International Standard Packages
- Fast Intrinsic Rectifier
- Avalanche Rated
- Low $R_{DS(ON)}$ and $Q_G$
- Low Package Inductance

### Advantages

- High Power Density
- Easy to Mount
- Space Savings

### Applications

- Switch-Mode and Resonant-Mode Power Supplies
- DC-DC Converters
- Laser Drivers
- AC and DC Motor Drives
- Robotics and Servo Controls

© 2018 IXYS CORPORATION, All Rights Reserved

| Symbol | Test Conditions ($T_J$ = 25°C, Unless Otherwise Specified) | Characteristic Values Min. | Typ. | Max | |
|---|---|---|---|---|---|
| $g_{fs}$ | $V_{DS}$ = 20V, $I_D$ = 0.5 • $I_{D25}$, Note 1 | 3.6 | 6.0 | | S |
| $R_{Gi}$ | Gate Input Resistance | | 1.8 | | Ω |
| $C_{iss}$ | $V_{GS}$ = 0V, $V_{DS}$ = 25V, f = 1MHz | | 2590 | | pF |
| $C_{oss}$ | | | 158 | | pF |
| $C_{rss}$ | | | 26 | | pF |
| $t_{d(on)}$ | **Resistive Switching Times** | | 25 | | ns |
| $t_r$ | $V_{GS}$ = 10V, $V_{DS}$ = 0.5 • $V_{DSS}$, $I_D$ = 0.5 • $I_{D25}$ | | 49 | | ns |
| $t_{d(off)}$ | $R_G$ = 10Ω (External) | | 42 | | ns |
| $t_f$ | | | 44 | | ns |
| $Q_{g(on)}$ | $V_{GS}$ = 10V, $V_{DS}$ = 0.5 • $V_{DSS}$, $I_D$ = 0.5 • $I_{D25}$ | | 47 | | nC |
| $Q_{gs}$ | | | 21 | | nC |
| $Q_{gd}$ | | | 21 | | nC |
| $R_{thJC}$ | | | | 0.42 | °C/W |
| $R_{thCS}$ | TO-220 | | 0.50 | | °C/W |
| | TO-247 | | 0.21 | | °C/W |

**Source-Drain Diode**

| Symbol | Test Conditions ($T_J$ = 25°C, Unless Otherwise Specified) | Characteristic Values Min. | Typ. | Max | |
|---|---|---|---|---|---|
| $I_S$ | $V_{GS}$ = 0V, Note1 | | | 7 | A |
| $I_{SM}$ | Repetitive, Pulse Width Limited by $T_{JM}$ | | | 28 | A |
| $V_{SD}$ | $I_F$ = $I_S$, $V_{GS}$ = 0V, Note 1 | | | 1.3 | V |
| $t_{rr}$ | $I_F$ = 3.5A, -di/dt = 100A/μs | | | 300 | ns |
| $Q_{RM}$ | $V_R$ = 100V | | 0.4 | | μC |
| $I_{RM}$ | | | 4.0 | | A |

Note 1. Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,860,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123B1 6,306,728B1 6,404,065B1 6,534,343 6,583,505 6,683,344 6,710,405B2 6,710,463 6,727,585 6,759,692 6,771,478B2 7,005,734B2 7,063,975B2 7,071,537 7,157,338B2

**Fig. 1. Output Characteristics @ $T_J = 25^oC$**





**Fig. 2. Extended Output Characteristics @ $T_J = 25^oC$**





**Fig. 3. Output Characteristics @ $T_J = 125^oC$**





**Fig. 4. $R_{DS(on)}$ Normalized to $I_D = 3.5A$ Value vs. Junction Temperature**





**Fig. 5. $R_{DS(on)}$ Normalized to $I_D = 3.5A$ Value vs. Drain Current**






**Fig. 6. Maximum Drain Current vs. Case Temperature**




© 2018 IXYS CORPORATION, All Rights Reserved

**Fig. 7. Input Admittance**





**Fig. 8. Transconductance**





**Fig. 9. Forward Voltage Drop of Intrinsic Diode**





**Fig. 10. Gate Charge**





**Fig. 11. Capacitance**







**Fig. 14. Forward-Bias Safe Operating Area**





IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

**Fig. 13. Maximum Transient Thermal Impedance**




© 2018 IXYS CORPORATION, All Rights Reserved


## TO-263 Outline




**1 - Gate**
**2,4 - Drain**
**3 - Source**

| SYM | INCHES | | MILLIMETER | |
|---|---|---|---|---|
| | MIN | MAX | MIN | MAX |
| A | .170 | .185 | 4.30 | 4.70 |
| A1 | .000 | .008 | 0.00 | 0.20 |
| A2 | .091 | .098 | 2.30 | 2.50 |
| b | .028 | .035 | 0.70 | 0.90 |
| b2 | .046 | .060 | 1.18 | 1.52 |
| C | .018 | .024 | 0.45 | 0.60 |
| C2 | .049 | .060 | 1.25 | 1.52 |
| D | .340 | .370 | 8.63 | 9.40 |
| D1 | .300 | .327 | 7.62 | 8.30 |
| E | .380 | .410 | 9.65 | 10.41 |
| E1 | .270 | .330 | 6.86 | 8.38 |
| e | .100 BSC | | 2.54 BSC | |
| H | .580 | .620 | 14.73 | 15.75 |
| L | .075 | .105 | 1.91 | 2.67 |
| L1 | .039 | .060 | 1.00 | 1.52 |
| L2 | — | .070 | — | 1.77 |
| L3 | .010 BSC | | 0.254 BSC | |


## TO-220 Outline




**1 - Gate**
**2,4 - Drain**
**3 - Source**

| SYM | INCHES | | MILLIMETERS | |
|---|---|---|---|---|
| | MIN | MAX | MIN | MAX |
| A | .169 | .185 | 4.30 | 4.70 |
| A1 | .047 | .055 | 1.20 | 1.40 |
| A2 | .079 | .106 | 2.00 | 2.70 |
| b | .024 | .039 | 0.60 | 1.00 |
| b2 | .045 | .057 | 1.15 | 1.45 |
| c | .014 | .026 | 0.35 | 0.65 |
| D | .587 | .626 | 14.90 | 15.90 |
| D1 | .335 | .370 | 8.50 | 9.40 |
| (D2) | .500 | .531 | 12.70 | 13.50 |
| E | .382 | .406 | 9.70 | 10.30 |
| (E1) | .283 | .323 | 7.20 | 8.20 |
| e | .100 BSC | | 2.54 BSC | |
| e1 | .200 BSC | | 5.08 BSC | |
| H1 | .244 | .268 | 6.20 | 6.80 |
| L | .492 | .547 | 12.50 | 13.90 |
| L1 | .110 | .154 | 2.80 | 3.90 |
| ØP | .134 | .150 | 3.40 | 3.80 |
| Q | .106 | .126 | 2.70 | 3.20 |

## TO-247 Outline




**1 - Gate**
**2,4 - Drain**
**3 - Source**

| SYM | INCHES | | MILLIMETERS | |
|---|---|---|---|---|
| | MIN | MAX | MIN | MAX |
| A | .190 | .205 | 4.83 | 5.21 |
| A1 | .090 | .100 | 2.29 | 2.54 |
| A2 | .075 | .085 | 1.91 | 2.16 |
| b | .045 | .055 | 1.14 | 1.40 |
| b2 | .075 | .087 | 1.91 | 2.20 |
| b4 | .115 | .126 | 2.92 | 3.20 |
| C | .024 | .031 | 0.61 | 0.80 |
| D | .819 | .840 | 20.80 | 21.34 |
| D1 | .650 | .690 | 16.51 | 17.53 |
| D2 | .035 | .050 | 0.89 | 1.27 |
| E | .620 | .635 | 15.75 | 16.13 |
| E1 | .545 | .565 | 13.84 | 14.35 |
| e | .215 BSC | | 5.45 BSC | |
| J | -- | .010 | -- | 0.25 |
| K | -- | .025 | -- | 0.64 |
| L | .780 | .810 | 19.81 | 20.57 |
| L1 | .150 | .170 | 3.81 | 4.32 |
| øP | .140 | .144 | 3.55 | 3.65 |
| øP1 | .275 | .290 | 6.99 | 7.37 |
| Q | .220 | .244 | 5.59 | 6.20 |
| R | .170 | .190 | 4.32 | 4.83 |
| S | .242 BSC | | 6.15 BSC | |

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.




Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.