Date:- 30 Aug, 2019

Data Sheet Issue:- P1

Tentative data

Insulated Gate Bi-Polar Transistor

Type T0140QC33G

Absolute Maximum Ratings

	VOLTAGE RATINGS	MAXIMUM LIMITS	UNITS
V_{CES}	Collector – emitter voltage	3300	V
$V_{DC\ link}$	Permanent DC voltage for 100 FIT failure rate.	1800	V
V_{GES}	Peak gate – emitter voltage	±20	V

	RATINGS	MAXIMUM LIMITS	UNITS
$I_{C(DC)}$	DC collector current, IGBT	140	A
I_{CRM}	Repetitive peak collector current, t_p=1ms, IGBT	280	A
$I_{F(DC)}$	Continuous DC forward current, Diode	140	A
I_{FRM}	Repetitive peak forward current, t_p=1ms, Diode	280	A
I_{FSM}	Peak non-repetitive surge t_p=10ms, V_{RM}=60%V_{RRM}, Diode (Note 4)	880	A
I_{FSM2}	Peak non-repetitive surge t_p=10ms, V_{RM}≤10V, Diode (Note 4)	970	A
P_{MAX}	Maximum power dissipation, IGBT (Note 2)	0.93	kW
P_D	Maximum power dissipation, Diode (Note 2)	0.58	kW
$(di/dt)_{cr}$	Critical diode di/dt (note 3)	350	A/µs
T_j	Operating temperature range.	-40 to +125	°C
T_{stg}	Storage temperature range.	-40 to +125	°C

Notes: -
1) Unless otherwise indicated T_j = 125ºC.
2) T_{sink} = 25°C, double side cooled.
3) Maximum commutation loop inductance 1000nH.
4) Half-sinewave, 125°C T_j initial.

Characteristics

IGBT Characteristics

	PARAMETER	MIN	TYP	MAX	TEST CONDITIONS	UNITS
$V_{CE(sat)}$	Collector – emitter saturation voltage	-	2.64	2.95	I_C = 140A, V_{GE} = 15V, T_j = 25°C	V
		-	3.35	3.70	I_C = 140A, V_{GE} = 15V	V
V_{T0}	Threshold voltage	-	-	1.63	Current range: 47 – 140A	V
r_T	Slope resistance	-	-	14.8		mΩ
$V_{GE(TH)}$	Gate threshold voltage	-	5.2	-	V_{CE} = V_{GE}, I_C = 12mA	V
I_{CES}	Collector – emitter cut-off current		1.5	11	V_{CE} = V_{CES}, V_{GE} = 0V	mA
I_{GES}	Gate leakage current	-	-	±3	V_{GE} = ±20V	µA
C_{ies}	Input capacitance	-	20	-	V_{CE} = 25V, V_{GE} = 0V, f = 1MHz	nF
$t_{d(on)}$	Turn-on delay time	-	1.4	-		µs
t_r(V)	Rise time	-	1.9	-	I_C =140A, V_{CE} =1800V, di/dt=300A/µs	µs
$Q_{g(on)}$	Turn-on gate charge	-	2.7	-	V_{GE} = ±15V, L_s=1.5µH	µC
E_{on}	Turn-on energy	-	0.37	-	$R_{G(ON)}$= 15Ω, $R_{G(OFF)}$=100Ω, C_{GE}=56nF	J
$t_{d(off)}$	Turn-off delay time	-	4.7	-	Integral diode used as freewheel diode	µs
t_f(I)	Fall time	-	1.1	-	(Note 3, 4 & 5)	µs
$Q_{g(off)}$	Turn-off gate charge	-	2.0	-		µC
E_{off}	Turn-off energy	-	0.38	-		J
I_{SC}	Short circuit current	-	550	-	V_{GE}=+15V, V_{CC}=1800V, V_{CEmax}≤V_{CES}, t_p≤10µs	A

Diode Characteristics

	PARAMETER	MIN	TYP	MAX	TEST CONDITIONS	UNITS
V_F	Forward voltage	-	2.65	2.95	I_F = 140A, T_j =25°C	V
		-	3.0	3.3	I_F = 140A	V
V_{To}	Threshold voltage	-	-	1.72	Current range 47 - 140A	V
r_T	Slope resistance	-	-	11.3		mΩ
I_{rm}	Peak reverse recovery current	-	100	-	I_F = 140A, V_{GE} = ±15V, di/dt=300A/µs	A
Q_{rr}	Recovered charge	-	150	-		µC
t_{rr}	Reverse recovery time, 50% chord	-	1.9	-		µs
E_r	Reverse recovery energy	-	0.16	-		J

Thermal Characteristics

	PARAMETER	MIN	TYP	MAX	TEST CONDITIONS	UNITS
R_{thJK}	Thermal resistance junction to sink, IGBT	-	-	108	Double side cooled	K/kW
		-	-	177	Collector side cooled	K/kW
		-	-	279	Emitter side cooled	K/kW
R_{thJK}	Thermal resistance junction to sink, Diode	-	-	172	Double side cooled	K/kW
		-	-	268	Cathode side cooled	K/kW
		-	-	478	Anode side cooled	K/kW
F	Mounting force	4.5	-	6	Note 2	kN
W_t	Weight	-	240	-		g

Notes:-
1) Unless otherwise indicated T_j=125°C.
2) Consult application note 2008AN01 for detailed mounting requirements
3) C_{GE} is additional gate – emitter capacitance added to output of gate drive
4) E_{on} integration time 15µs from 10% rising I_G.
5) E_{off} integration time 15µs from 90% falling V_{GE} .

Curves

Figure 1 – Typical collector-emitter saturation voltage characteristics




Figure 2 – Typical output characteristic




Figure 3 – Typical output characteristic




Figure 4 – Typical turn-on delay time vs gate resistance




Figure 5 – Typical turn-off delay time vs. gate resistance




Figure 6 – Typical turn-on energy vs. collector current




Figure 7 – Typical turn-on energy vs. di/dt




Figure 8 – Typical turn-off energy vs. collector current




Figure 9 – Turn-off energy vs voltage




Figure 10 – Safe operating area (IGBT)




Figure 11 – Typical diode forward characteristics




Figure 12 – Typical recovered charge




Figure 13 – Typical reverse recovery current




Figure 14 – Typical reverse recovery time




Figure 15 – Typical reverse recovery energy




Figure 16 – Safe operating area (Diode)




Figure 17 – Transient thermal impedance (IGBT)






Figure 18 – Transient thermal impedance (Diode)



Outline Drawing & Ordering Information



101A425

ORDERING INFORMATION (Please quote 10 digit code as below)

T0140	QC	33	G
Fixed type Code	Fixed Outline Code	Voltage Grade V_{CES}/100 33	Fixed format code

Typical order code: T0140QC33G (V_{CES} = 3300V)

IXYS Semiconductor GmbH
Edisonstraße 15
D-68623 Lampertheim
Tel: +49 6206 503-0
Fax: +49 6206 503-627
E-mail: marcom@ixys.de

IXYS UK Westcode Ltd
Langley Park Way, Langley Park,
Chippenham, Wiltshire, SN15 1GE.
Tel: +44 (0)1249 444524
E-mail: sales@ixysuk.com

IXYS Corporation
1590 Buckeye Drive
Milpitas CA 95035-7418
Tel: +1 (408) 457 9000
Fax: +1 (408) 496 0670
E-mail: sales@ixys.net

www.littelfuse.com
www.ixysuk.com
www.ixys.net

IXYS Long Beach
IXYS Long Beach, Inc
2500 Mira Mar Ave, Long Beach
CA 90815
Tel: +1 (562) 296 6584
Fax: +1 (562) 296 6585
E-mail: service@ixyslongbeach.com

The information contained herein is confidential and is protected by Copyright. The information may not be used or disclosed except with the written permission of and in the manner permitted by the proprietors IXYS UK Westcode Ltd.

© IXYS UK Westcode Ltd.

In the interest of product improvement, IXYS UK Westcode Ltd reserves the right to change specifications at any time without prior notice.

Devices with a suffix code (2-letter, 3-letter or letter/digit/letter combination) added to their generic code are not necessarily subject to the conditions and limits contained in this report.

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics