TVM SERIES



Description

The TVM Series Provides protection for motors and other sensitive loads. Continuously measures the voltage of each of the three phases using a microcomputer circuit design that senses under and overvoltage, voltage unbalance, phase loss, and phase reversal. Protection is provided even when regenerated voltages are present. Includes a trip delay to prevent nuisance tripping and a restart delay to prevent short cycling after a momentary power outage.

Operation

Upon application of line voltage, the restart delay begins. The output relay is de-energized during restart delay. Under normal conditions, the output energizes after restart delay. Undervoltage, overvoltage, and voltage unbalance must be sensed for continuous trip delay period before the output is de-energized. The output will not de-energize if a fault is corrected during the trip delay. The restart delay begins as soon as the output relay de-energizes. If the restart delay is completed when the fault is corrected, the output relay will energize immediately.


The output relay will not energize if a fault or phase reversal is sensed as 3-phase input voltage is applied.

Reset: Reset is automatic upon correction of a fault.

LED Operation

The LED flashes green during the restart delay, then glows green when the output energizes. It flashes red during the trip delay then glows red when the output de-energizes. It flashes red/green if phase reversal is sensed.

Wiring Diagram



L1 = Phase A
L2 = Phase B
L3 = Phase C
NO = Normally Open
NC = Normally Closed
C = Common, Transfer Contact

Relay contacts are isolated.

F = 2A Fast acting fuses are recommended, but not required

Features & Benefits

FEATURES	BENEFITS
Proprietary microcontroller based circuitry	Constant monitoring to protect against phase loss, phase reversal; over, under, and unbalanced voltage; short cycling
Compact design measures 2 in. (50.8mm) square	Perfect for OEM applications where cost, size and ease of installation are important
LED indication	Provides diagnostics of relay, fault and time delay status
Encapsulated	Protects against shock, vibration and humidity

Ordering Information

MODEL	LINE VOLTAGE	VOLTAGE UNBALANCE	TRIP DELAY	RESTART DELAY
TVM208A100.5S3S	208VAC	10%	0.5s	3s
TVM230A101S1S	230VAC	10%	1s	1s
TVM460A41S5M	460VAC	4%	1s	5m
TVM460A75S2M	460VAC	7%	5s	2m
TVM480A45S5S	480VAC	4%	5s	5s
TVM480A100.5S3S	480VAC	10%	0.5s	3s

If you don't find the part you need, call us for a custom product 800-843-8848

© 2016 Littelfuse Protection Relays & Controls

TVM SERIES

Accessories



LPSM003ZXID (Indicating), LPSM003Z (Non-indicating) Fuse Holders
Littelfuse POWR-SAFE Dead Front holders provide optimum protection to personnel for Class CC and Midget-Style fuses. 600 VAC/DC



0KLK002.T Midget Fuse (2 Amp)
10 x 38 fast acting, high-interrupting capacity, current-limiting type fuse. 600 Vac/500 Vdc



P1015-13 (AWG 10/12), **P1015-64** (AWG 14/16), **P1015-14** (AWG 18/22) **Female Quick Connect**
These 0.25 in. (6.35 mm) female terminals are constructed with an insulator barrel to provide strain relief.



P1023-20 DIN Rail Adapter
Allows module to be mounted on a 35 mm DIN type rail with two #10 screws.



VRM6048 Voltage Reduction Module
Allows the voltage monitor to monitor a 3-phase 550 to 600VAC Line.

Specifications

Line Voltage	
Type	3-phase delta or wye with no connection to neutral
Input Voltage	208 to 480VAC
AC Line Frequency	50 - 100 Hz
Phase Sequence	ABC
Power Consumption	Approx. 2W for 240V units Approx. 3W for 480V units
Overvoltage, Undervoltage, & Voltage Unbalance	
Overvoltage & Undervoltage	Voltage detection with delay trip & automatic reset
Undervoltage Trip Point	88 - 92% of the selected line voltage
Reset Voltage	≅ +3% of trip voltage
Overvoltage Trip Point	109 - 113% of the selected line voltage
Reset Voltage	≅ -3% of trip voltage
Trip Variation vs Temperature	≤ ±2%
Voltage Unbalance	Factory fixed from 4 - 10%
Reset On Balance	≅ -0.7% unbalance
Trip Delay Range	Fixed from 0.2 - 100s ±15% or ±0.1s, whichever is greater
Restart Delay Range	Fixed from 0.5s - 999m ±15% or ±0.2s, whichever is greater
Phase Reversal & Phase Loss Response	≤ 200ms; automatic reset
Phase Loss	≥ 25% unbalance
Output	
Type	Isolated SPDT relay contacts
Rating	
208 to 240VAC (55°C)	10A resistive @ 125VAC, 5A @ 250VAC, 1/4 hp @ 125VAC
380 to 480VAC	10A resistive @ 240VAC, 1/4 hp @ 125VAC, 1/3 hp @ 250VAC, max. voltage 277VAC
Life	Mechanical - 1 x 10^6; Electrical - 1 x 10^5
Protection	
Phase Reversal/Failure	ASME A17.1 Rule 210.6
Motors and Generators	NEMA MG1 14:30, 14:35
Surge	IEEE C62.41-1991 Level B
Dielectric Breakdown	
208 to 240VAC	≥ 1500V RMS input to output terminals
380 to 480VAC	≥ 2500V RMS input to output terminals
Mechanical	
Mounting	Surface mount with one #8 (M5 x 0.8) screw
Dimensions	**H** 50.8 mm (2.0"); **W** 50.8 mm (2.0"); **D** 31.75 mm (1.25")
Termination	0.25 in. (6.35 mm) male quick connect terminals
Environmental	
Operating/Storage Temperature	-40° to 55°C / -40° to 85°C
Humidity	95% relative, non-condensing
Weight	≅ 2.8 oz (79 g)

© 2016 Littelfuse Protection Relays & Controls