
Thyristor Module

3~ Rectifier		Brake Chopper	
V_{RRM} =	1600 V	V_{CES} =	1200 V
I_{DAV} =	240 A	I_{C25} =	180 A
I_{FSM} =	1500 A	$V_{CE(sat)}$ =	1.7 V

3~ Rectifier Bridge, half-controlled (high-side) + Brake Unit


Part number

MCMA240UI1600ED



Backside: isolated

E72873



Features / Advantages:

- Package with DCB ceramic
- Improved temperature and power cycling
- Planar passivated chips
- Very low forward voltage drop
- Very low leakage current
- X2PT - 2nd generation Xtreme light Punch Through
- Rugged X2PT design results in:
  - short circuit rated for 10 µsec.
  - very low gate charge
  - low EMI
  - square RBSOA @ 2x Ic
- Thin wafer technology combined with X2PT design results in a competitive low VCE(sat) and low thermal resistance

Applications:

- 3~ Rectifier with brake unit for drive inverters

Package: E2-Pack

- Isolation Voltage: 3600 V~
- Industry standard outline
- RoHS compliant
- Soldering pins for PCB mounting
- Height: 17 mm
- Base plate: Copper internally DCB isolated
- Advanced power cycling
- Phase Change Material available

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

© 2019 IXYS all rights reserved

Rectifier

Symbol	Definition	Conditions		Ratings min.	typ.	max.	Unit
$V_{RSM/DSM}$	*max. non-repetitive reverse/forward blocking voltage*		T_{VJ} = 25°C			1700	V
$V_{RRM/DRM}$	*max. repetitive reverse/forward blocking voltage*		T_{VJ} = 25°C			1600	V
$I_{R/D}$	*reverse current, drain current*	$V_{R/D}$ = 1600 V	T_{VJ} = 25°C			100	µA
		$V_{R/D}$ = 1600 V	T_{VJ} = 150°C			20	mA
V_T	*forward voltage drop*	I_T = 80 A	T_{VJ} = 25°C			1.27	V
		I_T = 240 A				1.89	V
		I_T = 80 A	T_{VJ} = 125°C			1.26	V
		I_T = 240 A				2.05	V
I_{DAV}	*bridge output current*	T_C = 80°C	T_{VJ} = 150°C			240	A
		rectangular d = 120°					
V_{T0}	*threshold voltage* } *for power loss calculation only*		T_{VJ} = 150°C			0.83	V
r_T	*slope resistance* }					5.3	mΩ
R_{thJC}	*thermal resistance junction to case*					0.4	K/W
R_{thCH}	*thermal resistance case to heatsink*				0.1		K/W
P_{tot}	*total power dissipation*		T_C = 25°C			312	W
I_{TSM}	*max. forward surge current*	t = 10 ms; (50 Hz), sine	T_{VJ} = 45°C			1.50	kA
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			1.62	kA
		t = 10 ms; (50 Hz), sine	T_{VJ} = 150°C			1.28	kA
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			1.38	kA
I^2t	*value for fusing*	t = 10 ms; (50 Hz), sine	T_{VJ} = 45°C			11.3	kA²s
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			10.9	kA²s
		t = 10 ms; (50 Hz), sine	T_{VJ} = 150°C			8.13	kA²s
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			7.87	kA²s
C_J	*junction capacitance*	V_R = 400 V f = 1 MHz	T_{VJ} = 25°C		74		pF
P_{GM}	*max. gate power dissipation*	t_P = 30 µs	T_C = 150°C			10	W
		t_P = 300 µs				5	W
P_{GAV}	*average gate power dissipation*					0.5	W
$(di/dt)_{cr}$	*critical rate of rise of current*	T_{VJ} = 150°C; f = 50 Hz	repetitive, I_T = 240 A			150	A/µs
		t_P = 200 µs; di_G/dt = 0.45 A/µs;					
		I_G = 0.45 A; V = ⅔ V_{DRM}	non-repet., I_T = 80 A			500	A/µs
$(dv/dt)_{cr}$	*critical rate of rise of voltage*	V = ⅔ V_{DRM}	T_{VJ} = 150°C			1000	V/µs
		R_{GK} = ∞; method 1 (linear voltage rise)					
V_{GT}	*gate trigger voltage*	V_D = 6 V	T_{VJ} = 25°C			1.5	V
			T_{VJ} = -40°C			1.6	V
I_{GT}	*gate trigger current*	V_D = 6 V	T_{VJ} = 25°C			95	mA
			T_{VJ} = -40°C			200	mA
V_{GD}	*gate non-trigger voltage*	V_D = ⅔ V_{DRM}	T_{VJ} = 150°C			0.2	V
I_{GD}	*gate non-trigger current*					10	mA
I_L	*latching current*	t_p = 10 µs	T_{VJ} = 25°C			450	mA
		I_G = 0.45 A; di_G/dt = 0.45 A/µs					
I_H	*holding current*	V_D = 6 V R_{GK} = ∞	T_{VJ} = 25°C			200	mA
t_{gd}	*gate controlled delay time*	V_D = ½ V_{DRM}	T_{VJ} = 25°C			2	µs
		I_G = 0.45 A; di_G/dt = 0.45 A/µs					
t_q	*turn-off time*	V_R = 100 V; I_T = 80A; V = ⅔ V_{DRM}	T_{VJ} = 125 °C		150		µs
		di/dt = 10 A/µs dv/dt = 20 V/µs t_p = 200 µs					


© 2019 IXYS all rights reserved

Brake IGBT + Diode				Ratings			
Symbol	**Definition**	**Conditions**		**min.**	**typ.**	**max.**	**Unit**
V_{CES}	*collector emitter voltage*		T_{VJ} = 25°C			1200	V
V_{GES}	*max. DC gate voltage*					±20	V
V_{GEM}	*max. transient gate emitter voltage*					±30	V
I_{C25}	*collector current*		T_C = 25°C			180	A
I_{C80}			T_C = 80°C			140	A
P_{tot}	*total power dissipation*		T_C = 25°C			500	W
$V_{CE(sat)}$	*collector emitter saturation voltage*	I_C = 100 A; V_{GE} = 15 V	T_{VJ} = 25°C		1.7	2.1	V
			T_{VJ} = 125°C		1.9		V
$V_{GE(th)}$	*gate emitter threshold voltage*	I_C = 4 mA; V_{GE} = V_{CE}	T_{VJ} = 25°C	6	6.8	7.5	V
I_{CES}	*collector emitter leakage current*	V_{CE} = V_{CES}; V_{GE} = 0 V	T_{VJ} = 25°C			0.1	mA
			T_{VJ} = 125°C		0.1		mA
I_{GES}	*gate emitter leakage current*	V_{GE} = ±20 V				500	nA
$Q_{G(on)}$	*total gate charge*	V_{CE} = 600 V; V_{GE} = 15 V; I_C = 100 A			340		nC
$t_{d(on)}$	*turn-on delay time*	inductive load V_{CE} = 600 V; I_C = 100 A V_{GE} = ±15 V; R_G = 6.8 Ω	T_{VJ} = 125°C		230		ns
t_r	*current rise time*				70		ns
$t_{d(off)}$	*turn-off delay time*				380		ns
t_f	*current fall time*				230		ns
E_{on}	*turn-on energy per pulse*				12.5		mJ
E_{off}	*turn-off energy per pulse*				11.5		mJ
RBSOA	*reverse bias safe operating area*	V_{GE} = ±15 V; R_G = 6.8 Ω	T_{VJ} = 125°C				
I_{CM}		V_{CEK} = 1200 V				300	A
SCSOA	*short circuit safe operating area*	V_{CEK} = 1200 V					
t_{SC}	*short circuit duration*	V_{CE} = 720 V; V_{GE} = ±15	T_{VJ} = 125°C			10	µs
I_{SC}	*short circuit current*	R_G = 6.8 Ω; non-repetitive			450		A
R_{thJC}	*thermal resistance junction to case*					0.25	K/W
R_{thCH}	*thermal resistance case to heatsink*				0.10		K/W

Brake Diode							
V_{RRM}	*max. repetitive reverse voltage*		T_{VJ} = 25°C			1200	V
I_{F25}	*forward current*		T_C = 25°C			88	A
I_{F80}			T_C = 80°C			59	A
V_F	*forward voltage*	I_F = 60 A	T_{VJ} = 25°C			2.20	V
			T_{VJ} = 125°C		1.95		V
I_R	*reverse current*	V_R = V_{RRM}	T_{VJ} = 25°C			0.1	mA
			T_{VJ} = 125°C			1.2	mA
Q_{rr}	*reverse recovery charge*	V_R = 600 V $-di_F/dt$ = 900 A/µs I_F = 60 A; V_{GE} = 0 V	T_{VJ} = 125°C		9.6		µC
I_{RM}	*max. reverse recovery current*				47		A
t_{rr}	*reverse recovery time*				450		ns
E_{rec}	*reverse recovery energy*				3		mJ
R_{thJC}	*thermal resistance junction to case*					0.6	K/W
R_{thCH}	*thermal resistance case to heatsink*				0.1		K/W

© 2019 IXYS all rights reserved

Package E2-Pack				Ratings			
Symbol	**Definition**	**Conditions**		**min.**	**typ.**	**max.**	**Unit**
I_{RMS}	*RMS current*	per terminal				50	A
T_{VJ}	*virtual junction temperature*			-40		150	°C
T_{op}	*operation temperature*			-40		125	°C
T_{stg}	*storage temperature*			-40		125	°C
Weight					176		g
M_D	*mounting torque*			3		6	Nm
$d_{Spp/App}$	*creepage distance on surface | striking distance through air*		*terminal to terminal*	6.0			mm
$d_{Spb/Apb}$			*terminal to backside*	12.0			mm
V_{ISOL}	*isolation voltage*	t = 1 second	50/60 Hz, RMS; I_{ISOL} ≤ 1 mA	3600			V
		t = 1 minute		3000			V




Part description

M = Module
C = Thyristor (SCR)
M = Thyristor
A = (up to 1800V)
240 = Current Rating [A]
UI = 3~ Rectifier Bridge, half-controlled (high-side) + Brake Unit
1600 = Reverse Voltage [V]
ED = E2-Pack

Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	MCMA240UI1600ED	MCMA240UI1600ED	Box	6	520454


Equivalent Circuits for Simulation ** on die level* T_{VJ} = 150°C



		Thyristor	Brake IGBT +	Brake Diode	
$V_{0\,max}$	*threshold voltage*	0.83	1.2	1.25	V
$R_{0\,max}$	*slope resistance **	2.7	11.6	8.5	mΩ

© 2019 IXYS all rights reserved

Outlines E2-Pack




Bemerkung / ***Note:***

- Nichttolerierte Maße nach / *Measure without tolerances according DIN ISO 2768-T1-m*
- PCB-Lochmuster / *PCB hole pattern:* **see pin position**
- Toleranz Pin-Position und PCB-Lochmuster / *Tolerance of pin position and PCB hole pattern:* ⌖ **0.1**
- Montageanleitung / *Mounting instruction:* www.ixys.com **Application note IXAN0024**

***Detail A*:** PCB-Montage / *Mounting on PCB*

- Empfohlene, selbstschneidende Schraube / *Recommended, self-tapping screw:* **EJOT PT®** (Größe / *size:* **K25**)
- Max. Schraubenlänge / *Max. screw length:* **PCB-Dicke** / **thickness + 6 mm** *(*max. Lochtiefe / *hole depth)*
- Empfohlenes Drehmoment / *Recommended mounting torque:* **1.5 Nm**



© 2019 IXYS all rights reserved

Thyristor




Fig. 1 Forward characteristics




Fig. 2 Surge overload current
I_{TSM}: crest value, t: duration




Fig. 3 I^2t versus time (1-10 s)




Fig. 4 Gate voltage & gate current




Fig. 5 Gate controlled delay time t_{gd}




Fig. 6 Max. forward current at case temperature




Fig. 7a Power dissipation versus direct output current
Fig. 7b and ambient temperature




Fig. 8 Transient thermal impedance junction to case

© 2019 IXYS all rights reserved

Brake IGBT + Diode




Fig.1 Output characteristics IGBT




Fig.2 Typ. output characteristics IGBT




Fig. 3 Typ. transfer charact. IGBT




Fig. 4 Typ. turn-on energy & switch. times vs. collector current




Fig. 5 Typ. turn-off energy & switch. times vs. collector current




Fig. 6 Typ. forward current versus V_F




Fig. 7 Typ. reverse recovery characteristics Diode




Fig. 8 Typ. reverse recovery characteristics Diode




Fig. 9 Transient thermal resistance junction to case

© 2019 IXYS all rights reserved