



## 485 Series Fuse (Not Recommended for Automotive Applications)



### Agency Approvals

| Agency  | Agency File Number | Ampere Rating |
|---|--------------------|---------------|
|  | E10480             | 1A - 3.15A    |
|  | 29862              | 1A - 3.15A    |

### Electrical Characteristics for Series

| % of Ampere Rating | Opening Time at 25°C |
|--------------------|----------------------|
| 100%               | 4 hours, Minimum     |
| 200%               | 60 seconds, Maximum  |

### Description

The 485 Nano<sup>2</sup>® Fuse Series is a small, fast-acting, surface mount ceramic fuse rated at a remarkable 600VDC at its small size and with 100A breaking capacity. It is primarily designed for circuit protection in high energy applications. This product is fully compatible with lead-free solder alloys and higher temperature profiles associated with lead-free assembly.

### Features

- Fast-Acting / Surface mount high fuse for high voltage (up to 600VDC) applications.
- Relatively high breaking capacity at 100A.
- Fully compatible with lead-free solder alloys and higher temperature profiles associated with lead-free assembly.
- RoHS-compliant and Halogen-free
- Ampere Ratings: 1A - 3.15A

### Applications

- PC server and Telecom systems
- LCD TV inverter boards DC input protection
- Uninterruptible Power Supply (UPS) / 3-Phase Power Supplies
- 380VDC server / lighting in data center

### Additional Information



Datasheet





Resources



Samples


### Electrical Specifications by Item

| Ampere Rating (A) | Amp Code | Max Voltage Rating (V) | Interrupting Rating         | Nominal Cold Resistance (Ohms) | Nominal Melting I <sup>2</sup> t (A <sup>2</sup> sec) | Agency Approvals  |   |
|-------------------|----------|------------------------|-----------------------------|--------------------------------|---|---|---|
|                   |          |                        |                             |                                |   |  |  |
| 1.00              | 001.     | 600                    | 100A@600VDC,<br>100A@250VAC | 0.264                          | 0.3044  | X   | X   |
| 1.50              | 01.5     | 600                    |                             | 0.123                          | 0.3917  | X   | X   |
| 2.00              | 002.     | 600                    |                             | 0.0744                         | 0.8962  | X   | X   |
| 2.50              | 02.5     | 600                    |                             | 0.0583                         | 1.4921  | X   | X   |
| 3.15              | 3.15     | 600                    |                             | 0.0395                         | 3.304   | X   | X   |

#### Notes:

1. Cold resistance measured at less than 10% of rated current at 23°C.
2. Agency Approval Table Key: X=Approved or Certified, P=Pending and Blank=Not Approved.
3. I<sup>2</sup>t values stated for 8 msec opening time.


**Temperature Re-rating Curve**



**Note:**


1. Derating depicted in this curve is in addition to the standard derating of 25% for continuous operation.

**Average Time Current Curves**



**Soldering Parameters - Reflow Soldering**

|  |                                    |                         |
|--|------------------------------------|-------------------------|
| <b>Reflow Condition</b>  |                                    | Pb – Free Assembly      |
| <b>Pre Heat</b>  | - Temperature Min ( $T_{s(min)}$ ) | 150°C                   |
|  | - Temperature Max ( $T_{s(max)}$ ) | 200°C                   |
|  | - Time (Min to Max) ( $t_s$ )      | 60 – 180 ses            |
| <b>Average Ramp-up Rate (Liquidus Temp (<math>T_L</math>) to peak)</b> |                                    | 5°C/second max.         |
| <b><math>T_{s(max)}</math> to <math>T_L</math> - Ramp-up Rate</b>      |                                    | 5°C/second max.         |
| <b>Reflow</b>  | - Temperature ( $T_L$ ) (Liquidus) | 217°C                   |
|  | - Temperature ( $t_L$ )            | 60 – 150 seconds        |
| <b>Peak Temperature (<math>T_p</math>)</b>                             |                                    | 260 <sup>+0/-5</sup> °C |
| <b>Time within 5°C of actual peak Temperature (<math>t_p</math>)</b>   |                                    | 20 – 40 seconds         |
| <b>Ramp-down Rate</b>  |                                    | 5°C/second max.         |
| <b>Time 25°C to peak Temperature (<math>T_p</math>)</b>                |                                    | 8 minutes max.          |
| <b>Do not exceed</b>   |                                    | 260°C                   |




### Product Characteristics


|  |   |
|--|---|
| <b>Material</b>                              | Body: Ceramic<br>Cap: Silver Plated Brass                           |
| <b>Product Marking</b>                       | Body: Brand Logo, Current Rating                                    |
| <b>Operating Temperature</b>                 | -55°C to 125°C with proper derating                                 |
| <b>Moisture Sensitivity Level</b>            | Level 1 J-STD-020   |
| <b>Solderability</b>                         | MIL-STD-202, Method 208   |
| <b>Insulation Resistance (after Opening)</b> | MIL-STD-202, Method 302,<br>Test Condition A (10,000 ohms, Minimum) |

|                                     |  |
|-------------------------------------|--|
| <b>Thermal Shock</b>                | MIL-STD-202, Method 107,<br>Test Condition B, 5 cycles, -65°C to 125°C, 15 minutes @ each extreme  |
| <b>Mechanical Shock</b>             | MIL-STD-202, Method 213,<br>Test Condition I: Deenergized. 100G's peak amplitude, sawtooth wave 6ms duration, 3 cycles XYZ+xyz = 18 shocks |
| <b>Vibratio</b>                     | MIL-STD-202, Method 201: 0.03" amplitude, 10-55 Hz in 1 min. 2 hrs. each XYZ=6hrs  |
| <b>Moisture Resistance</b>          | MIL-STD-202, Method 106, 10 cycles   |
| <b>Salt Spray</b>                   | MIL-STD-202, Method 101,<br>Test Condition B (48hrs)   |
| <b>Resistance to Soldering Heat</b> | MIL-STD-202, Method 210,<br>Test Condition B (10 sec at 260°C)   |

### Dimensions



### Part Numbering System



### Packaging

| Packaging Option   | Packaging Specification         | Quantity | Quantity & Option Code |
|--------------------|---------------------------------|----------|------------------------|
| 24mm Tape and Reel | EIA-RS 481-1, (IEC 286, Part 3) | 1500     | DR                     |