IXYS


Advance Technical Information

XPT™ 650V IGBT GenX4™ w/Diode


IXXH40N65C4D1

V_{CES} = 650V
I_{C110} = 40A
$V_{CE(sat)}$ ≤ 2.3V
$t_{fi(typ)}$ = 27ns

Extreme Light Punch Through
IGBT for 5-20 kHz Switching



TO-247



G = Gate C = Collector
E = Emitter Tab = Collector

Symbol	Test Conditions	Maximum Ratings	
V_{CES}	T_J = 25°C to 175°C	650	V
V_{CGR}	T_J = 25°C to 175°C, R_{GE} = 1MΩ	650	V
V_{GES}	Continuous	±20	V
V_{GEM}	Transient	±30	V
I_{C25}	T_C = 25°C	110	A
I_{C110}	T_C = 110°C	40	A
I_{F110}	T_C = 110°C	55	A
I_{CM}	T_C = 25°C, 1ms	215	A
SSOA (RBSOA)	V_{GE} = 15V, T_{VJ} = 150°C, R_G = 5Ω Clamped Inductive Load	I_{CM} = 80 @$V_{CE} \leq V_{CES}$	A
t_{sc} (SCSOA)	V_{GE} = 15V, V_{CE} = 360V, T_J = 150°C R_G = 82Ω, Non Repetitive	10	μs
P_C	T_C = 25°C	455	W
T_J		-55 ... +175	°C
T_{JM}		175	°C
T_{stg}		-55 ... +175	°C
T_L	Maximum Lead Temperature for Soldering	300	°C
T_{SOLD}	1.6 mm (0.062in.) from Case for 10s	260	°C
M_d	Mounting Torque	1.13/10	Nm/lb.in
Weight		6	g

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
BV_{CES}	I_C = 250μA, V_{GE} = 0V	650			V
$V_{GE(th)}$	I_C = 250μA, V_{CE} = V_{GE}	4.0		6.5	V
I_{CES}	V_{CE} = V_{CES}, V_{GE} = 0V			25	μA
	T_J = 150°C			1.5	mA
I_{GES}	V_{CE} = 0V, V_{GE} = ±20V			±100	nA
$V_{CE(sat)}$	I_C = 40A, V_{GE} = 15V, Note 1		1.90	2.30	V
	T_J = 150°C		2.24		V

Features

- Optimized for 5-20kHz Switching
- Square RBSOA
- Anti-Parallel Diode
- Avalanche Rated
- Short Circuit Capability
- International Standard Package

Advantages

- High Power Density
- Extremely Rugged
- Low Gate Drive Requirement

Applications

- Power Inverters
- UPS
- Motor Drives
- SMPS
- PFC Circuits
- Battery Chargers
- Welding Machines
- Lamp Ballasts

© 2017 IXYS CORPORATION, All Rights Reserved

Symbol	Test Conditions (T_J = 25°C Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	I_C = 40A, V_{CE} = 10V, Note 1	14	24		S
C_{ies}	V_{CE} = 25V, V_{GE} = 0V, f = 1MHz		2100		pF
C_{oes}			200		pF
C_{res}			32		pF
$Q_{g(on)}$	I_C = 40A, V_{GE} = 15V, V_{CE} = 0.5 • V_{CES}		68		nC
Q_{ge}			14		nC
Q_{gc}			26		nC
$t_{d(on)}$	**Inductive load, T_J = 25°C**		20		ns
t_{ri}	I_C = 40A, V_{GE} = 15V		62		ns
E_{on}	V_{CE} = 400V, R_G = 5Ω		1.60		mJ
$t_{d(off)}$	Note 2		100		ns
t_{fi}			27		ns
E_{off}			0.42		mJ
$t_{d(on)}$	**Inductive load, T_J = 150°C**		19		ns
t_{ri}	I_C = 40A, V_{GE} = 15V		52		ns
E_{on}	V_{CE} = 400V, R_G = 5Ω		2.75		mJ
$t_{d(off)}$	Note 2		106		ns
t_{fi}			36		ns
E_{off}			0.64		mJ
R_{thJC}				0.33	°C/W
R_{thCS}			0.21		°C/W

Reverse Diode (FRED)

Symbol	Test Conditions (T_J = 25°C Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
V_F	I_F = 30A, V_{GE} = 0V, Note 1			2.6	V
	T_J = 150°C		1.3		V
I_{RM}	I_F = 30A, V_{GE} = 0V, T_J = 150°C		20		A
t_{rr}	$-di_F/dt$ = 500A/µs, V_R = 400V		155		ns
R_{thJC}				0.60	°C/W


Notes:

1. Pulse test, t ≤ 300µs, duty cycle, d ≤ 2%.
2. Switching times & energy losses may increase for higher V_{CE}(clamp), T_J or R_G.

ADVANCE TECHNICAL INFORMATION

The product presented herein is under development. The Technical Specifications offered are derived from a subjective evaluation of the design, based upon prior knowledge and experience, and constitute a "considered reflection" of the anticipated result. IXYS reserves the right to change limits, test conditions, and dimensions without notice.

TO-247 (IXYH) Outline



1 - Gate
2,4 - Collector
3 - Emitter

Dim.	Millimeter min	Millimeter max	Inches min	Inches max
A	4.70	5.30	0.185	0.209
A1	2.21	2.59	0.087	0.102
A2	1.50	2.49	0.059	0.098
b	0.99	1.40	0.039	0.055
b2	1.65	2.39	0.065	0.094
b4	2.59	3.43	0.102	0.135
c	0.38	0.89	0.015	0.035
D	20.79	21.45	0.819	0.845
D1	13.07	-	0.515	-
D2	0.51	1.35	0.020	0.053
E	15.48	16.24	0.610	0.640
E1	13.45	-	0.53	-
E2	4.31	5.48	0.170	0.216
e	5.45 BSC		0.215 BSC	
L	19.80	20.30	0.078	0.800
L1	-	4.49	-	0.177
Ø P	3.55	3.65	0.140	0.144
Ø P1	-	7.39	-	0.290
Q	5.38	6.19	0.212	0.244
S	6.14 BSC		0.242 BSC	

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,860,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2 7,005,734 B2 7,063,975 B2 7,071,537 7,157,338B2

Fig. 1. Output Characteristics @ T_J = 25°C




Fig. 2. Extended Output Characteristics @ T_J = 25°C




Fig. 3. Output Characteristics @ T_J = 150°C




Fig. 4. Dependence of $V_{CE(sat)}$ on Junction Temperature




Fig. 5. Collector-to-Emitter Voltage vs. Gate-to-Emitter Voltage





Fig. 6. Input Admittance



© 2017 IXYS CORPORATION, All Rights Reserved

Fig. 7. Transconductance




Fig. 8. Gate Charge




Fig. 9. Capacitance




Fig. 10. Reverse-Bias Safe Operating Area





Fig. 11. Maximum Transient Thermal Impedance (IGBT)



IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

Fig. 12. Inductive Switching Energy Loss vs. Gate Resistance




Fig. 13. Inductive Switching Energy Loss vs. Collector Current




Fig. 14. Inductive Switching Energy Loss vs. Junction Temperature




Fig. 15. Inductive Turn-off Switching Times vs. Gate Resistance




Fig. 16. Inductive Turn-off Switching Times vs. Collector Current





Fig. 17. Inductive Turn-off Switching Times vs. Junction Temperature



© 2017 IXYS CORPORATION, All Rights Reserved

Fig. 18. Inductive Turn-on Switching Times vs. Gate Resistance




Fig. 19. Inductive Turn-on Switching Times vs. Collector Current




Fig. 20. Inductive Turn-on Switching Times vs. Junction Temperature




Fig. 21. Diode Forward Characteristics




Fig. 22. Reverse Recovery Charge vs. -di$_F$/dt




Fig. 23. Reverse Recovery Current vs. -di$_F$/dt




Fig. 24. Reverse Recovery Time vs. -di$_F$/dt




Fig. 25. Dynamic Parameters Q_{RR}, I_{RR} vs. Junction Temperature





Fig. 26. Maximum Transient Thermal Impedance (Diode)



© 2017 IXYS CORPORATION, All Rights Reserved



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.