preliminary


XPT IGBT

V_{CES} = 1200V
I_{C25} = 84A
$V_{CE(sat)}$ = 1.8V


Single IGBT

Part number

IXA55I1200HJ



Backside: isolated



Features / Advantages:

- Easy paralleling due to the positive temperature coefficient of the on-state voltage
- Rugged XPT design (Xtreme light Punch Through) results in:
  - short circuit rated for 10 µsec.
  - very low gate charge
  - low EMI
  - square RBSOA @ 3x Ic
- Thin wafer technology combined with the XPT design results in a competitive low VCE(sat)

Applications:

- AC motor drives
- Solar inverter
- Medical equipment
- Uninterruptible power supply
- Air-conditioning systems
- Welding equipment
- Switched-mode and resonant-mode power supplies
- Inductive heating, cookers
- Pumps, Fans

Package: ISOPLUS247

- Isolation Voltage: 3600 V~
- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0
- Soldering pins for PCB mounting
- Backside: DCB ceramic
- Reduced weight
- Advanced power cycling

© 2009 IXYS all rights reserved

preliminary


IGBT				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
V_{CES}	*collector emitter voltage*		T_{VJ} = 25°C			1200	V
V_{GES}	*max. DC gate voltage*					±20	V
V_{GEM}	*max. transient gate emitter voltage*					±30	V
I_{C25}	*collector current*		T_C = 25°C			84	A
I_{C80}			T_C = 80°C			54	A
P_{tot}	*total power dissipation*		T_C = 25°C			290	W
$V_{CE(sat)}$	*collector emitter saturation voltage*	I_C = 50A; V_{GE} = 15 V	T_{VJ} = 25°C		1.8	2.1	V
			T_{VJ} = 125°C		2.1		V
$V_{GE(th)}$	*gate emitter threshold voltage*	I_C = 2mA; V_{GE} = V_{CE}	T_{VJ} = 25°C	5.5	6.0	6.5	V
I_{CES}	*collector emitter leakage current*	V_{CE} = V_{CES}; V_{GE} = 0 V	T_{VJ} = 25°C			0.1	mA
			T_{VJ} = 125°C		0.1		mA
I_{GES}	*gate emitter leakage current*	V_{GE} = ±20 V				500	nA
$Q_{G(on)}$	*total gate charge*	V_{CE} = 600 V; V_{GE} = 15 V; I_C = 50 A			190		nC
$t_{d(on)}$	*turn-on delay time*	inductive load V_{CE} = 600 V; I_C = 50 A V_{GE} = ±15 V; R_G = 15 Ω	T_{VJ} = 125°C		70		ns
t_r	*current rise time*				40		ns
$t_{d(off)}$	*turn-off delay time*				250		ns
t_f	*current fall time*				100		ns
E_{on}	*turn-on energy per pulse*				4.5		mJ
E_{off}	*turn-off energy per pulse*				5.5		mJ
RBSOA	*reverse bias safe operating area*	V_{GE} = ±15 V; R_G = 15 Ω	T_{VJ} = 125°C				
I_{CM}		V_{CEmax} = 1200 V				150	A
SCSOA	*short circuit safe operating area*	V_{CEmax} = 900 V					
t_{SC}	*short circuit duration*	V_{CE} = 900 V; V_{GE} = ±15 V	T_{VJ} = 125°C			10	µs
I_{SC}	*short circuit current*	R_G = 15 Ω; non-repetitive			200		A
R_{thJC}	*thermal resistance junction to case*					0.43	K/W
R_{thCH}	*thermal resistance case to heatsink*				0.25		K/W

© 2009 IXYS all rights reserved

preliminary

Package ISOPLUS247				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
I_{RMS}	*RMS current*	per terminal				70	A
T_{VJ}	*virtual junction temperature*			-40		150	°C
T_{op}	*operation temperature*			-40		125	°C
T_{stg}	*storage temperature*			-40		150	°C
Weight					6		g
F_C	*mounting force with clip*			20		120	N
$d_{Spp/App}$	*creepage distance on surface | striking distance through air*		*terminal to terminal*	2.7			mm
$d_{Spb/Apb}$			*terminal to backside*	4.1			mm
V_{ISOL}	*isolation voltage*	t = 1 second	50/60 Hz, RMS; I_{ISOL} ≤ 1 mA	3600			V
		t = 1 minute		3000			V

Product Marking




Part number

I = IGBT
X = XPT IGBT
A = Gen 1 / std
55 = Current Rating [A]
I = Single IGBT
1200 = Reverse Voltage [V]
HJ = ISOPLUS247 (3)

Ordering	Part Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	IXA55I1200HJ	IXA55I1200HJ	Tube	30	508000


Equivalent Circuits for Simulation ** on die level* T_{VJ} = 150 °C



		IGBT	
$V_{0\,max}$	*threshold voltage*	1.1	V
$R_{0\,max}$	*slope resistance **	28	mΩ

© 2009 IXYS all rights reserved


Outlines ISOPLUS247



Dim.	Millimeter		Inches	
	min	max	min	max
A	4.83	5.21	0.190	0.205
A1	2.29	2.54	0.090	0.100
A2	1.91	2.16	0.075	0.085
b	1.14	1.40	0.045	0.055
b2	1.91	2.20	0.075	0.087
b4	2.92	3.24	0.115	0.128
c	0.61	0.83	0.024	0.033
D	20.80	21.34	0.819	0.840
D1	15.75	16.26	0.620	0.640
D2	1.65	2.15	0.065	0.085
D3	20.30	20.70	0.799	0.815
E	15.75	16.13	0.620	0.635
E1	13.21	13.72	0.520	0.540
e	5.45 BSC		0.215 BSC	
L	19.81	20.60	0.780	0.811
L1	3.81	4.38	0.150	0.172
Q	5.59	6.20	0.220	0.244
R	4.25	5.50	0.167	0.217
W	-	0.10	-	0.004

Die konvexe Form des Substrates ist typ. < 0.04 mm über der Kunststoffoberfläche der Bauteilunterseite
The convex bow of substrate is typ. < 0.04 mm over plastic surface level of device bottom side

Die Gehäuseabmessungen entsprechen dem Typ TO-247 AD gemäß JEDEC außer Schraubloch und $L_{max.}$
This drawing will meet all dimensions requiarement of JEDEC outline TO-247 AD except screw hole and except $L_{max.}$



© 2009 IXYS all rights reserved

IGBT




Fig. 1 Typ. output characteristics




Fig. 2 Typ. output characteristics




Fig. 3 Typ. tranfer characteristics




Fig. 4 Typ. turn-on gate charge




Fig. 5 Typ. switching energy vs. collector current




Fig. 6 Typ. switching energy vs. gate resistance

© 2009 IXYS all rights reserved



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.