
IXYS

GenX3™ 600V IGBT with Diode

IXGR72N60C3D1

V_{CES} = 600V
I_{C110} = 35A
$V_{CE(sat)}$ ≤ 2.7V
$t_{fi(typ)}$ = 55ns


High-Speed Low-Vsat PT IGBT
40-100 kHz Switching



Symbol	Test Conditions	Maximum Ratings	
V_{CES}	T_J = 25°C to 150°C	600	V
V_{CGR}	T_J = 25°C to 150°C, R_{GE} = 1MΩ	600	V
V_{GES}	Continuous	±20	V
V_{GEM}	Transient	±30	V
I_{C25}	T_C = 25°C (Limited by Leads)	75	A
I_{C110}	T_C = 110°C	35	A
I_{F110}	T_C = 110°C	36	A
I_{CM}	T_C = 25°C, 1ms	400	A
I_A	T_C = 25°C	50	A
E_{AS}	T_C = 25°C	500	mJ
SSOA (RBSOA)	V_{GE} = 15V, T_{VJ} = 125°C, R_G = 2Ω Clamped Inductive Load	I_{CM} = 150 $V_{CE} \le V_{CES}$	A
P_C	T_C = 25°C	200	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
V_{ISOL}	50/60 Hz, RMS, t = 1Minute I_{ISOL} < 1mA t = 20 Seconds	2500 3000	V~ V~
F_C	Mounting Force	20..120/4.5..27	N/lb
T_L	Maximum Lead Temperature for Soldering	300	°C
T_{SOLD}	1.6mm (0.062 in.) from Case for 10s	260	°C
Weight		5	g

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
$V_{GE(th)}$	I_C = 250μA, V_{CE} = V_{GE}	3.0		5.5	V
I_{CES}	V_{CE} = V_{CES}, V_{GE} = 0V			300	μA
	T_J = 125°C			5	mA
I_{GES}	V_{CE} = 0V, V_{GE} = ±20V			±100	nA
$V_{CE(sat)}$	I_C = 50A, V_{GE} = 15V, Note 1		2.10	2.70	V
	T_J = 125°C		1.65		V

ISOPLUS 247™



G = Gate C = Collector
E = Emitter

Features

- Silicon Chip on Direct-Copper Bond (DCB) Substrate
- Optimized for Low Switching Losses
- Square RBSOA
- Isolated Mounting Surface
- Anti-Parallel Ultra Fast Diode
- Avalanche Rated
- 2500V Electrical Isolation

Advantages

- High Power Density
- Low Gate Drive Requirement


Applications

- High Frequency Power Inverters
- UPS
- Motor Drives
- SMPS
- PFC Circuits
- Battery Chargers
- Welding Machines
- Lamp Ballasts

© 2009 IXYS CORPORATION, All Rights Reserved

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	I_C = 50A, V_{CE} = 10V, Note 1	33	55		S
C_{ies}	V_{CE} = 25V, V_{GE} = 0V, f = 1MHz		4780		pF
C_{oes}			330		pF
C_{res}			117		pF
Q_g	I_C = 50A, V_{GE} = 15V, V_{CE} = 0.5 • V_{CES}		175		nC
Q_{ge}			33		nC
Q_{gc}			72		nC
$t_{d(on)}$	**Inductive Load, T_J = 25°C**		27		ns
t_{ri}			37		ns
E_{on}	I_C = 50A, V_{GE} = 15V		1.03		mJ
$t_{d(off)}$	V_{CE} = 480V, R_G = 2Ω, Note 2		77	130	ns
t_{fi}			55	110	ns
E_{off}			0.48	0.95	mJ
$t_{d(on)}$	**Inductive Load, T_J =1 25°C**		26		ns
t_{ri}			36		ns
E_{on}	I_C = 50A, V_{GE} = 15V		1.48		mJ
$t_{d(off)}$	V_{CE} = 480V, R_G = 2Ω, Note 2		120		ns
t_{fi}			124		ns
E_{off}			0.93		mJ
R_{thJC}				0.62	°C/W
R_{thCS}			0.15		°C/W

ISOPLUS247 (IXGR) Outline



SYM	INCHES MIN	INCHES MAX	MILLIMETERS MIN	MILLIMETERS MAX
A	.190	.205	4.83	5.21
A1	.090	.100	2.29	2.54
A2	.075	.085	1.91	2.16
b	.045	.055	1.14	1.40
b1	.075	.084	1.91	2.13
b2	.115	.123	2.92	3.12
C	.024	.031	0.61	0.80
D	.819	.840	20.80	21.34
E	.620	.635	15.75	16.13
e	.215 BSC		5.45 BSC	
L	.780	.800	19.81	20.32
L1	.150	.170	3.81	4.32
Q	.220	.244	5.59	6.20
R	.170	.190	4.32	4.83
S	.520	.540	13.21	13.72
T	.620	.640	15.75	16.26
U	.065	.080	1.65	2.03

1 – GATE
2 – DRAIN (COLLECTOR)
3 – SOURCE (EMITTER)
4 – NO CONNECTION

NOTE: This drawing will meet all dimensions requirement of JEDEC outline TO-247AD except screw hole.

Reverse Diode (FRED)

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
V_F	I_F = 60A, V_{GE} = 0V, Note 1			2.5	V
	T_J = 150°C		1.4		V
I_{RM}	I_F = 60A, V_{GE} = 0V, T_J = 100°C		8.3		A
	$-di_F/dt$ = 100A/µs, V_R = 100V				
t_{rr}	I_F = 1A, -di/dt = 200A/µs, V_R = 30V		35		ns
R_{thJC}				0.85	°C/W

Notes:

1. Pulse test, t ≤ 300µs, duty cycle, d ≤ 2%.
2. Switching times & energy losses may increase for higher V_{CE}(Clamp), T_J or R_G.

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or moreof the following U.S. patents: 4,835,592 4,850,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2 7,005,734 B2 7,063,975 B2 7,071,537 7,157,338B2

Fig. 1. Output Characteristics @ T_J = 25ºC




Fig. 2. Extended Output Characteristics @ T_J = 25ºC




Fig. 3. Output Characteristics @ T_J = 125ºC




Fig. 4. Dependence of $V_{CE(sat)}$ on JunctionTemperature




Fig. 5. Collector-to-Emitter Voltage vs. Gate-to-Emitter Voltage





Fig. 6. Input Admittance



© 2009 IXYS CORPORATION, All Rights Reserved

Fig. 7. Transconductance




Fig. 8. Gate Charge




Fig. 9. Capacitance




Fig. 10. Reverse-Bias Safe Operating Area





Fig. 11. Maximum Transient Thermal Impedance



IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

Fig. 12. Inductive Switching Energy Loss vs. Gate Resistance




Fig. 13. Inductive Switching Energy Loss vs. Collector Current




Fig. 14. Inductive Switching Energy Loss vs. Junction Temperature




Fig. 15. Inductive Turn-off Switching Times vs. Gate Resistance




Fig. 16. Inductive Turn-off Switching Times vs. Collector Current





Fig. 17. Inductive Turn-off Switching Times vs. Junction Temperature



© 2009 IXYS CORPORATION, All Rights Reserved

Fig. 18. Inductive Turn-on Switching Times vs. Gate Resistance




Fig. 19. Inductive Turn-on Switching Times vs. Collector Current





Fig. 20. Inductive Turn-on Switching Times vs. Junction Temperature






Fig. 21. Forward Current I_F Versus V_F




Fig. 22. Reverse Recorvery Charge Q_r Versus $-di_F/dt$




Fig. 23. Peak ReverseCurrent I_{RM} Versus $-di_F/dt$




Fig. 24. Dynamic paraments Q_r, I_{RM} Versus T_{VJ}




Fig. 25. Recorvery Time t_{rr} Versus $-di_F/dt$




Fig. 26. Peak Forward Voltage V_{RM} and t_{rr} Versus $-di_F/dt$




Fig. 27. Maximum Transient Thermal Impedance (for diode)

© 2009 IXYS CORPORATION, All Rights Reserved



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.