


## PolarP™ Power MOSFET


## IXTR32P60P

P-Channel Enhancement Mode  
Avalanche Rated



$$\begin{aligned} V_{DSS} &= -600V \\ I_{D25} &= -18A \\ R_{DS(on)} &\leq 385m\Omega \end{aligned}$$

ISOPLUS247  
E153432



G = Gate      D = Drain  
S = Source

| Symbol     | Test Conditions                                                          | Maximum Ratings |                  |
|------------|--------------------------------------------------------------------------|-----------------|------------------|
| $V_{DSS}$  | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$                          | - 600           | V                |
| $V_{DGR}$  | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$ , $R_{GS} = 1M\Omega$    | - 600           | V                |
| $V_{GSS}$  | Continuous                                                               | $\pm 20$        | V                |
| $V_{GSM}$  | Transient                                                                | $\pm 30$        | V                |
| $I_{D25}$  | $T_C = 25^\circ\text{C}$                                                 | - 18            | A                |
| $I_{DM}$   | $T_C = 25^\circ\text{C}$ , Pulse Width Limited by $T_{JM}$               | - 96            | A                |
| $I_A$      | $T_C = 25^\circ\text{C}$                                                 | - 32            | A                |
| $E_{AS}$   | $T_C = 25^\circ\text{C}$                                                 | 3.5             | J                |
| $dv/dt$    | $I_S \leq I_{DM}$ , $V_{DD} \leq V_{DSS}$ , $T_J \leq 150^\circ\text{C}$ | 10              | V/ns             |
| $P_D$      | $T_C = 25^\circ\text{C}$                                                 | 310             | W                |
| $T_J$      |                                                                          | -55 ... +150    | $^\circ\text{C}$ |
| $T_{JM}$   |                                                                          | 150             | $^\circ\text{C}$ |
| $T_{stg}$  |                                                                          | -55 ... +150    | $^\circ\text{C}$ |
| $T_L$      | 1.6mm (0.062 in.) from Case for 10s                                      | 300             | $^\circ\text{C}$ |
| $T_{SOLD}$ | Plastic Body for 10s                                                     | 260             | $^\circ\text{C}$ |
| $V_{ISOL}$ | 50/60 Hz, 1 Minute                                                       | 2500            | V~               |
| $M_d$      | Mounting Force                                                           | 20..120/4.5..27 | N/lb.            |
| Weight     |                                                                          | 5               | g                |

### Features

- Silicon Chip on Direct-Copper Bond (DCB) Substrate
  - UL Recognized Package
  - Isolated Mounting Surface
  - 2500V~ Electrical Isolation
- Avalanche Rated
- The Rugged PolarP™ Process
- Low  $Q_g$
- Low Drain-to-Tab Capacitance
- Low Package Inductance

### Advantages

- Easy to Mount
- Space Savings
- High Power Density

### Applications

- High-Side Switches
- Push Pull Amplifiers
- DC Choppers
- Automatic Test Equipment
- Current Regulators

| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified) | Characteristic Values |      |                               |
|--------------|-----------------------------------------------------------------------------|-----------------------|------|-------------------------------|
|              |                                                                             | Min.                  | Typ. | Max.                          |
| $BV_{DSS}$   | $V_{GS} = 0V$ , $I_D = -250\mu A$                                           | - 600                 |      | V                             |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = -1mA$                                            | - 2.0                 |      | - 4.0 V                       |
| $I_{GSS}$    | $V_{GS} = \pm 20V$ , $V_{DS} = 0V$                                          |                       |      | $\pm 100$ nA                  |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$ , $V_{GS} = 0V$<br>$T_J = 125^\circ\text{C}$             |                       |      | - 50 $\mu A$<br>- 250 $\mu A$ |
| $R_{DS(on)}$ | $V_{GS} = -10V$ , $I_D = -16A$ , Note 1                                     |                       |      | 385 m $\Omega$                |


| Symbol       | Test Conditions<br>( $T_J = 25^{\circ}\text{C}$ , Unless Otherwise Specified)                                                                 | Characteristic Values |      |                           |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|------|---------------------------|
|              |                                                                                                                                               | Min.                  | Typ. | Max.                      |
| $g_{fs}$     | $V_{DS} = -10\text{V}$ , $I_D = -16\text{A}$ , Note 1                                                                                         | 21                    | 32   | S                         |
| $C_{iss}$    | $V_{GS} = 0\text{V}$ , $V_{DS} = -25\text{V}$ , $f = 1\text{MHz}$                                                                             |                       | 11.1 | nF                        |
| $C_{oss}$    |                                                                                                                                               |                       | 925  | pF                        |
| $C_{rss}$    |                                                                                                                                               |                       | 77   | pF                        |
| $t_{d(on)}$  | <b>Resistive Switching Times</b><br>$V_{GS} = -10\text{V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = -16\text{A}$<br>$R_G = 1\Omega$ (External) |                       | 37   | ns                        |
| $t_r$        |                                                                                                                                               |                       | 27   | ns                        |
| $t_{d(off)}$ |                                                                                                                                               |                       | 95   | ns                        |
| $t_f$        |                                                                                                                                               |                       | 33   | ns                        |
| $Q_{g(on)}$  | $V_{GS} = -10\text{V}$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_D = -16\text{A}$                                                                   |                       | 196  | nC                        |
| $Q_{gs}$     |                                                                                                                                               |                       | 54   | nC                        |
| $Q_{gd}$     |                                                                                                                                               |                       | 58   | nC                        |
| $R_{thJC}$   |                                                                                                                                               |                       |      | 0.40 $^{\circ}\text{C/W}$ |
| $R_{thCS}$   |                                                                                                                                               |                       | 0.15 | $^{\circ}\text{C/W}$      |

## Source-Drain Diode

| Symbol   | Test Conditions<br>( $T_J = 25^{\circ}\text{C}$ , Unless Otherwise Specified)                            | Characteristic Values |        |               |
|----------|----------------------------------------------------------------------------------------------------------|-----------------------|--------|---------------|
|          |                                                                                                          | Min.                  | Typ.   | Max.          |
| $I_S$    | $V_{GS} = 0\text{V}$                                                                                     |                       |        | - 32 A        |
| $I_{SM}$ | Repetitive, Pulse Width Limited by $T_{JM}$                                                              |                       |        | - 128 A       |
| $V_{SD}$ | $I_F = -16\text{A}$ , $V_{GS} = 0\text{V}$ , Note 1                                                      |                       |        | - 2.8 V       |
| $t_{rr}$ | $I_F = -16\text{A}$ , $-di/dt = -150\text{A}/\mu\text{s}$<br>$V_R = -100\text{V}$ , $V_{GS} = 0\text{V}$ |                       | 480    | ns            |
| $Q_{RM}$ |                                                                                                          |                       | 11.4   | $\mu\text{C}$ |
| $I_{RM}$ |                                                                                                          |                       | - 47.6 | A             |

Note 1: Pulse test,  $t \leq 300\mu\text{s}$ , duty cycle,  $d \leq 2\%$ .

## ISOPLUS247 (IXTR) Outline









1 - Gate  
2,4 - Drain  
3 - Source


| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .190     | .205 | 4.83        | 5.21  |
| A1  | .090     | .100 | 2.29        | 2.54  |
| A2  | .075     | .085 | 1.91        | 2.16  |
| b   | .045     | .055 | 1.14        | 1.40  |
| b1  | .075     | .084 | 1.91        | 2.13  |
| b2  | .115     | .123 | 2.92        | 3.12  |
| C   | .024     | .031 | 0.61        | 0.80  |
| D   | .819     | .840 | 20.80       | 21.34 |
| E   | .620     | .635 | 15.75       | 16.13 |
| e   | .215 BSC |      | 5.45 BSC    |       |
| L   | .780     | .800 | 19.81       | 20.32 |
| L1  | .150     | .170 | 3.81        | 4.32  |
| Q   | .220     | .244 | 5.59        | 6.20  |
| R   | .170     | .190 | 4.32        | 4.83  |
| S   | .520     | .540 | 13.21       | 13.72 |
| T   | .620     | .640 | 15.75       | 16.26 |
| U   | .065     | .080 | 1.65        | 2.03  |

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.


|                                                                                  |           |           |           |           |              |              |              |              |              |             |
|----------------------------------------------------------------------------------|-----------|-----------|-----------|-----------|--------------|--------------|--------------|--------------|--------------|-------------|
| IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: | 4,835,592 | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665    | 6,404,065 B1 | 6,683,344    | 6,727,585    | 7,005,734 B2 | 7,157,338B2 |
|                                                                                  | 4,860,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123 B1 | 6,534,343    | 6,710,405 B2 | 6,759,692    | 7,063,975 B2 |             |
|                                                                                  | 4,881,106 | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728 B1 | 6,583,505    | 6,710,463    | 6,771,478 B2 | 7,071,537    |             |

**Fig. 1. Output Characteristics @  $T_J = 25^\circ\text{C}$** 

**Fig. 2. Extended Output Characteristics @  $T_J = 25^\circ\text{C}$** 

**Fig. 3. Output Characteristics @  $T_J = 125^\circ\text{C}$** 

**Fig. 4.  $R_{DS(on)}$  Normalized to  $I_D = -16\text{A}$  Value vs. Junction Temperature**

**Fig. 5.  $R_{DS(on)}$  Normalized to  $I_D = -16\text{A}$  Value vs. Drain Current**

**Fig. 6. Maximum Drain Current vs. Case Temperature**



**Fig. 7. Input Admittance**




**Fig. 8. Transconductance**




**Fig. 9. Forward Voltage Drop of Intrinsic Diode**



**Fig. 10. Gate Charge**



**Fig. 11. Capacitance**



**Fig. 12. Forward-Bias Safe Operating Area**





Fig. 13. Maximum Transient Thermal Impedance





---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).