


# 1200V XPT™ IGBT GenX3™

## IXYH40N120C3


High-Speed IGBT  
for 20-50 kHz Switching



$$\begin{aligned} V_{CES} &= 1200V \\ I_{C110} &= 40A \\ V_{CE(sat)} &\leq 3.5V \\ t_{fi(typ)} &= 50ns \end{aligned}$$

| Symbol                        | Test Conditions                                                                            | Maximum Ratings                          |                  |
|-------------------------------|--------------------------------------------------------------------------------------------|------------------------------------------|------------------|
| $V_{CES}$                     | $T_J = 25^\circ\text{C}$ to $175^\circ\text{C}$                                            | 1200                                     | V                |
| $V_{CGR}$                     | $T_J = 25^\circ\text{C}$ to $175^\circ\text{C}$ , $R_{GE} = 1M\Omega$                      | 1200                                     | V                |
| $V_{GES}$                     | Continuous                                                                                 | $\pm 20$                                 | V                |
| $V_{GEM}$                     | Transient                                                                                  | $\pm 30$                                 | V                |
| $I_{C25}$                     | $T_C = 25^\circ\text{C}$ (Chip Capability)                                                 | 90                                       | A                |
| $I_{C110}$                    | $T_C = 110^\circ\text{C}$                                                                  | 40                                       | A                |
| $I_{CM}$                      | $T_C = 25^\circ\text{C}$ , 1ms                                                             | 175                                      | A                |
| $I_A$                         | $T_C = 25^\circ\text{C}$                                                                   | 20                                       | A                |
| $E_{AS}$                      | $T_C = 25^\circ\text{C}$                                                                   | 400                                      | mJ               |
| <b>SSOA</b><br><b>(RBSOA)</b> | $V_{GE} = 15V$ , $T_{VJ} = 150^\circ\text{C}$ , $R_G = 10\Omega$<br>Clamped Inductive Load | $I_{CM} = 80$<br>@ $V_{CE} \leq V_{CES}$ | A                |
| $P_C$                         | $T_C = 25^\circ\text{C}$                                                                   | 577                                      | W                |
| $T_J$                         |                                                                                            | -55 ... +175                             | $^\circ\text{C}$ |
| $T_{JM}$                      |                                                                                            | 175                                      | $^\circ\text{C}$ |
| $T_{stg}$                     |                                                                                            | -55 ... +175                             | $^\circ\text{C}$ |
| $T_L$                         | Maximum Lead Temperature for Soldering                                                     | 300                                      | $^\circ\text{C}$ |
| $T_{SOLD}$                    | 1.6 mm (0.062in.) from Case for 10s                                                        | 260                                      | $^\circ\text{C}$ |
| $M_d$                         | Mounting Torque                                                                            | 1.13/10                                  | Nm/lb.in.        |
| <b>Weight</b>                 |                                                                                            | 6                                        | g                |

### TO-247 AD



G = Gate      C = Collector  
E = Emitter    Tab = Collector

### Features

- Optimized for Low Switching Losses
- Square RBSOA
- Positive Thermal Coefficient of  $V_{ce(sat)}$
- Avalanche Rated
- High Current Handling Capability
- International Standard Package

### Advantages

- High Power Density
- Low Gate Drive Requirement

### Applications

- High Frequency Power Inverters
- UPS
- Motor Drives
- SMPS
- PFC Circuits
- Battery Chargers
- Welding Machines
- Lamp Ballasts

| Symbol        | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified) | Characteristic Values |            |                                       |
|---------------|-----------------------------------------------------------------------------|-----------------------|------------|---------------------------------------|
|               |                                                                             | Min.                  | Typ.       | Max.                                  |
| $BV_{CES}$    | $I_C = 250\mu\text{A}$ , $V_{GE} = 0V$                                      | 1200                  |            | V                                     |
| $V_{GE(th)}$  | $I_C = 250\mu\text{A}$ , $V_{CE} = V_{GE}$                                  | 3.0                   |            | 5.0 V                                 |
| $I_{CES}$     | $V_{CE} = V_{CES}$ , $V_{GE} = 0V$<br>$T_J = 150^\circ\text{C}$             |                       |            | 10 $\mu\text{A}$<br>750 $\mu\text{A}$ |
| $I_{GES}$     | $V_{CE} = 0V$ , $V_{GE} = \pm 20V$                                          |                       |            | $\pm 100$ nA                          |
| $V_{CE(sat)}$ | $I_C = 40A$ , $V_{GE} = 15V$ , Note 1<br>$T_J = 150^\circ\text{C}$          |                       | 2.9<br>3.7 | 3.5 V<br>V                            |

## Symbol Test Conditions

( $T_J = 25^\circ\text{C}$  Unless Otherwise Specified)


## Characteristic Values

|              |                                                                                                                                                                  | Min. | Typ. | Max.                    |
|--------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|------|-------------------------|
| $g_{fs}$     | $I_C = 40\text{A}, V_{CE} = 10\text{V}$ , Note 1                                                                                                                 | 11   | 18   | S                       |
| $C_{ies}$    | $V_{CE} = 25\text{V}, V_{GE} = 0\text{V}, f = 1\text{MHz}$                                                                                                       |      | 1870 | pF                      |
| $C_{oes}$    |                                                                                                                                                                  |      | 107  | pF                      |
| $C_{res}$    |                                                                                                                                                                  |      | 38   | pF                      |
| $Q_{g(on)}$  | $I_C = 40\text{A}, V_{GE} = 15\text{V}, V_{CE} = 0.5 \cdot V_{CES}$                                                                                              |      | 80   | nC                      |
| $Q_{ge}$     |                                                                                                                                                                  |      | 14   | nC                      |
| $Q_{gc}$     |                                                                                                                                                                  |      | 37   | nC                      |
| $t_{d(on)}$  | <b>Inductive load, <math>T_J = 25^\circ\text{C}</math></b><br>$I_C = 40\text{A}, V_{GE} = 15\text{V}$<br>$V_{CE} = 0.5 \cdot V_{CES}, R_G = 10\Omega$<br>Note 2  |      | 18   | ns                      |
| $t_{ri}$     |                                                                                                                                                                  |      | 64   | ns                      |
| $E_{on}$     |                                                                                                                                                                  |      | 3.8  | mJ                      |
| $t_{d(off)}$ |                                                                                                                                                                  |      | 133  | ns                      |
| $t_{fi}$     |                                                                                                                                                                  |      | 50   | ns                      |
| $E_{off}$    |                                                                                                                                                                  |      | 1.1  | mJ                      |
| $t_{d(on)}$  | <b>Inductive load, <math>T_J = 150^\circ\text{C}</math></b><br>$I_C = 40\text{A}, V_{GE} = 15\text{V}$<br>$V_{CE} = 0.5 \cdot V_{CES}, R_G = 10\Omega$<br>Note 2 |      | 22   | ns                      |
| $t_{ri}$     |                                                                                                                                                                  |      | 73   | ns                      |
| $E_{on}$     |                                                                                                                                                                  |      | 6.6  | mJ                      |
| $t_{d(off)}$ |                                                                                                                                                                  |      | 160  | ns                      |
| $t_{fi}$     |                                                                                                                                                                  |      | 143  | ns                      |
| $E_{off}$    |                                                                                                                                                                  |      | 2.1  | mJ                      |
| $R_{thJC}$   |                                                                                                                                                                  |      |      | 0.26 $^\circ\text{C/W}$ |
| $R_{thCS}$   |                                                                                                                                                                  |      | 0.21 | $^\circ\text{C/W}$      |

## Notes:

1. Pulse test,  $t \leq 300\mu\text{s}$ , duty cycle,  $d \leq 2\%$ .
2. Switching times & energy losses may increase for higher  $V_{CE}(\text{clamp})$ ,  $T_J$  or  $R_G$ .







## TO-247 (IXYH) Outline




| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .190     | .205 | 4.83        | 5.21  |
| A1  | .090     | .100 | 2.29        | 2.54  |
| A2  | .075     | .085 | 1.91        | 2.16  |
| b   | .045     | .055 | 1.14        | 1.40  |
| b2  | .075     | .087 | 1.91        | 2.20  |
| b4  | .115     | .126 | 2.92        | 3.20  |
| C   | .024     | .031 | 0.61        | 0.80  |
| D   | .819     | .840 | 20.80       | 21.34 |
| D1  | .650     | .690 | 16.51       | 17.53 |
| D2  | .035     | .050 | 0.89        | 1.27  |
| E   | .620     | .635 | 15.75       | 16.13 |
| E1  | .545     | .565 | 13.84       | 14.35 |
| e   | .215 BSC |      | 5.45 BSC    |       |
| J   | --       | .010 | --          | 0.25  |
| K   | --       | .025 | --          | 0.64  |
| L   | .780     | .810 | 19.81       | 20.57 |
| L1  | .150     | .170 | 3.81        | 4.32  |
| ØP  | .140     | .144 | 3.55        | 3.65  |
| ØP1 | .275     | .290 | 6.99        | 7.37  |
| Q   | .220     | .244 | 5.59        | 6.20  |
| R   | .170     | .190 | 4.32        | 4.83  |
| S   | .242 BSC |      | 6.15 BSC    |       |

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.


|                                                                                  |           |           |           |           |              |              |              |              |              |             |
|----------------------------------------------------------------------------------|-----------|-----------|-----------|-----------|--------------|--------------|--------------|--------------|--------------|-------------|
| IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: | 4,835,592 | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665    | 6,404,065 B1 | 6,683,344    | 6,727,585    | 7,005,734 B2 | 7,157,338B2 |
|                                                                                  | 4,860,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123 B1 | 6,534,343    | 6,710,405 B2 | 6,759,692    | 7,063,975 B2 |             |
|                                                                                  | 4,881,106 | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728 B1 | 6,583,505    | 6,710,463    | 6,771,478 B2 | 7,071,537    |             |

**Fig. 1. Output Characteristics @  $T_J = 25^\circ\text{C}$** 

**Fig. 2. Extended Output Characteristics @  $T_J = 25^\circ\text{C}$** 

**Fig. 3. Output Characteristics @  $T_J = 150^\circ\text{C}$** 

**Fig. 4. Dependence of  $V_{CE(sat)}$  on Junction Temperature**

**Fig. 5. Collector-to-Emitter Voltage vs. Gate-to-Emitter Voltage**

**Fig. 6. Input Admittance**



**Fig. 7. Transconductance**




**Fig. 8. Gate Charge**




**Fig. 9. Capacitance**









**Fig. 10. Reverse-Bias Safe Operating Area**




**Fig. 11. Maximum Transient Thermal Impedance**




**Fig. 12. Inductive Switching Energy Loss vs. Gate Resistance**

**Fig. 13. Inductive Switching Energy Loss vs. Collector Current**

**Fig. 14. Inductive Switching Energy Loss vs. Junction Temperature**

**Fig. 15. Inductive Turn-off Switching Times vs. Gate Resistance**

**Fig. 16. Inductive Turn-off Switching Times vs. Collector Current**

**Fig. 17. Inductive Turn-off Switching Times vs. Junction Temperature**



**Fig. 18. Inductive Turn-on Switching Times vs. Gate Resistance**



**Fig. 19. Inductive Turn-on Switching Times vs. Collector Current**



**Fig. 20. Inductive Turn-on Switching Times vs. Junction Temperature**





---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).