
IXYS

PolarHV™ HiPerFET Power MOSFET

N-Channel Enhancement Mode
Avalanche Rated
Fast Intrinsic Diode


IXFH 20N80P
IXFT 20N80P
IXFV 20N80P
IXFV 20N80PS

V_{DSS} = 800 V
I_{D25} = 20 A
$R_{DS(on)}$ ≤ 520 mΩ
t_{rr} ≤ 250 ns




Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 150°C	800	V
V_{DGR}	T_J = 25°C to 150°C; R_{GS} = 1 MΩ	800	V
V_{GSS}	Continuous	± 30	V
V_{GSM}	Transient	± 40	V
I_{D25}	T_C = 25°C	20	A
I_{DM}	T_C = 25°C, pulse width limited by T_{JM}	50	A
I_{AR}	T_C = 25°C	10	A
E_{AR}	T_C = 25°C	30	mJ
E_{AS}	T_C = 25°C	1.0	J
dv/dt	$I_S \le I_{DM}$, di/dt ≤100 A/μs, $V_{DD} \le V_{DSS}$, T_J ≤150°C, R_G = 4 Ω	10	V/ns
P_D	T_C = 25°C	500	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
T_L	Maximum lead temperature for soldering	300	°C
T_{SOLD}	Plastic case for 10 s	260	°C
M_d	Mounting torque (TO-247)	1.13/10	Nm/lb.in.
F_C	Mounting force (PLUS220)	1..65 / 2.5..15	N/lb
Weight	TO-247	6	g
	TO-268	5.5	g
	PLUS220 types	4	g


TO-247 (IXFH)




TO-268 (IXFT)



PLUS220 (IXFV)



PLUS220 SMD(IXFV..S)



G = Gate D = Drain
S = Source Tab = Drain

Symbol (T_J = 25°C, unless otherwise specified)	Test Conditions	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0 V, I_D = 250 μA	800			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 4 mA	3.0		5.0	V
I_{GSS}	V_{GS} = ±30 V_{DC}, V_{DS} = 0			± 200	nA
I_{DSS}	$V_{DS} = V_{DSS}$, V_{GS} = 0 V			25	μA
	T_J = 125°C			1000	μA
$R_{DS(on)}$	V_{GS} = 10 V, I_D = 10 A, Pulse test, t ≤300 μs, duty cycle d ≤ 2 %			520	mΩ

Features

- International standard packages
- Fast recovery diode
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
  - easy to drive and to protect

Advantages

- Easy to mount
- Space savings
- High power density

DS99511E(03/06)

© 2006 IXYS All rights reserved

Symbol	Test Conditions (T_J = 25°C unless otherwise specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	V_{DS} = 20 V; I_D = 10 A, pulse test	14	23		S
C_{iss}	V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz		4685		pF
C_{oss}			356		pF
C_{rss}			26		pF
$t_{d(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 V_{DSS}, I_D = 10 A R_G = 2 Ω (External)		30		ns
t_r			24		ns
$t_{d(off)}$			85		ns
t_f			24		ns
$Q_{g(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 V_{DSS}, I_D = 10 A		86		nC
Q_{gs}			27		nC
Q_{gd}			24		nC
R_{thJC}				0.25	°C/W
R_{thCS}	(TO-247, PLUS220)		0.21		°C/W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C unless otherwise specified)	Characteristic Values Min.	Typ.	Max.	
I_S	V_{GS} = 0 V			20	A
I_{SM}	Repetitive			50	A
V_{SD}	$I_F = I_S$, V_{GS} = 0 V, Pulse test, t ≤ 300 µs, duty cycle d ≤ 2 %			1.5	V
t_{rr}	I_F = 25A, -di/dt = 100 A/µs			250	ns
Q_{RM}	V_R = 100V; V_{GS} = 0 V		0.8		µC
I_{RM}			6.0		A

IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,850,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2

Fig. 1. Output Characteristics @ 25°C




Fig. 2. Extended Output Characteristics @ 25°C




Fig. 3. Output Characteristics @ 125°C




Fig. 4. $R_{DS(on)}$ Normalized to I_D = 10A Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to I_D = 10A Value vs. Drain Current





Fig. 6. Drain Current vs. Case Temperature



© 2006 IXYS All rights reserved

Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Source Current vs. Source-To-Drain Voltage




Fig. 10. Gate Charge




Fig. 11. Capacitance






Fig. 12. Maximum Transient Thermal Resistance



IXYS reserves the right to change limits, test conditions, and dimensions.


Package Outline Drawings

TO-247AD (IXFH) Outline




Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.7	5.3	.185	.209
A_1	2.2	2.54	.087	.102
A_2	2.2	2.6	.059	.098
b	1.0	1.4	.040	.055
b_1	1.65	2.13	.065	.084
b_2	2.87	3.12	.113	.123
C	.4	.8	.016	.031
D	20.80	21.46	.819	.845
E	15.75	16.26	.610	.640
e	5.20	5.72	0.205	0.225
L	19.81	20.32	.780	.800
L1		4.50		.177
ØP	3.55	3.65	.140	.144
Q	5.89	6.40	0.232	0.252
R	4.32	5.49	.170	.216
S	6.15 BSC		242 BSC	

TO-268 (IXFT) Outline



SYM	INCHES MIN	MAX	MILLIMETERS MIN	MAX
A	.193	.201	4.90	5.10
A1	.106	.114	2.70	2.90
A2	.001	.010	0.02	0.25
b	.045	.057	1.15	1.45
b2	.075	.083	1.90	2.10
C	.016	.026	0.40	0.65
C2	.057	.063	1.45	1.60
D	.543	.551	13.80	14.00
D1	.488	.500	12.40	12.70
E	.624	.632	15.85	16.05
E1	.524	.535	13.30	13.60
e	.215 BSC		5.45 BSC	
H	.736	.752	18.70	19.10
L	.094	.106	2.40	2.70
L1	.047	.055	1.20	1.40
L2	.039	.045	1.00	1.15
L3	.010 BSC		0.25 BSC	
L4	.150	.161	3.80	4.10


PLUS220 (IXFV) Outline



1. GATE
2. DRAIN (COLLECTOR)
3. SOURCE (EMITTER)
4. DRAIN (COLLECTOR)

SYM	INCHES MIN	MAX	MILLIMETER MIN	MAX
A	.169	.185	4.30	4.70
A1	.028	.035	0.70	0.90
A2	.098	.118	2.50	3.00
b	.035	.047	0.90	1.20
b1	.080	.095	2.03	2.41
b2	.054	.064	1.37	1.63
c	.028	.035	0.70	0.90
D	.551	.591	14.00	15.00
D1	.512	.539	13.00	13.70
E	.394	.433	10.00	11.00
E1	.331	.346	8.40	8.80
e	.100 BSC		2.54 BSC	
L	.512	.551	13.00	14.00
L1	.118	.138	3.00	3.50
L2	.035	.051	0.90	1.30
L3	.047	.059	1.20	1.50

PLUS220SMD (IXFV_S) Outline



1. GATE
2. DRAIN (COLLECTOR)
3. SOURCE (EMITTER)
4. DRAIN (COLLECTOR)

SYM	INCHES MIN	MAX	MILLIMETER MIN	MAX
A	.169	.185	4.30	4.70
A1	.028	.035	0.70	0.90
A2	.098	.118	2.50	3.00
A3	.000	.010	0.00	0.25
b	.035	.047	0.90	1.20
b1	.080	.095	2.03	2.41
b2	.054	.064	1.37	1.63
c	.028	.035	0.70	0.90
D	.551	.591	14.00	15.00
D1	.512	.539	13.00	13.70
E	.394	.433	10.00	11.00
E1	.331	.346	8.40	8.80
e	.200BSC		5.08 BSC	
L	.209	.228	5.30	5.80
L1	.118	.138	3.00	3.50
L2	.035	.051	0.90	1.30
L3	.047	.059	1.20	1.50
L4	.039	.059	1.00	1.50

© 2006 IXYS All rights reserved



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.