Standard Rectifier Module

3~ Rectifier		
V_{RRM}	=	800 V
I_{DAV}	=	90 A
I_{FSM}	=	750 A

3~ Rectifier Bridge

Part number

VUO82-08NO7

E72873



Features / Advantages:

- Package with DCB ceramic
- Improved temperature and power cycling
- Planar passivated chips
- Very low forward voltage drop
- Very low leakage current

Applications:

- Diode for main rectification
- For three phase bridge configurations
- Supplies for DC power equipment
- Input rectifiers for PWM inverter
- Battery DC power supplies
- Field supply for DC motors

Package: PWS-D

- Isolation Voltage: 3000 V~
- Industry standard outline
- RoHS compliant
- Easy to mount with two screws
- Base plate: Copper internally DCB isolated
- Advanced power cycling

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

© 2019 IXYS all rights reserved

Rectifier

Symbol	Definition	Conditions		Ratings min.	typ.	max.	Unit
V_{RSM}	*max. non-repetitive reverse blocking voltage*		T_{VJ} = 25°C			900	V
V_{RRM}	*max. repetitive reverse blocking voltage*		T_{VJ} = 25°C			800	V
I_R	*reverse current*	V_R = 800 V	T_{VJ} = 25°C			100	µA
		V_R = 800 V	T_{VJ} = 150°C			1.5	mA
V_F	*forward voltage drop*	I_F = 30 A	T_{VJ} = 25°C			1.08	V
		I_F = 90 A				1.35	V
		I_F = 30 A	T_{VJ} = 125°C			0.99	V
		I_F = 90 A				1.33	V
I_{DAV}	*bridge output current*	T_C = 115°C	T_{VJ} = 150°C			90	A
		rectangular d = ⅓					
V_{F0}	*threshold voltage* } *for power loss calculation only*		T_{VJ} = 150°C			0.78	V
r_F	*slope resistance* }					6	mΩ
R_{thJC}	*thermal resistance junction to case*					0.9	K/W
R_{thCH}	*thermal resistance case to heatsink*				0.4		K/W
P_{tot}	*total power dissipation*		T_C = 25°C			135	W
I_{FSM}	*max. forward surge current*	t = 10 ms; (50 Hz), sine	T_{VJ} = 45°C			750	A
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			810	A
		t = 10 ms; (50 Hz), sine	T_{VJ} = 150°C			640	A
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			690	A
I^2t	*value for fusing*	t = 10 ms; (50 Hz), sine	T_{VJ} = 45°C			2.82	kA²s
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			2.73	kA²s
		t = 10 ms; (50 Hz), sine	T_{VJ} = 150°C			2.05	kA²s
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			1.98	kA²s
C_J	*junction capacitance*	V_R = 400 V; f = 1 MHz	T_{VJ} = 25°C		27		pF

© 2019 IXYS all rights reserved

Package PWS-D				Ratings			
Symbol	**Definition**	**Conditions**		**min.**	**typ.**	**max.**	**Unit**
I_{RMS}	*RMS current*	per terminal				150	A
T_{VJ}	*virtual junction temperature*			-40		150	°C
T_{op}	*operation temperature*			-40		125	°C
T_{stg}	*storage temperature*			-40		125	°C
Weight					159		g
M_D	*mounting torque*			4.25		5.75	Nm
M_T	*terminal torque*			4.25		5.75	Nm
$d_{Spp/App}$	*creepage distance on surface | striking distance through air*		*terminal to terminal*	9.5			mm
$d_{Spb/Apb}$			*terminal to backside*	26.0			mm
V_{ISOL}	*isolation voltage*	t = 1 second	50/60 Hz, RMS; I_{ISOL} ≤ 1 mA	3000			V
		t = 1 minute		2500			V



Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	VUO82-08NO7	VUO82-08NO7	Box	10	460400

Equivalent Circuits for Simulation

** on die level* T_{VJ} = 150°C



Rectifier

$V_{0\ max}$	*threshold voltage*	0.78	V
$R_{0\ max}$	*slope resistance **	4.8	mΩ

© 2019 IXYS all rights reserved

Outlines PWS-D





© 2019 IXYS all rights reserved

Rectifier



Fig. 1 Forward current versus voltage drop per diode



Fig. 2 Surge overload current



Fig. 3 I^2t versus time per diode



Fig. 4 Power dissipation vs. direct output current & ambient temperature



Fig. 5 Max. forward current vs. case temperature



Fig. 6 Transient thermal impedance junction to case

Constants for Z_{thJC} calculation:

i	R_{th} (K/W)	t_i (s)
1	0.05	0.001
2	0.14	0.030
3	0.18	0.070
4	0.28	0.150
5	0.25	0.950

© 2019 IXYS all rights reserved