



### SRDA3.3 Series 8pF 35A Diode Array




#### Pinout



SOIC-8 (Top View)

Note: Pinout diagrams above shown as device footprint on circuit board.

#### Functional Block Diagram



Life Support Note:

**Not Intended for Use in Life Support or Life Saving Applications**

The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.

#### Description

The SRDA3.3 integrates low capacitance rail-to-rail diodes with an additional zener diode to protect I/O pins against ESD and lightning induced surge events. This device can safely absorb up to 35A per IEC61000-4-5 ( $t_p=8/20\mu s$ ) without performance degradation and a minimum  $\pm 30kV$  ESD per IEC61000-4-2 international standard. Its low loading capacitance makes it ideal for high-speed interface protection.


#### Features

- Lightning protection, IEC61000-4-5, 35A (8/20 $\mu s$ )
- EFT, IEC61000-4-4, 50A (5/50ns)
- ESD, IEC61000-4-2,  $\pm 30kV$  contact,  $\pm 30kV$  air
- Low clamping voltage
- Low leakage current
- SOIC-8 surface mount package (JEDEC MS-012)

#### Applications

- Tertiary (IC Side) Protection:
  - T1/E1/T3/E3
  - HDSD/SDSL
  - Ethernet
- RS232, RS485
- Video Line Protection
- Security Cameras
- Storage DVRs
- Network Equipment
- Instrumentation, Medical Equipment

#### Application Example



T1/E1/T3/E3 Interface Protection

### Absolute Maximum Ratings

| Symbol     | Parameter                         | Value      | Units |
|------------|-----------------------------------|------------|-------|
| $P_{pk}$   | Peak Pulse Power (8/20 $\mu$ s)   | 600        | W     |
| $I_{pp}$   | Peak Pulse Current (8/20 $\mu$ s) | 35         | A     |
| $T_{op}$   | Operating Temperature             | -40 to 125 | °C    |
| $T_{stor}$ | Storage Temperature               | -55 to 150 | °C    |

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

### Thermal Information


| Parameter   | Rating     | Units |
|---|------------|-------|
| SOIC Package  | 170        | °C/W  |
| Operating Temperature Range   | -40 to 125 | °C    |
| Storage Temperature Range   | -55 to 150 | °C    |
| Maximum Junction Temperature  | 150        | °C    |
| Maximum Lead Temperature (Soldering 20-40s) (SOIC - Lead Tips Only) | 260        | °C    |

### Electrical Characteristics ( $T_{op} = 25^{\circ}\text{C}$ )


| Parameter                                    | Symbol        | Test Conditions                               | Min      | Typ  | Max | Units         |
|--|---------------|---|----------|------|-----|---------------|
| Reverse Stand-Off Voltage                    | $V_{RWM}$     | $I_T \leq 1\mu\text{A}$                       | -        | -    | 3.3 | V             |
| Reverse Breakdown Voltage                    | $V_{BR}$      | $I_T = 2\mu\text{A}$                          | 3.5      | -    | -   | V             |
| Snap Back Voltage                            | $V_{SB}$      | $I_T = 50\text{mA}$                           | 2.9      | -    | -   | V             |
| Reverse Leakage Current                      | $I_R$         | $V_R = 3.3\text{V}$                           | -        | -    | 1   | $\mu\text{A}$ |
| Clamping Voltage, Line-Ground <sup>1</sup>   | $V_C$         | $I_{pp} = 1\text{A}, t_p = 8/20 \mu\text{s}$  | -        | 5.7  | -   | V             |
| Clamping Voltage, Line-Ground <sup>1</sup>   | $V_C$         | $I_{pp} = 10\text{A}, t_p = 8/20 \mu\text{s}$ | -        | 10.1 | -   | V             |
| Clamping Voltage, Line-Ground <sup>1</sup>   | $V_C$         | $I_{pp} = 30\text{A}, t_p = 8/20 \mu\text{s}$ | -        | 17.7 | -   | V             |
| Dynamic Resistance, Line-Ground <sup>1</sup> | $R_{DYN}$     | $(V_{C2} - V_{C1}) / (I_{PP2} - I_{PP1})$     | -        | 0.5  | -   | $\Omega$      |
| ESD Withstand Voltage <sup>1</sup>           | $V_{ESD}$     | IEC61000-4-2 (Contact Discharge)              | $\pm 30$ | -    | -   | kV            |
|  |               | IEC61000-4-2 (Air Discharge)                  | $\pm 30$ | -    | -   | kV            |
| Diode Capacitance <sup>1</sup>               | $C_{I/O-I/O}$ | Reverse Bias=0V                               | -        | 4.0  | -   | pF            |
|  | $C_{I/O-GND}$ | Reverse Bias=0V                               | -        | 8.0  | -   | pF            |

<sup>1</sup> Parameter is guaranteed by design and/or device characterization.


### Normalized Capacitance vs. Bias Voltage




### Non-Repetitive Peak Pulse Power vs. Pulse Time




### Clamping Voltage vs. $I_{PP}$



### Power Derating Curve



### Pulse Waveform



### Product Characteristics


|                            |                         |
|----------------------------|-------------------------|
| <b>Lead Plating</b>        | Matte Tin               |
| <b>Lead Material</b>       | Copper Alloy            |
| <b>Lead Coplanarity</b>    | 0.0004 inches (0.102mm) |
| <b>Substitute Material</b> | Silicon                 |
| <b>Body Material</b>       | Molded Epoxy            |
| <b>Flammability</b>        | UL 94 V-0               |

Notes :


- All dimensions are in millimeters
- Dimensions include solder plating.
- Dimensions are exclusive of mold flash & metal burr.
- Blo is facing up for mold and facing down for trim/form, i.e. reverse trim/form.
- Package surface matte finish VDI 11-13.

### Soldering Parameters


|  |                                    |                         |
|--|------------------------------------|-------------------------|
| <b>Reflow Condition</b>                                |                                    | Pb – Free assembly      |
| <b>Pre Heat</b>  | - Temperature Min ( $T_{s(min)}$ ) | 150°C                   |
|  | - Temperature Max ( $T_{s(max)}$ ) | 200°C                   |
|  | - Time (min to max) ( $t_s$ )      | 60 – 180 secs           |
| Average ramp up rate (Liquidus Temp ( $T_L$ ) to peak) |                                    | 3°C/second max          |
| $T_{s(max)}$ to $T_L$ - Ramp-up Rate                   |                                    | 3°C/second max          |
| <b>Reflow</b>  | - Temperature ( $T_L$ ) (Liquidus) | 217°C                   |
|  | - Temperature ( $t_L$ )            | 60 – 150 seconds        |
| Peak Temperature ( $T_p$ )                             |                                    | 260 <sup>+0/-5</sup> °C |
| Time within 5°C of actual peak Temperature ( $t_p$ )   |                                    | 20 – 40 seconds         |
| Ramp-down Rate   |                                    | 6°C/second max          |
| Time 25°C to peak Temperature ( $T_p$ )                |                                    | 8 minutes Max.          |
| Do not exceed  |                                    | 260°C                   |



**Part Numbering System**




**Part Marking System**



**Ordering Information**


| Part Number  | Package | Marking | Min. Order Qty. |
|--------------|---------|---------|-----------------|
| SRDA3.3-4BTG | SOIC-8  | SRDA3.3 | 2500            |

**Package Dimensions – Mechanical Drawings and Recommended Solder Pad Outline**



| Package   | SOIC        |      |           |       |
|-----------|-------------|------|-----------|-------|
| Pins      | 8           |      |           |       |
| JEDEC     | MS-012      |      |           |       |
|           | Millimetres |      | Inches    |       |
|           | Min         | Max  | Min       | Max   |
| <b>A</b>  | 1.35        | 1.75 | 0.053     | 0.069 |
| <b>A1</b> | 0.10        | 0.25 | 0.004     | 0.010 |
| <b>A2</b> | 1.25        | 1.65 | 0.050     | 0.065 |
| <b>B</b>  | 0.31        | 0.51 | 0.012     | 0.020 |
| <b>c</b>  | 0.17        | 0.25 | 0.007     | 0.010 |
| <b>D</b>  | 4.80        | 5.00 | 0.189     | 0.197 |
| <b>E</b>  | 5.80        | 6.20 | 0.228     | 0.244 |
| <b>E1</b> | 3.80        | 4.00 | 0.150     | 0.157 |
| <b>e</b>  | 1.27 BSC    |      | 0.050 BSC |       |
| <b>L</b>  | 0.40        | 1.27 | 0.016     | 0.050 |

**Embossed Carrier Tape & Reel Specification – SOIC Package**



|             | Millimetres   |      | Inches          |       |
|-------------|---------------|------|-----------------|-------|
|             | Min           | Max  | Min             | Max   |
| <b>E</b>    | 1.65          | 1.85 | 0.065           | 0.073 |
| <b>F</b>    | 5.4           | 5.6  | 0.213           | 0.22  |
| <b>P2</b>   | 1.95          | 2.05 | 0.077           | 0.081 |
| <b>D</b>    | 1.5           | 1.6  | 0.059           | 0.063 |
| <b>D1</b>   | 1.50 Min      |      | 0.059 Min       |       |
| <b>P0</b>   | 3.9           | 4.1  | 0.154           | 0.161 |
| <b>10P0</b> | 40.0 +/- 0.20 |      | 1.574 +/- 0.008 |       |
| <b>W</b>    | 11.9          | 12.1 | 0.468           | 0.476 |
| <b>P</b>    | 7.9           | 8.1  | 0.311           | 0.319 |
| <b>A0</b>   | 6.3           | 6.5  | 0.248           | 0.256 |
| <b>B0</b>   | 5.1           | 5.3  | 0.2             | 0.209 |
| <b>K0</b>   | 2             | 2.2  | 0.079           | 0.087 |
| <b>t</b>    | 0.30 +/- 0.05 |      | 0.012 +/- 0.002 |       |