


# DSA20C100PN

## 100 V, 20 A Schottky Rectifier Diode

RoHS



Pb



### Features:

- Very low  $V_F$
- Extremely low switching losses
- Low  $I_{RM}$  values
- Improved thermal behaviour
- High reliability circuit operation
- Low voltage peaks for reduced protection circuits
- Low noise switching
- Terminals finish: 100% pure tin
- This is a Pb-free device
- Epoxy meets UL 94 V-0
- Isolation Voltage:  $V \sim 2500$
- Soldering pins for PCB mounting
- Base plate: Plastic over molded tab

### Pinout Diagram (TO-220-3L ABFP)



### Applications:

- Switching power supply
- Free-Wheeling diodes
- Converters
- Reverse battery protection

### Product Summary

| Characteristic | Value         | Unit |
|----------------|---------------|------|
| $V_{RRM}$      | 100           | V    |
| $I_{FAV}$      | $2 \times 10$ | A    |
| $V_F$          | 0.71          | V    |

**A:** Anode; **C:** Cathode

**Maximum Ratings** ( $T_{VJ} = 25^{\circ}\text{C}$  unless otherwise specified)

| Symbol    | Characteristic                                        | Conditions                                                              | Value            | Unit |
|-----------|-------------------------------------------------------|-------------------------------------------------------------------------|------------------|------|
| $V_{RRM}$ | Peak Repetitive Reverse Voltage                       | -                                                                       | 100              | V    |
| $V_{RWM}$ | Working Peak Reverse Voltage                          |                                                                         |                  |      |
| $V_R$     | DC Blocking Voltage                                   |                                                                         |                  |      |
| $I_{FAV}$ | Average Rectified Forward Current                     | 50% duty cycle @ $T_C = 140^{\circ}\text{C}$ ,<br>rectangular wave form | per leg<br>10    | A    |
|           |                                                       |                                                                         | per device<br>20 | A    |
| $I_{FSM}$ | Peak One Cycle Non-Repetitive Surge Current (per leg) | 10 ms, Half Sine pulse, $T_{VJ} = 25^{\circ}\text{C}$                   | 240              | A    |
| $P_{tot}$ | Total Power Dissipation                               | $T_C = 25^{\circ}\text{C}$                                              | 33               | W    |

**Electrical Characteristics** ( $T_{VJ} = 25^{\circ}\text{C}$  unless otherwise specified)

| Symbol    | Characteristic                              | Conditions                                                                    | Value |      |      | Unit          |
|-----------|---------------------------------------------|-------------------------------------------------------------------------------|-------|------|------|---------------|
|           |                                             |                                                                               | Min.  | Typ. | Max. |               |
| $V_{F1}$  | Forward Voltage Drop (per leg) <sup>1</sup> | @10 A, Pulse, $T_{VJ} = 25^{\circ}\text{C}$                                   | -     | -    | 0.89 | V             |
| $V_{F2}$  |                                             | @10 A, Pulse, $T_{VJ} = 125^{\circ}\text{C}$                                  | -     | -    | 0.71 | V             |
| $I_{R1}$  | Reverse Current (per leg) <sup>1</sup>      | @ $V_R = \text{rated } V_R$ , $T_{VJ} = 25^{\circ}\text{C}$                   | -     | -    | 200  | $\mu\text{A}$ |
| $I_{R2}$  |                                             | @ $V_R = \text{rated } V_R$ , $T_{VJ} = 125^{\circ}\text{C}$                  | -     | -    | 10   | mA            |
| $C_T$     | Junction Capacitance (per leg)              | @ $V_R = 12\text{ V}$ , $T_C = 25^{\circ}\text{C}$ , $f_{sig} = 1\text{ MHz}$ | -     | 180  | -    | pF            |
| $V_{ISO}$ | Isolation Voltage                           | $t = 1\text{ sec.}$ , 50/60 Hz. RMS; $I_{ISOL} \leq 1\text{ mA}$              | 2500  | -    | -    | V             |
|           |                                             | $t = 1\text{ min.}$ , 50/60 Hz. RMS; $I_{ISOL} \leq 1\text{ mA}$              | 2100  | -    | -    |               |

**Note 1:** Pulse width < 300  $\mu\text{s}$ , duty cycle < 2%**Thermal-Mechanical Specifications**

| Symbol     | Characteristics                              | Condition    | Specification      | Units              |
|------------|----------------------------------------------|--------------|--------------------|--------------------|
| $T_{VJ}$   | Junction Temperature                         | -            | -55 to +175        | $^{\circ}\text{C}$ |
| $T_O$      | Operation Temperature                        | -            | -55 to +150        | $^{\circ}\text{C}$ |
| $T_{stg}$  | Storage Temperature                          | -            | -55 to +150        | $^{\circ}\text{C}$ |
| $M_D$      | Mounting torque                              | -            | Min 0.4<br>Max 0.6 | Nm                 |
| $F_C$      | Mounting force with clip                     | -            | Min 20<br>Max 60   | N                  |
| $R_{thJC}$ | Maximum Thermal Resistance Junction to Case  | DC operation | 4.5                | K/W                |
| $R_{thCS}$ | Typical Thermal Resistance Case to Heat Sink | -            | 0.50               | K/W                |
| wt         | Approximate Weight                           | -            | 2                  | g                  |

Characteristic Curves

Fig. 1. Typical Forward Characteristics




Fig. 2. Typical Reverse Characteristics






Fig. 3. Typical Junction Capacitance



Part Outline Drawing (TO-220-3L ABFP)



| Symbol | Inches |         |       | Millimeters |         |       |
|--------|--------|---------|-------|-------------|---------|-------|
|        | Min.   | Typical | Max.  | Min.        | Typical | Max   |
| A      | 0.169  | 0.177   | 0.185 | 4.30        | 4.50    | 4.70  |
| A1     | 0.043  | 0.051   | 0.059 | 1.10        | 1.30    | 1.50  |
| A2     | 0.110  | 0.118   | 0.126 | 2.80        | 3.00    | 3.20  |
| A3     | 0.098  | 0.106   | 0.114 | 2.50        | 2.70    | 2.90  |
| b      | 0.020  | 0.024   | 0.03  | 0.50        | 0.60    | 0.75  |
| b1     | 0.043  | 0.047   | 0.053 | 1.10        | 1.20    | 1.35  |
| b2     | 0.059  | 0.063   | 0.069 | 1.50        | 1.60    | 1.75  |
| b3     | 0.047  | 0.051   | 0.057 | 1.20        | 1.30    | 1.45  |
| b4     | 0.063  | 0.067   | 0.073 | 1.60        | 1.70    | 1.85  |
| c      | 0.020  | 0.024   | 0.030 | 0.50        | 0.60    | 0.75  |
| D      | 0.583  | 0.591   | 0.598 | 14.80       | 15.00   | 15.20 |
| E      | 0.392  | 0.400   | 0.408 | 9.96        | 10.16   | 10.36 |
| e      | —      | 0.100   | —     | —           | 2.55    | —     |
| e1     | —      | 0.201   | —     | —           | 5.10    | —     |
| H1     | 0.256  | 0.264   | 0.272 | 6.50        | 6.70    | 6.90  |
| L      | 0.500  | 0.520   | 0.539 | 12.70       | 13.20   | 13.70 |
| L1     | 0.063  | 0.071   | 0.079 | 1.60        | 1.80    | 2.00  |
| L2     | 0.031  | 0.039   | 0.047 | 0.80        | 1.00    | 1.20  |
| L3     | 0.024  | 0.031   | 0.039 | 0.60        | 0.80    | 1.00  |
| ØP1    | 0.130  | 0.138   | 0.146 | 3.30        | 3.50    | 3.70  |
| ØP2    | 0.118  | 0.126   | 0.133 | 2.99        | 3.19    | 3.39  |
| Q      | 0.098  | 0.106   | 0.114 | 2.50        | 2.70    | 2.90  |

Ordering Information


| Part Number | Marking     | Packing Mode | Quantity    |
|-------------|-------------|--------------|-------------|
| DSA20C100PN | DSA20C100PN | Tube         | 50 pcs/tube |

Part Numbering and Marking

DSA20C100PN  
IXYS YYWWWS  
XXXXXXX

D = Diode  
S = Schottky Diode  
A = Product Generation  
20 = Current Rating (20 A)  
C = Common Cathode  
100 = Voltage Rating (100 V)  
PN = Package Code  
YY = Year  
WW = Work Week  
S = Plant Location Code  
XXXXXXX = Lot Number

Packing Specifications



**Disclaimer Notice**  
Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.  
Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.

Part of: