


HiPerFRED²

$$\begin{aligned} V_{RRM} &= 300 \text{ V} \\ I_{FAV} &= 2 \times 60 \text{ A} \\ t_{rr} &= 35 \text{ ns} \end{aligned}$$


High Performance Fast Recovery Diode
 Low Loss and Soft Recovery
 Common Cathode

Part number

DPG120C300QB



Backside: cathode



Features / Advantages:

- Planar passivated chips
- Very low leakage current
- Very short recovery time
- Improved thermal behaviour
- Very low I_{rm} -values
- Very soft recovery behaviour
- Avalanche voltage rated for reliable operation
- Soft reverse recovery for low EMI/RFI
- Low I_{rm} reduces:
 - Power dissipation within the diode
 - Turn-on loss in the commutating switch

Applications:

- Antiparallel diode for high frequency switching devices
- Antisaturation diode
- Snubber diode
- Free wheeling diode
- Rectifiers in switch mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)

Package: TO-3P

- Industry standard outline compatible with TO-247
- RoHS compliant
- Epoxy meets UL 94V-0

Disclaimer Notice


Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.



Fast Diode				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
V _{RSM}	max. non-repetitive reverse blocking voltage	T _{VJ} = 25°C				300	V
V _{RRM}	max. repetitive reverse blocking voltage	T _{VJ} = 25°C				300	V
I _R	reverse current, drain current	V _R = 300 V	T _{VJ} = 25°C			1	μA
		V _R = 300 V	T _{VJ} = 150°C			0.35	mA
V _F	forward voltage drop	I _F = 60 A	T _{VJ} = 25°C			1.40	V
		I _F = 120 A				1.72	V
		I _F = 60 A	T _{VJ} = 125°C			1.10	V
		I _F = 120 A				1.45	V
I _{FAV}	average forward current	T _C = 130°C rectangular d = 0.5	T _{VJ} = 175°C			60	A
V _{F0}	threshold voltage	} for power loss calculation only		T _{VJ} = 175°C		0.69	V
r _F	slope resistance					5.8	mΩ
R _{thJC}	thermal resistance junction to case					0.55	K/W
R _{thCH}	thermal resistance case to heatsink				0.3		K/W
P _{tot}	total power dissipation	T _C = 25°C				275	W
I _{FSM}	max. forward surge current	t = 10 ms; (50 Hz), sine; V _R = 0 V		T _{VJ} = 45°C		450	A
C _J	junction capacitance	V _R = 150 V f = 1 MHz		T _{VJ} = 25°C	80		pF
I _{RM}	max. reverse recovery current	} I _F = 60 A; V _R = 200 V -di _F /dt = 200 A/μs		T _{VJ} = 25 °C	3.5		A
t _{rr}	reverse recovery time			T _{VJ} = 125 °C	9		A
				T _{VJ} = 25 °C	35		ns
				T _{VJ} = 125 °C	65		ns

Package TO-3P			Ratings			
Symbol	Definition	Conditions	min.	typ.	max.	Unit
I_{RMS}	RMS current	per terminal ¹⁾			70	A
T_{VJ}	virtual junction temperature		-55		175	°C
T_{op}	operation temperature		-55		150	°C
T_{stg}	storage temperature		-55		150	°C
Weight				5		g
M_D	mounting torque		0.8		1.2	Nm
F_C	mounting force with clip		20		120	N

Product Marking



Part description

D = Diode
 P = HiPerFRED
 G = extreme fast
 120 = Current Rating [A]
 C = Common Cathode
 300 = Reverse Voltage [V]
 QB = TO-3P (3)


Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	DPG120C300QB	DPG120C300QB	Tube	30	503821

Equivalent Circuits for Simulation


* on die level

$T_{VJ} = 175^{\circ}\text{C}$

		Fast Diode	
$V_{0\max}$	threshold voltage	0.69	V
$R_{0\max}$	slope resistance *	3.2	mΩ

Outlines TO-3P


Dim.	Millimeter		Inches	
	min	max	min	max
A	4.70	4.90	0.185	0.193
A1	1.30	1.50	0.051	0.059
A2	1.45	1.65	0.057	0.065
b	0.90	1.15	0.035	0.045
b2	1.90	2.20	0.075	0.087
b4	2.90	3.20	0.114	0.126
c	0.55	0.80	0.022	0.031
D	19.80	20.10	0.780	0.791
D1	16.90	17.20	0.665	0.677
E	15.50	15.80	0.610	0.622
E1	13.50	13.70	0.531	0.539
e	5.45 BSC		0.215 BSC	
L	19.80	20.20	0.780	0.795
L1	3.40	3.60	0.134	0.142
Ø P	3.20	3.40	0.126	0.134
ØP1	6.90	7.10	0.272	0.280
S	4.90	5.10	0.193	0.201




Fast Diode


Fig. 1 Forward current I_F versus V_F




Fig. 2 Typ. reverse recov. charge Q_{rr} versus $-di_F/dt$




Fig. 3 Typ. reverse recov. current I_{RM} versus $-di_F/dt$




Fig. 4 Typ. dynamic parameters Q_{rr} , I_{RM} versus T_{VJ}




Fig. 5 Typ. reverse recov. time t_{rr} versus $-di_F/dt$




Fig. 6 Typ. forward recov. voltage V_{FR} & time t_{fr} versus di_F/dt




Fig. 7 Typ. recovery energy E_{rec} versus $-di_F/dt$




Fig. 8 Transient thermal impedance junction to case