


### High Voltage, High Gain BIMOSFET™ Monolithic Bipolar MOS Transistor

### IXBT42N170A IXBH42N170A



$$V_{CES} = 1700V$$


$$I_{C90} = 21A$$

$$V_{CE(sat)} \leq 6.0V$$


$$t_{fi} = 20ns$$

| Symbol                                       | Test Conditions                                                                               | Maximum Ratings       |            |
|----------------------------------------------|-----------------------------------------------------------------------------------------------|-----------------------|------------|
| $V_{CES}$                                    | $T_C = 25^\circ C$ to $150^\circ C$                                                           | 1700                  | V          |
| $V_{CGR}$                                    | $T_J = 25^\circ C$ to $150^\circ C$ , $R_{GE} = 1M\Omega$                                     | 1700                  | V          |
| $V_{GES}$                                    | Continuous                                                                                    | $\pm 20$              | V          |
| $V_{GEM}$                                    | Transient                                                                                     | $\pm 30$              | V          |
| $I_{C25}$                                    | $T_C = 25^\circ C$                                                                            | 42                    | A          |
| $I_{C90}$                                    | $T_C = 90^\circ C$                                                                            | 21                    | A          |
| $I_{CM}$                                     | $T_C = 25^\circ C$ , 1ms                                                                      | 265                   | A          |
| <b>SSOA</b><br><b>(RBSOA)</b>                | $V_{GE} = 15V$ , $T_{VJ} = 125^\circ C$ , $R_G = 10\Omega$<br>Clamped Inductive Load          | $I_{CM} = 84$<br>1360 | A<br>V     |
| <b><math>T_{SC}</math></b><br><b>(SCSOA)</b> | $V_{GE} = 15V$ , $V_{CES} = 1200V$ , $T_J = 125^\circ C$<br>$R_G = 10\Omega$ , non repetitive | 10                    | $\mu s$    |
| $P_C$                                        | $T_C = 25^\circ C$                                                                            | 357                   | W          |
| $T_J$                                        |                                                                                               | -55 ... +150          | $^\circ C$ |
| $T_{JM}$                                     |                                                                                               | 150                   | $^\circ C$ |
| $T_{stg}$                                    |                                                                                               | -55 ... +150          | $^\circ C$ |
| $T_L$                                        | 1.6mm (0.062 in.) from Case for 10s                                                           | 300                   | $^\circ C$ |
| $T_{SOLD}$                                   | Plastic Body for 10 seconds                                                                   | 260                   | $^\circ C$ |
| $M_d$                                        | Mounting Torque (TO-247)                                                                      | 1.13/10               | Nm/lb.in.  |
| <b>Weight</b>                                | TO-268                                                                                        | 4                     | g          |
|                                              | TO-247                                                                                        | 6                     | g          |

TO-268 (IXBT)



TO-247 (IXBH)



G = Gate      C = Collector  
E = Emitter    Tab = Collector

#### Features

- High Blocking Voltage
- International Standard Packages
- Anti-Parallel Diode
- Low Conduction Losses

#### Advantages

- Low Gate Drive Requirement
- High Power Density

#### Applications

- Switch-Mode and Resonant-Mode Power Supplies
- Uninterruptible Power Supplies (UPS)
- AC Motor Drives
- Capacitor Discharge Circuits
- AC Switches

| Symbol                          | Test Conditions<br>( $T_J = 25^\circ C$ Unless Otherwise Specified) | Characteristic Values |      |                      |
|---------------------------------|---------------------------------------------------------------------|-----------------------|------|----------------------|
|                                 |                                                                     | Min.                  | Typ. | Max.                 |
| <b><math>BV_{CES}</math></b>    | $I_C = 250\mu A$ , $V_{GE} = 0V$                                    | 1700                  |      | V                    |
| <b><math>V_{GE(th)}</math></b>  | $I_C = 750\mu A$ , $V_{CE} = V_{GE}$                                | 2.5                   |      | 5.5 V                |
| <b><math>I_{CES}</math></b>     | $V_{CE} = 0.8 \cdot V_{CES}$ , $V_{GE} = 0V$<br>$T_J = 125^\circ C$ |                       |      | 50 $\mu A$<br>1.5 mA |
| <b><math>I_{GES}</math></b>     | $V_{CE} = 0V$ , $V_{GE} = \pm 20V$                                  |                       |      | $\pm 100$ nA         |
| <b><math>V_{CE(sat)}</math></b> | $I_C = I_{C90}$ , $V_{GE} = 15V$ , Note 1<br>$T_J = 125^\circ C$    |                       | 5.2  | 6.0 V                |
|                                 |                                                                     |                       | 5.3  | V                    |

## Symbol Test Conditions

( $T_J = 25^\circ\text{C}$  Unless Otherwise Specified)

## Characteristic Values

Min. Typ. Max.

|              |                                                                                                                                                                                |    |      |                        |
|--------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----|------|------------------------|
| $g_{fs}$     | $I_C = I_{C90}, V_{CE} = 10V, \text{Note 1}$                                                                                                                                   | 14 | 23   | S                      |
| $C_{ies}$    | $V_{CE} = 25V, V_{GE} = 0V, f = 1\text{MHz}$                                                                                                                                   |    | 3920 | pF                     |
| $C_{oes}$    |                                                                                                                                                                                |    | 275  | pF                     |
| $C_{res}$    |                                                                                                                                                                                |    | 107  | pF                     |
| $Q_{g(on)}$  | $I_C = I_{C90}, V_{GE} = 15V, V_{CE} = 0.5 \cdot V_{CES}$                                                                                                                      |    | 188  | nC                     |
| $Q_{ge}$     |                                                                                                                                                                                |    | 23   | nC                     |
| $Q_{gc}$     |                                                                                                                                                                                |    | 80   | nC                     |
| $t_{d(on)}$  | <b>Inductive load, <math>T_J = 25^\circ\text{C}</math></b><br>$I_C = I_{C90}, V_{GE} = 15V$<br>$V_{CE} = 0.5 \cdot V_{CES}, R_G = 1\Omega$<br>Diode Type = DH40-18A<br>Note 2  |    | 19   | ns                     |
| $t_{ri}$     |                                                                                                                                                                                |    | 17   | ns                     |
| $E_{on}$     |                                                                                                                                                                                |    | 3.43 | mJ                     |
| $t_{d(off)}$ |                                                                                                                                                                                |    | 200  | ns                     |
| $t_{fi}$     |                                                                                                                                                                                |    | 20   | ns                     |
| $E_{off}$    |                                                                                                                                                                                |    | 0.43 | mJ                     |
| $t_{d(on)}$  | <b>Inductive load, <math>T_J = 125^\circ\text{C}</math></b><br>$I_C = I_{C90}, V_{GE} = 15V$<br>$V_{CE} = 0.5 \cdot V_{CES}, R_G = 1\Omega$<br>Diode Type = DH40-18A<br>Note 2 |    | 19   | ns                     |
| $t_{ri}$     |                                                                                                                                                                                |    | 14   | ns                     |
| $E_{on}$     |                                                                                                                                                                                |    | 5.40 | mJ                     |
| $t_{d(off)}$ |                                                                                                                                                                                |    | 226  | ns                     |
| $t_{fi}$     |                                                                                                                                                                                |    | 82   | ns                     |
| $E_{off}$    |                                                                                                                                                                                |    | 0.83 | mJ                     |
| $R_{thJC}$   | TO-247                                                                                                                                                                         |    | 0.21 | $0.35^\circ\text{C/W}$ |
| $R_{thCS}$   |                                                                                                                                                                                |    |      | $^\circ\text{C/W}$     |

## Reverse Diode

## Symbol Test Conditions

( $T_J = 25^\circ\text{C}$  Unless Otherwise Specified)

## Characteristic Values

Min. Typ. Max.


|          |                                                |  |     |    |
|----------|------------------------------------------------|--|-----|----|
| $V_F$    | $I_F = I_{C90}, V_{GE} = 0V$                   |  | 5.0 | V  |
| $t_{rr}$ | $I_F = 25A, V_{GE} = 0V, -di_F/dt = 50A/\mu s$ |  | 330 | ns |
| $I_{RM}$ |                                                |  | 15  | A  |

Note 1: Pulse test,  $t \leq 300\mu s$ , duty cycle,  $d \leq 2\%$ .

## PRELIMINARY TECHNICAL INFORMATION

The product presented herein is under development. The Technical Specifications offered are derived from data gathered during objective characterizations of preliminary engineering lots; but also may yet contain some information supplied during a pre-production design evaluation. IXYS reserves the right to change limits, test conditions, and dimensions without notice.


## TO-268 Outline



Terminals: 1 - Gate 2,4 - Collector  
3 - Emitter

| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .193     | .201 | 4.90        | 5.10  |
| A1  | .106     | .114 | 2.70        | 2.90  |
| A2  | .001     | .010 | 0.02        | 0.25  |
| b   | .045     | .057 | 1.15        | 1.45  |
| b2  | .075     | .083 | 1.90        | 2.10  |
| C   | .016     | .026 | 0.40        | 0.65  |
| C2  | .057     | .063 | 1.45        | 1.60  |
| D   | .543     | .551 | 13.80       | 14.00 |
| D1  | .488     | .500 | 12.40       | 12.70 |
| E   | .624     | .632 | 15.85       | 16.05 |
| E1  | .524     | .535 | 13.30       | 13.60 |
| e   | .215 BSC |      | 5.45 BSC    |       |
| H   | .736     | .752 | 18.70       | 19.10 |
| L   | .094     | .106 | 2.40        | 2.70  |
| L1  | .047     | .055 | 1.20        | 1.40  |
| L2  | .039     | .045 | 1.00        | 1.15  |
| L3  | .010 BSC |      | 0.25 BSC    |       |
| L4  | .150     | .161 | 3.80        | 4.10  |

## TO-247 Outline



Terminals: 1 - Gate 2 - Collector  
3 - Emitter

| Dim. | Millimeter |       | Inches  |       |
|------|------------|-------|---------|-------|
|      | Min.       | Max.  | Min.    | Max.  |
| A    | 4.7        | 5.3   | .185    | .209  |
| A1   | 2.2        | 2.54  | .087    | .102  |
| A2   | 2.2        | 2.6   | .059    | .098  |
| b    | 1.0        | 1.4   | .040    | .055  |
| b1   | 1.65       | 2.13  | .065    | .084  |
| b2   | 2.87       | 3.12  | .113    | .123  |
| C    | .4         | .8    | .016    | .031  |
| D    | 20.80      | 21.46 | .819    | .845  |
| E    | 15.75      | 16.26 | .610    | .640  |
| e    | 5.20       | 5.72  | 0.205   | 0.225 |
| L    | 19.81      | 20.32 | .780    | .800  |
| L1   |            | 4.50  |         | .177  |
| ØP   | 3.55       | 3.65  | .140    | .144  |
| Q    | 5.89       | 6.40  | 0.232   | 0.252 |
| R    | 4.32       | 5.49  | .170    | .216  |
| S    | 6.15 BSC   |       | 242 BSC |       |

IXYS Reserves the Right to Change Limits, Test Conditions and Dimensions.

IXYS MOSFETs and IGBTs are covered 4,835,592 4,931,844 5,049,961 5,237,481 6,162,665 6,404,065 B1 6,683,344 6,727,585 7,005,734 B2 7,157,338B2  
by one or more of the following U.S. patents: 4,860,072 5,017,508 5,063,307 5,381,025 6,259,123 B1 6,534,343 6,710,405 B2 6,759,692 7,063,975 B2  
4,881,106 5,034,796 5,187,117 5,486,715 6,306,728 B1 6,583,505 6,710,463 6,771,478 B2 7,071,537







**Fig. 1. Output Characteristics @  $T_J = 25^\circ\text{C}$** 

**Fig. 2. Extended Output Characteristics @  $T_J = 25^\circ\text{C}$** 

**Fig. 3. Output Characteristics @  $T_J = 125^\circ\text{C}$** 

**Fig. 4. Dependence of  $V_{CE(sat)}$  on Junction Temperature**

**Fig. 5. Collector-to-Emitter Voltage vs. Gate-to-Emitter Voltage**

**Fig. 6. Input Admittance**


Fig. 7. Transconductance




Fig. 8. Gate Charge




Fig. 9. Forward Voltage Drop of Intrinsic Diode




Fig. 10. Capacitance




Fig. 11. Reverse-Bias Safe Operating Area




Fig. 12. Maximum Transient Thermal Impedance




Fig. 13. Forward-Bias Safe Operating Area @  $T_C = 25^\circ\text{C}$




Fig. 14. Forward-Bias Safe Operating Area @  $T_C = 75^\circ\text{C}$




Fig. 15. Inductive Switching Energy Loss vs. Gate Resistance




Fig. 16. Inductive Switching Energy Loss vs. Collector Current




Fig. 17. Inductive Switching Energy Loss vs. Junction Temperature







Fig. 18. Inductive Turn-off Switching Times vs. Gate Resistance




**Fig. 19. Inductive Turn-off  
Switching Times vs. Collector Current**




**Fig. 20. Inductive Turn-off  
Switching Times vs. Junction Temperature**




**Fig. 21. Inductive Turn-on Switching Times  
vs. Gate Resistance**



**Fig. 22. Inductive Turn-on Switching Times  
vs. Collector Current**



**Fig. 23. Inductive Turn-on  
Switching Times vs. Junction Temperature**





---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).