


# 1200V XPT™ IGBT GenX3™ w/ Diode

## IXYN100N120C3H1


High-Speed IGBT  
for 20-50 kHz Switching



$$\begin{aligned} V_{CES} &= 1200V \\ I_{C110} &= 60A \\ V_{CE(sat)} &\leq 3.50V \\ t_{fi(typ)} &= 110ns \end{aligned}$$

| Symbol                        | Test Conditions                                                                     | Maximum Ratings                           |                          |
|-------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------|--------------------------|
| $V_{CES}$                     | $T_J = 25^\circ C$ to $150^\circ C$                                                 | 1200                                      | V                        |
| $V_{CGR}$                     | $T_J = 25^\circ C$ to $150^\circ C$ , $R_{GE} = 1M\Omega$                           | 1200                                      | V                        |
| $V_{GES}$                     | Continuous                                                                          | $\pm 20$                                  | V                        |
| $V_{GEM}$                     | Transient                                                                           | $\pm 30$                                  | V                        |
| $I_{C25}$                     | $T_C = 25^\circ C$ (Chip Capability)                                                | 140                                       | A                        |
| $I_{C110}$                    | $T_C = 110^\circ C$                                                                 | 60                                        | A                        |
| $I_{F110}$                    | $T_C = 110^\circ C$                                                                 | 49                                        | A                        |
| $I_{CM}$                      | $T_C = 25^\circ C$ , 1ms                                                            | 420                                       | A                        |
| $I_A$                         | $T_C = 25^\circ C$                                                                  | 50                                        | A                        |
| $E_{AS}$                      | $T_C = 25^\circ C$                                                                  | 1.2                                       | J                        |
| <b>SSOA</b><br><b>(RBSOA)</b> | $V_{GE} = 15V$ , $T_{VJ} = 125^\circ C$ , $R_G = 1\Omega$<br>Clamped Inductive Load | $I_{CM} = 200$<br>@ $V_{CE} \leq V_{CES}$ | A                        |
| $P_C$                         | $T_C = 25^\circ C$                                                                  | 690                                       | W                        |
| $T_J$                         |                                                                                     | -55 ... +150                              | $^\circ C$               |
| $T_{JM}$                      |                                                                                     | 150                                       | $^\circ C$               |
| $T_{stg}$                     |                                                                                     | -55 ... +150                              | $^\circ C$               |
| $V_{ISOL}$                    | 50/60Hz<br>$I_{ISOL} \leq 1mA$                                                      | $t = 1min$<br>$t = 1s$                    | 2500<br>3000<br>V~<br>V~ |
| $M_d$                         | Mounting Torque<br>Terminal Connection Torque                                       | 1.5/13<br>1.3/11.5                        | Nm/lb.in.<br>Nm/lb.in.   |
| <b>Weight</b>                 |                                                                                     | 30                                        | g                        |

SOT-227B, miniBLOC  
E153432



G = Gate, C = Collector, E = Emitter  
① either emitter terminal can be used as  
Main or Kelvin Emitter

### Features

- Optimized for Low Switching Losses
- Square RBSOA
- Isolation Voltage 2500V~
- Anti-Parallel Sonic Diode
- Positive Thermal Coefficient of  $V_{ce(sat)}$
- Avalanche Rated
- High Current Handling Capability
- International Standard Package

### Advantages

- High Power Density
- Low Gate Drive Requirement

### Applications

- High Frequency Power Inverters
- UPS
- Motor Drives
- SMPS
- PFC Circuits
- Battery Chargers
- Welding Machines
- Lamp Ballasts

| Symbol        | Test Conditions<br>( $T_J = 25^\circ C$ , Unless Otherwise Specified) | Characteristic Values |      |                    |
|---------------|-----------------------------------------------------------------------|-----------------------|------|--------------------|
|               |                                                                       | Min.                  | Typ. | Max.               |
| $BV_{CES}$    | $I_C = 250\mu A$ , $V_{GE} = 0V$                                      | 1200                  |      | V                  |
| $V_{GE(th)}$  | $I_C = 250\mu A$ , $V_{CE} = V_{GE}$                                  | 3.0                   |      | 5.0 V              |
| $I_{CES}$     | $V_{CE} = V_{CES}$ , $V_{GE} = 0V$<br>$T_J = 125^\circ C$             |                       |      | 50 $\mu A$<br>3 mA |
| $I_{GES}$     | $V_{CE} = 0V$ , $V_{GE} = \pm 20V$                                    |                       |      | $\pm 100$ nA       |
| $V_{CE(sat)}$ | $I_C = 100A$ , $V_{GE} = 15V$ , Note 1<br>$T_J = 150^\circ C$         | 2.96<br>3.78          | 3.50 | V<br>V             |

| Symbol Test Conditions<br>( $T_J = 25^\circ\text{C}$ Unless Otherwise Specified) |                                                                                                                                                               | Characteristic Values |       |                         |
|----------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-------|-------------------------|
|                                                                                  |                                                                                                                                                               | Min.                  | Typ.  | Max.                    |
| $g_{fs}$                                                                         | $I_C = 60\text{A}, V_{CE} = 10\text{V}$ , Note 1                                                                                                              | 30                    | 50    | S                       |
| $C_{ies}$                                                                        | $V_{CE} = 25\text{V}, V_{GE} = 0\text{V}, f = 1\text{MHz}$                                                                                                    |                       | 4950  | pF                      |
| $C_{oes}$                                                                        |                                                                                                                                                               |                       | 490   | pF                      |
| $C_{res}$                                                                        |                                                                                                                                                               |                       | 120   | pF                      |
| $Q_{g(on)}$                                                                      | $I_C = I_{C110}, V_{GE} = 15\text{V}, V_{CE} = 0.5 \cdot V_{CES}$                                                                                             |                       | 260   | nC                      |
| $Q_{ge}$                                                                         |                                                                                                                                                               |                       | 47    | nC                      |
| $Q_{gc}$                                                                         |                                                                                                                                                               |                       | 102   | nC                      |
| $t_{d(on)}$                                                                      | <b>Inductive load, <math>T_J = 25^\circ\text{C}</math></b><br>$I_C = I_{C110}, V_{GE} = 15\text{V}$<br>$V_{CE} = 0.5 \cdot V_{CES}, R_G = 1\Omega$<br>Note 2  |                       | 27    | ns                      |
| $t_{ri}$                                                                         |                                                                                                                                                               |                       | 110   | ns                      |
| $E_{on}$                                                                         |                                                                                                                                                               |                       | 12.00 | mJ                      |
| $t_{d(off)}$                                                                     |                                                                                                                                                               |                       | 120   | ns                      |
| $t_{fi}$                                                                         |                                                                                                                                                               |                       | 110   | ns                      |
| $E_{off}$                                                                        |                                                                                                                                                               |                       | 4.90  | mJ                      |
| $t_{d(on)}$                                                                      | <b>Inductive load, <math>T_J = 125^\circ\text{C}</math></b><br>$I_C = I_{C110}, V_{GE} = 15\text{V}$<br>$V_{CE} = 0.5 \cdot V_{CES}, R_G = 1\Omega$<br>Note 2 |                       | 27    | ns                      |
| $t_{ri}$                                                                         |                                                                                                                                                               |                       | 116   | ns                      |
| $E_{on}$                                                                         |                                                                                                                                                               |                       | 15.00 | mJ                      |
| $t_{d(off)}$                                                                     |                                                                                                                                                               |                       | 146   | ns                      |
| $t_{fi}$                                                                         |                                                                                                                                                               |                       | 125   | ns                      |
| $E_{off}$                                                                        |                                                                                                                                                               |                       | 6.15  | mJ                      |
| $R_{thJC}$                                                                       |                                                                                                                                                               |                       |       | 0.18 $^\circ\text{C/W}$ |
| $R_{thCS}$                                                                       |                                                                                                                                                               |                       | 0.05  | $^\circ\text{C/W}$      |

## Reverse Sonic Diode (FRD)

| Symbol Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified) |                                                                                                    | Characteristic Values |      |                         |
|------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------|-----------------------|------|-------------------------|
|                                                                                    |                                                                                                    | Min.                  | Typ. | Max.                    |
| $V_F$                                                                              | $I_F = 60\text{A}, V_{GE} = 0\text{V}$ , Note 1                                                    |                       |      | 2.7 V                   |
|                                                                                    | $T_J = 125^\circ\text{C}$                                                                          |                       | 1.95 | V                       |
| $I_{RM}$                                                                           | $I_F = 60\text{A}, V_{GE} = 0\text{V},$<br>$-di_F/dt = 700\text{A}/\mu\text{s}, V_R = 600\text{V}$ |                       | 50   | A                       |
| $t_{rr}$                                                                           |                                                                                                    |                       | 235  | ns                      |
| $R_{thJC}$                                                                         |                                                                                                    |                       |      | 0.52 $^\circ\text{C/W}$ |







## Notes:






1. Pulse test,  $t \leq 300\mu\text{s}$ , duty cycle,  $d \leq 2\%$ .
2. Switching times & energy losses may increase for higher  $V_{CE}(\text{clamp})$ ,  $T_J$  or  $R_G$ .

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.


IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents:

|           |           |           |           |              |              |              |              |              |             |
|-----------|-----------|-----------|-----------|--------------|--------------|--------------|--------------|--------------|-------------|
| 4,835,592 | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665    | 6,404,065 B1 | 6,683,344    | 6,727,585    | 7,005,734 B2 | 7,157,338B2 |
| 4,860,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123 B1 | 6,534,343    | 6,710,405 B2 | 6,759,692    | 7,063,975 B2 |             |
| 4,881,106 | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728 B1 | 6,583,505    | 6,710,463    | 6,771,478 B2 | 7,071,537    |             |


**Fig. 1. Output Characteristics @  $T_J = 25^\circ\text{C}$** 

**Fig. 2. Extended Output Characteristics @  $T_J = 25^\circ\text{C}$** 

**Fig. 3. Output Characteristics @  $T_J = 150^\circ\text{C}$** 

**Fig. 4. Dependence of  $V_{CE(sat)}$  on Junction Temperature**

**Fig. 5. Collector-to-Emitter Voltage vs. Gate-to-Emitter Voltage**

**Fig. 6. Input Admittance**


**Fig. 7. Transconductance**

**Fig. 8. Gate Charge**

**Fig. 9. Capacitance**

**Fig. 10. Reverse-Bias Safe Operating Area**

**Fig. 11. Maximum Transient Thermal Impedance (IGBT)**



**Fig. 12. Inductive Switching Energy Loss vs. Gate Resistance**




**Fig. 13. Inductive Switching Energy Loss vs. Collector Current**




**Fig. 14. Inductive Switching Energy Loss vs. Junction Temperature**




**Fig. 15. Inductive Turn-off Switching Times vs. Gate Resistance**




**Fig. 16. Inductive Turn-off Switching Times vs. Collector Current**




**Fig. 17. Inductive Turn-off Switching Times vs. Junction Temperature**




**Fig. 18. Inductive Turn-on Switching Times vs. Gate Resistance**




**Fig. 19. Inductive Turn-on Switching Times vs. Collector Current**




**Fig. 20. Inductive Turn-on Switching Times vs. Junction Temperature**




**Fig. 21. Diode Forward Characteristics**




**Fig. 22. Reverse Recovery Charge vs.  $-di_F/dt$**




**Fig. 23. Reverse Recovery Current vs.  $-di_F/dt$**




**Fig. 24. Reverse Recovery Time vs.  $-di_F/dt$**




**Fig. 25. Dynamic Parameters  $Q_{RR}$ ,  $I_{RR}$  vs. Junction Temperature**



**Fig. 26. Maximum Transient Thermal Impedance (Diode)**



**SOT-227 miniBLOC (IXYN)**


| SYM | INCHES |       | MILLIMETERS |       |
|-----|--------|-------|-------------|-------|
|     | MIN    | MAX   | MIN         | MAX   |
| A   | 1.224  | 1.260 | 31.10       | 32.00 |
| B   | .303   | .327  | 7.70        | 8.30  |
| C   | .161   | .173  | 4.10        | 4.40  |
| D   | .161   | .173  | 4.10        | 4.40  |
| E   | .161   | .173  | 4.10        | 4.40  |
| F   | .587   | .598  | 14.90       | 15.20 |
| G   | 1.181  | 1.201 | 30.00       | 30.50 |
| H   | 1.488  | 1.508 | 37.80       | 38.30 |
| J   | .461   | .484  | 11.70       | 12.30 |
| L   | .030   | .033  | 0.75        | 0.85  |
| M   | .492   | .512  | 12.50       | 13.00 |
| N   | .984   | 1.004 | 25.00       | 25.50 |
| O   | .075   | .087  | 1.90        | 2.20  |
| S   | .181   | .193  | 4.60        | 4.90  |
| U   | .000   | .005  | 0.00        | 0.13  |

- NUT MATERIAL:  
STANDARD – Low carbon steel with Ni plating.  
OPTIONAL: – Brass Nut is available.  
PART NUMBER-BN
- ALL METAL SURFACE ARE PRE NI PLATED EXCEPT TRIM AREA.