

# STD

## Strap Type, 15 V / 24 V

### Standard

UL 1434 1<sup>st</sup> Edition  
 CSA C22.2 No. 0 CSA TIL No. CA-3A

### Approvals

cULus Recognition  
 TÜV

### Features

This axial leaded strap product is designed to provide reliable, non-cycling protection for rechargeable batteries. The weldable nickel leads with a narrow, low profile design are ideal to be installed directly onto battery cells.

## Specifications

### Packaging

A small pack  
 D standard

### Materials

Insulating material: Polyester Tape  
 Terminals: Nickel

### Max. Device Surface Temperature in Tripped State

125 °C

### Operating / Storage Temperature

-40 °C to +85 °C (consider derating)

### Humidity Ageing

+85 °C, 85 % R.H., 7 days, ± 5 % typical resistance change

### Vibration


MIL-STD-883C, Condition A, no change

### Marking

"P", Part Code, identification, lot number



Dimensions (mm)



S: one slot



Dimensions (mm)													
Model	Fig	A		B		C		D		E		packaging quantity	
		Min	Max	Min	Max	Min	Max	Min	Max	Min	Max	small pack	standard
STD120	1	19.9	22.1	4.9	5.2	0.6	1.0	5.5	3.9	4.1		500	10,000
STD120S	2	19.9	22.1	4.9	5.2	0.6	1.0	5.5	3.9	4.1		500	10,000
STD175	1	20.9	23.1	4.9	5.2	0.6	1.0	4.1	3.9	4.1		500	10,000
STD175S	2	20.9	23.1	4.9	5.2	0.6	1.0	4.1	3.8	4.2		500	10,000
STD200	1	23.3	23.4	10.2	11.0	0.5	1.1	5.0	4.8	5.4		500	10,000
STD350	1	28.4	31.8	13.0	13.5	0.5	1.1	6.3	6.0	6.6		500	5,000
STD420	1	30.6	32.4	12.9	13.6	0.5	1.1	5.0	5.0	6.7		500	5,000

Permissible continuous operating current is ≤ 100 % at ambient temperature of 20 °C (68 °F).											
Model	I <sub>hold</sub> (A)	I <sub>Trip</sub> (A)	V <sub>max. dc</sub> (V)	I <sub>max.</sub> (A)	max. time to trip (s @ A)	P <sub>d max.</sub> (W)	Resistance			Approvals	
							R <sub>min.</sub> (Ω)	R <sub>max.</sub> (Ω)	R <sub>I max.</sub> (Ω)	cULus TÜV	
STD120	1.20A	2.7	15V	100	5.00 @ 6.00	1.20	0.085	0.160	0.220	• •	
STD120S	1.20A	2.7	15V	100	5.00 @ 6.00	1.20	0.085	0.160	0.220	• •	
STD175	1.75A	3.8	15V	100	5.00 @ 8.75	1.50	0.050	0.090	0.120	• •	
STD175S	1.75A	3.8	15V	100	5.00 @ 8.75	1.50	0.050	0.090	0.120	• •	
STD200	2.00A	4.4	24V	100	4.00 @ 10.00	1.90	0.030	0.060	0.100	• •	
STD350	3.50A	6.3	24V	100	3.00 @ 20.00	2.50	0.017	0.031	0.050	• •	
STD420	4.20A	7.6	24V	100	6.00 @ 20.00	2.90	0.012	0.024	0.040	• •	

NOTE:


I<sub>hold</sub> = Hold current: maximum current device will pass without tripping in 20 °C still air.  
 I<sub>Trip</sub> = Trip current: minimum current at which the device will trip in 20 °C still air.  
 V<sub>max.</sub> = Maximum voltage device can withstand without damage at rated current (I<sub>max.</sub>)  
 I<sub>max.</sub> = Maximum fault current device can withstand without damage at rated voltage (V<sub>max.</sub>)

P<sub>d</sub> = Power dissipated from device when in the tripped state at 20 °C still air.  
 R<sub>min.</sub> = Minimum resistance of device in initial (un-soldered) state.  
 R<sub>I max.</sub> = Maximum resistance of device at 20 °C measured one hour after tripping for 20 s.  
**Caution: Operation beyond the specified rating may result in damage and possible arcing and flame. Specifications are subject to change without notice**

Order Information

Qty.	Order-Number	Model	Packaging

## STD



- A: STD120
- B: STD175
- C: STD200
- D: STD350
- E: STD420

Further Time-Current-Curves on request

## Thermal Derating Chart

Model	Ambient Operation Temperature - $I_{hold}$ (A)								
	-40 °C	-20 °C	0 °C	23 °C	40 °C	50 °C	60 °C	70 °C	85 °C
STD120	1.90	1.70	1.50	1.20	1.00	0.90	0.80	0.70	0.50
STD120S	1.90	1.70	1.50	1.20	1.00	0.90	0.80	0.70	0.50
STD175	2.50	2.30	2.00	1.75	1.50	1.30	1.20	1.10	0.90
STD175S	2.50	2.30	2.00	1.75	1.50	1.30	1.20	1.10	0.90
STD200	3.20	2.80	2.50	2.00	1.70	1.60	1.40	1.20	0.90
STD350	5.40	4.80	4.30	3.50	3.00	2.80	2.50	2.20	1.70
STD420	6.40	5.70	5.10	4.20	3.60	3.30	3.00	2.60	2.10