


X2PT IGBT Module

$$\begin{aligned} V_{CES} &= 1200 \text{ V} \\ I_{C25} &= 325 \text{ A} \\ V_{CE(sat)} &= 1.7 \text{ V} \end{aligned}$$


6-Pack + NTC

Part number

MIXG240W1200TEH



 E72873



Features / Advantages:

- X2PT - 2nd generation Xtreme light Punch Through
- $T_{vj} = 175^{\circ}\text{C}$
- Easy paralleling due to the positive temperature coefficient of the on-state voltage
- Rugged X2PT design results in:
 - short circuit rated for 10 μsec .
 - very low gate charge
 - low EMI
 - square RBSOA @ $2 \times I_c$
- Low $V_{CE(sat)}$ and low thermal resistance
- SONICTM diode
 - fast and soft reverse recovery
 - low operating forward voltage

Applications:

- AC motor drives
- Solar inverter
- Medical equipment
- Uninterruptible power supply
- Air-conditioning systems
- Welding equipment
- Switched-mode and resonant-mode power supplies
- Inductive heating, cookers
- Pumps, Fans

Package: E3-Pack

- Isolation Voltage: 4300 V~
- Industry standard outline
- RoHS compliant
- Base plate: Copper internally DCB isolated
- Advanced power cycling
- Solder pins

Option:

- Phase Change Material printed on base plate

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.




Inverter IGBT T1 - T6				Ratings			
Symbol	Definitions	Conditions	min.	typ.	max.		
V_{CES}	collector emitter voltage	$T_{VJ} = 25^{\circ}\text{C}$			1200	V	
V_{GES}	max. DC gate voltage		-20		+20	V	
V_{GEM}	max. transient gate emitter voltage		-30		+30	V	
I_{C25}	collector current	$T_C = 25^{\circ}\text{C}$			325	A	
I_{C80}	on die level	$T_C = 80^{\circ}\text{C}$			243	A	
I_{C100}		$T_C = 100^{\circ}\text{C}$			208	A	
P_{tot}	total power dissipation	$T_C = 25^{\circ}\text{C}$			1000	W	
$V_{CE(sat)}$	collector emitter saturation voltage on die level	$I_C = 200\text{ A}; V_{GE} = 15\text{ V}$ $T_{VJ} = 25^{\circ}\text{C}$ $T_{VJ} = 150^{\circ}\text{C}$		1.7 2	2	V	V
$V_{GE(th)}$	gate emitter threshold voltage	$I_C = 8\text{ mA}; V_{GE} = V_{GE}$ $T_{VJ} = 25^{\circ}\text{C}$	5.5		7.5	V	
I_{CES}	collector emitter leakage current	$V_{CE} = V_{CES}; V_{GE} = 0\text{ V}$ $T_{VJ} = 25^{\circ}\text{C}$ $T_{VJ} = 150^{\circ}\text{C}$		5	0.6	mA	mA
I_{GES}	gate emitter leakage current	$V_{GE} = \pm 20\text{ V}$			500	nA	
R_G	internal gate resistance			5.6		Ω	
C_{iss}	input capacitance	$V_{CE} = 100\text{ V}; V_{GS} = 0\text{ V}; f = 1\text{ MHz}$		10.6		nF	
C_{oss}	output capacitance					pF	
C_{rss}	reverse transfer (Miller) capacitance					pF	
Q_g	total gate charge	$V_{CE} = 600\text{ V}; V_{GE} = 15\text{ V}; I_C = 200\text{ A}$		630		nC	
Q_{gs}	gate source charge					nC	
Q_{gd}	gate drain (Miller) charge					nC	
$t_{d(on)}$	turn-on delay time	Inductive switching $V_{CE} = 600\text{ V}; I_C = 200\text{ A}$ $V_{GE} = \pm 15\text{ V}; R_G = 3.9\text{ }\Omega$ (external) $T_{VJ} = 25^{\circ}\text{C}$		170		ns	
t_r	current rise time			54		ns	
$t_{d(off)}$	turn-off delay time			298		ns	
t_f	current fall time			138		ns	
E_{on}	turn-on energy per pulse			15.5		mJ	
E_{off}	turn-off energy per pulse			16.1		mJ	
$E_{rec(off)}$	reverse recovery losses at turn-off			4.7		mJ	
$t_{d(on)}$	turn-on delay time	Inductive switching $V_{CE} = 600\text{ V}; I_C = 200\text{ A}$ $V_{GE} = \pm 15\text{ V}; R_G = 3.9\text{ }\Omega$ (external) $T_{VJ} = 100^{\circ}\text{C}$		176		ns	
t_r	current rise time			64		ns	
$t_{d(off)}$	turn-off delay time			336		ns	
t_f	current fall time			188		ns	
E_{on}	turn-on energy per pulse			19.6		mJ	
E_{off}	turn-off energy per pulse			19.7		mJ	
$E_{rec(off)}$	reverse recovery losses at turn-off			7.7		mJ	
$t_{d(on)}$	turn-on delay time	Inductive switching $V_{CE} = 600\text{ V}; I_C = 200\text{ A}$ $V_{GE} = \pm 15\text{ V}; R_G = 3.9\text{ }\Omega$ (external) $T_{VJ} = 150^{\circ}\text{C}$		182		ns	
t_r	current rise time			66		ns	
$t_{d(off)}$	turn-off delay time			366		ns	
t_f	current fall time			232		ns	
E_{on}	turn-on energy per pulse			21.4		mJ	
E_{off}	turn-off energy per pulse			22.0		mJ	
$E_{rec(off)}$	reverse recovery losses at turn-off			10.3		mJ	
RBSOA	reverse bias safe operating area	$V_{GE} = \pm 15\text{ V}; R_G = 3.9\text{ }\Omega$ $V_{CEmax} = 1200\text{ V}$ $T_{VJ} = 150^{\circ}\text{C}$			400	A	
SCSOA	short circuit safe operating area	$V_{CEmax} = 1200\text{ V}$ $T_{VJ} = 150^{\circ}\text{C}$			10	μs	
t_{SC}	short circuit duration	$V_{CE} = 900\text{ V}; V_{GE} = \pm 15\text{ V}$ non-repetitive		900		A	
I_{SC}	short circuit duration						
R_{thJC}	thermal resistance junction to case	with heatsink compound; IXYS test setup		0.195	0.15	K/W	
R_{thJH}	thermal resistance junction to heatsink					K/W	



Inverter Diode D1 - D6				Ratings			
Symbol	Definitions	Conditions		min.	typ.	max.	
V_{RRM}	max. repetitive reverse voltage	$T_{VJ} = 25^{\circ}\text{C}$				1200	V
I_{F25}	forward current	$T_C = 25^{\circ}\text{C}$				235	A
I_{F80}	on die level	$T_C = 80^{\circ}\text{C}$				170	A
I_{F100}		$T_C = 100^{\circ}\text{C}$				145	A
V_F	forward voltage on die level	$I_F = 200\text{ A}$	$T_{VJ} = 25^{\circ}\text{C}$ $T_{VJ} = 150^{\circ}\text{C}$		1.9 1.9	2.2	V V
I_R	reverse current * not applicable, see Ices at IGBT	$V_R = V_{RRM}$	$T_{VJ} = 25^{\circ}\text{C}$ $T_{VJ} = 150^{\circ}\text{C}$		*	*	mA mA
di/dt	rate of change of current	$V_{CE} = 600\text{ V}; I_C = 200\text{ A}$ $V_{GE} = \pm 15\text{ V}; R_G = 3.9\ \Omega$ (external)	$T_{VJ} = 25^{\circ}\text{C}$		3300		A/ μs
Q_{RM}	reverse recovery charge				13		μC
I_{RM}	max. reverse recovery current				129		A
t_{rr}	reverse recovery time				286		ns
E_{rec}	reverse recovery energy				4.7		mJ
di/dt	rate of change of current	$V_{CE} = 600\text{ V}; I_C = 200\text{ A}$ $V_{GE} = \pm 15\text{ V}; R_G = 3.9\ \Omega$ (external)	$T_{VJ} = 100^{\circ}\text{C}$		3080		A/ μs
Q_{RM}	reverse recovery charge				20.4		μC
I_{RM}	max. reverse recovery current				145		A
t_{rr}	reverse recovery time				384		ns
E_{rec}	reverse recovery energy				7.7		mJ
di/dt	rate of change of current	$V_{CE} = 600\text{ V}; I_C = 200\text{ A}$ $V_{GE} = \pm 15\text{ V}; R_G = 3.9\ \Omega$ (external)	$T_{VJ} = 150^{\circ}\text{C}$		2715		A/ μs
Q_{RM}	reverse recovery charge				27		μC
I_{RM}	max. reverse recovery current				158		A
t_{rr}	reverse recovery time				458		ns
E_{rec}	reverse recovery energy				10.3		mJ
R_{thJC}	thermal resistance junction to case	with heatsink compound; IXYS test setup				0.28	K/W
R_{thJH}	thermal resistance junction to heatsink				0.37		K/W



Package E3-Pack				Ratings		
Symbol	Definitions	Conditions	min.	typ.	max.	Unit
I_{RMS}	RMS current	per terminal			30	A
T_{stg}	storage temperature		-40		125	°C
T_{op}	operation temperature		-40		150	°C
T_{VJ}	virtual junction temperature		-40		175	°C
Weight				295		g
M_D	mounting torque		3		6	Nm
d_{Spp}	creepage distance on surface	terminal to terminal	6			mm
d_{Spb}		terminal to backside	12			mm
d_{App}	striking distance through air	terminal to terminal	6			mm
d_{Apb}		terminal to backside	12			mm
V_{ISOL}	isolation voltage	t = 1 second t = 1 minute	4300 3600			V V
$R_{pin-chip}$	resistance pin to chip	$V = V_{CEsat} + 2 \cdot R \cdot I_C$ resp. $V = V_F + 2 \cdot R \cdot I_F$			1.5	mΩ
C_P	coupling capacity per switch	between shorted pins of switch and back side metallization				pF



Part number


M = Module
I = IGBT
X = XPT IGBT
G = Gen 2 / std
240 = Current Rating [A]
W = 6-pack
1200 = Reverse Voltage [V]
T = Thermistor
EH = E3-Pack


Ordering	Part Name	Marking on Product	Delivering Mode	Base Qty	Ordering Code
Standard	MIXG240W1200TEH	MIXG240W1200TEH	Box	5	517094
with Phase Change Material	MIXG240W1200TEH -PC	MIXG240W1200TEH	Blister	24	

Similar Part	Package	Voltage class
MIXG240W1200PTEH	E3- Pack, press fit pin	1200
MIXG240W1200PSTEh	E3- Pack, press fit pin + shunt	1200
MIXG240W1200STEh	E3- Pack, shunt	1200

Option: phase change material; please contact IXYS sales office for availability

Temperature Sensor NTC						
Symbol	Definitions	Conditions	min.	typ.	max.	Unit
R_{25}	resistance	$T_{VJ} = 25^{\circ}\text{C}$	4.75	5.0	5.25	kΩ
$B_{25/50}$	temperature coefficient			3375		K
Equivalent Circuits for Simulation *on die level						
			IGBT	Inverter Diode		
$V_{0\max}$	threshold voltage	$T_{VJ} = 175^{\circ}\text{C}$	1.2	1.2		V
$R_{0\max}$	slope resistance *		5.8	4.7		mΩ




Outlines E3-Pack

Bemerkung / Note:

- Nichttolerierete Maße nach / Measure without tolerances according DIN ISO 2768-T1-m
- PCB-Lochmuster / PCB hole pattern: **see pin position**
- Toleranz Pin-Position und PCB-Lochmuster / Tolerance of pin position and PCB hole pattern: $\oplus 0.1$
- Montageanleitung / Mounting instruction: www.ixys.com **Application note IXAN0024**

Detail A: PCB-Montage / Mounting on PCB

- Empfohlene, selbstschneidende Schraube / Recommended, self-tapping screw: **EJOT PT®** (Größe / size: **K25**)
- Max. Schraubenlänge / Max. screw length: **PCB-Dicke / thickness + 6 mm** (max. Lochtiefe / hole depth)
- Empfohlenes Drehmoment / Recommended mounting torque: **1.5 Nm**








IGBT T1 - T6

 Fig. 1 Typ. output characteristics ($T_{VJ} = 25^\circ\text{C}$)

 Fig. 2 Typ. output characteristics ($T_{VJ} = 150^\circ\text{C}$)

 Fig. 3 Typ. output characteristics ($V_{GE} = 15\text{ V}$)

 Fig. 4 Typ. transfer characteristics ($V_{CE} = 20\text{ V}$)


Fig. 5 Typ. turn-on gate charge 0/15V










Fig. 6 Typ. turn-on gate charge -15/+15V

IGBT T1 - T6




IGBT T1 - T6




Fig. 13 Typ. switching energy versus gate resistor (turn off)




Fig. 14 Typ. switching energy versus gate resistor (turn off)




Fig. 15 IGBT: Typ. transient thermal impedance junction to heat sink






DIODE D1 - D6

 Fig. 16 Typ. reverse recovery characteristics versus diode current I_F

 Fig. 17 Typ. reverse recovery characteristics versus diode current I_F

 Fig. 18 Typ. reverse recovery characteristics versus $-di_F/dt$

 Fig. 19 Typ. reverse recovery characteristics versus $-di_F/dt$


Fig. 20 Typ. forward characteristics of free wheeling diode




Fig. 21 Diode: Typ. transient thermal impedance junction to heat sink