

HiPerFRED


V_{RRM}	=	600 V
I_{FAV}	=	30 A
t_{rr}	=	35 ns

High Performance Fast Recovery Diode
 Low Loss and Soft Recovery
 Single Diode


Part number

DSEP29-06AS

Marking on Product: DSEP29-06AS



Backside: cathode



Features / Advantages:

- Planar passivated chips
- Very low leakage current
- Very short recovery time
- Improved thermal behaviour
- Very low I_{rm} -values
- Very soft recovery behaviour
- Avalanche voltage rated for reliable operation
- Soft reverse recovery for low EMI/RFI
- Low I_{rm} reduces:
 - Power dissipation within the diode
 - Turn-on loss in the commutating switch

Applications:

- Antiparallel diode for high frequency switching devices
- Antisaturation diode
- Snubber diode
- Free wheeling diode
- Rectifiers in switch mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)

Package: TO-263 (D2Pak)

- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0


Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

Fast Diode				Ratings				
Symbol	Definition	Conditions		min.	typ.	max.	Unit	
V _{RSM}	max. non-repetitive reverse blocking voltage	T _{VJ} = 25°C				600	V	
V _{RRM}	max. repetitive reverse blocking voltage	T _{VJ} = 25°C				600	V	
I _R	reverse current, drain current	V _R = 600 V	T _{VJ} = 25°C			250	μA	
		V _R = 600 V	T _{VJ} = 150°C			1	mA	
V _F	forward voltage drop	I _F = 30 A	T _{VJ} = 25°C			1.61	V	
		I _F = 60 A				1.94	V	
		I _F = 30 A	T _{VJ} = 150°C			1.26	V	
		I _F = 60 A				1.56	V	
I _{FAV}	average forward current	T _C = 135°C rectangular d = 0.5	T _{VJ} = 175°C			30	A	
V _{F0}	threshold voltage	} for power loss calculation only		T _{VJ} = 175°C		0.91	V	
r _F	slope resistance					9.4	mΩ	
R _{thJC}	thermal resistance junction to case					0.9	K/W	
R _{thCH}	thermal resistance case to heatsink				0.25		K/W	
P _{tot}	total power dissipation	T _C = 25°C				165	W	
I _{FSM}	max. forward surge current	t = 10 ms; (50 Hz), sine; V _R = 0 V		T _{VJ} = 45°C		250	A	
C _J	junction capacitance	V _R = 400 V f = 1 MHz		T _{VJ} = 25°C	26		pF	
I _{RM}	max. reverse recovery current	} I _F = 30 A; V _R = 300 V -di _F /dt = 200 A/μs		T _{VJ} = 25 °C	6		A	
				T _{VJ} = 100 °C	10		A	
t _{rr}	reverse recovery time			T _{VJ} = 25 °C	35		ns	
				T _{VJ} = 100 °C	100		ns	

Package TO-263 (D2Pak)			Ratings			
Symbol	Definition	Conditions	min.	typ.	max.	Unit
I_{RMS}	RMS current	per terminal			35	A
T_{VJ}	virtual junction temperature		-55		175	°C
T_{op}	operation temperature		-55		150	°C
T_{stg}	storage temperature		-55		150	°C
Weight				1.5		g
F_c	mounting force with clip		20		60	N

Product Marking



Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	DSEP29-06AS-TRL	DSEP29-06AS	Tape & Reel	800	499498
Alternative	DSEP29-06AS-TUB	DSEP29-06AS	Tube	50	473537


Similar Part	Package	Voltage class
DSEP29-06A	TO-220AC (2)	600
DSEP30-06A	TO-247AD (2)	600
DSEP30-06B	TO-247AD (2)	600
DSEP30-06BR	ISOPLUS247 (2)	600

DHG30I600PA	TO-220AC (2)	600
DHG30I600HA	TO-247AD (2)	600
DHG30IM600PC	TO-263AB (D2Pak) (2)	600

Equivalent Circuits for Simulation

* on die level

$T_{VJ} = 175^{\circ}\text{C}$



Fast Diode

$V_{0\max}$ threshold voltage


0.91

V

$R_{0\max}$ slope resistance *


6.1

mΩ

Outlines TO-263 (D2Pak)


Dim.	Millimeter		Inches	
	min	max	min	max
A	4.06	4.83	0.160	0.190
A1	typ. 0.10		typ. 0.004	
A2	2.41		0.095	
b	0.51	0.99	0.020	0.039
b2	1.14	1.40	0.045	0.055
c	0.40	0.74	0.016	0.029
c2	1.14	1.40	0.045	0.055
D	8.38	9.40	0.330	0.370
D1	8.00	8.89	0.315	0.350
D2	2.5		0.098	
E	9.65	10.41	0.380	0.410
E1	6.22	8.50	0.245	0.335
e	2.54 BSC		0.100 BSC	
e1	4.28		0.169	
H	14.61	15.88	0.575	0.625
L	1.78	2.79	0.070	0.110
L1	1.02	1.68	0.040	0.066
W	typ. 0.02	0.040	typ. 0.0008	0.002

All dimensions conform with and/or within JEDEC standard.




Fast Diode


Fig. 1 Forward current
 I_F versus V_F




Fig. 2 Typ. reverse recov. charge
 Q_r versus $-di_F/dt$




Fig. 3 Typ. peak reverse current
 I_{RM} versus $-di_F/dt$




Fig. 4 Dynamic parameters
 Q_r , I_{RM} versus T_{VJ}




Fig. 5 Typ. recovery time
 t_{rr} versus $-di_F/dt$




Fig. 6 Typ. peak forward voltage
 V_{FR} and t_{fr} versus di_F/dt




Fig. 7 Transient thermal impedance junction to case

Constants for Z_{thJC} calculation:

i	R_{thi} (K/W)	t_i (s)
1	0.030	0.001
2	0.080	0.030
3	0.300	0.006
4	0.490	0.060