
XPT™ 650V IGBT GenX4™

IXXH110N65C4

V_{CES} = 650V
I_{C110} = 110A
$V_{CE(sat)}$ ≤ 2.35V
$t_{fi(typ)}$ = 35ns


Extreme Light Punch Through
IGBT for 20-60 kHz Switching



Symbol	Test Conditions	Maximum Ratings	
V_{CES}	T_J = 25°C to 175°C	650	V
V_{CGR}	T_J = 25°C to 175°C, R_{GE} = 1MΩ	650	V
V_{GES}	Continuous	±20	V
V_{GEM}	Transient	±30	V
I_{C25}	T_C = 25°C (Chip Capability)	235	A
I_{LRMS}	Terminal Current Limit	160	A
I_{C110}	T_C = 110°C	110	A
I_{CM}	T_C = 25°C, 1ms	600	A
SSOA (RBSOA)	V_{GE} = 15V, T_{VJ} = 150°C, R_G = 2Ω Clamped Inductive Load	I_{CM} = 220 @$V_{CE} \leq V_{CES}$	A
t_{sc} (SCSOA)	V_{GE} = 15V, V_{CE} = 360V, T_J = 150°C R_G = 10Ω, Non Repetitive	10	μs
P_C	T_C = 25°C	880	W
T_J		-55 ... +175	°C
T_{JM}		175	°C
T_{stg}		-55 ... +175	°C
T_L	Maximum Lead Temperature for Soldering	300	°C
T_{SOLD}	1.6 mm (0.062in.) from Case for 10s	260	°C
M_d	Mounting Torque	1.13/10	Nm/lb.in.
Weight		6	g

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
BV_{CES}	I_C = 250μA, V_{GE} = 0V	650			V
$V_{GE(th)}$	I_C = 4mA, V_{CE} = V_{GE}	4.0		6.5	V
I_{CES}	V_{CE} = V_{CES}, V_{GE} = 0V			10	μA
	T_J = 150°C			500	μA
I_{GES}	V_{CE} = 0V, V_{GE} = ±20V			±100	nA
$V_{CE(sat)}$	I_C = 110A, V_{GE} = 15V, Note 1		2.06	2.35	V
	T_J = 150°C		2.50		V

TO-247 AD



G = Gate C = Collector
E = Emitter Tab = Collector

Features

- Optimized for 20-60kHz Switching
- Square RBSOA
- Avalanche Capability
- Short Circuit Capability
- International Standard Package

Advantages

- High Power Density
- 175°C Rated
- Extremely Rugged
- Low Gate Drive Requirement


Applications

- UPS
- Motor Drives
- SMPS
- PFC Circuits
- Battery Chargers
- Welding Machines
- Lamp Ballasts
- High Frequency Power Inverters

© 2016 IXYS CORPORATION, All Rights Reserved

Symbol	Test Conditions (T_J = 25°C Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	I_C = 60A, V_{CE} = 10V, Note 1	30	52		S
C_{ies}	V_{CE} = 25V, V_{GE} = 0V, f = 1MHz		5500		pF
C_{oes}			267		pF
C_{res}			80		pF
$Q_{g(on)}$	I_C = 110A, V_{GE} = 15V, V_{CE} = 0.5 • V_{CES}		167		nC
Q_{ge}			44		nC
Q_{gc}			63		nC
$t_{d(on)}$	**Inductive load, T_J = 25°C**		30		ns
t_{ri}	I_C = 55A, V_{GE} = 15V		45		ns
E_{on}	V_{CE} = 400V, R_G = 2Ω		2.50		mJ
$t_{d(off)}$	Note 2		110		ns
t_{fi}			35		ns
E_{off}			0.63	1.05	mJ
$t_{d(on)}$	**Inductive load, T_J = 150°C**		26		ns
t_{ri}	I_C = 55A, V_{GE} = 15V		45		ns
E_{on}	V_{CE} = 400V, R_G = 2Ω		3.55		mJ
$t_{d(off)}$	Note 2		120		ns
t_{fi}			40		ns
E_{off}			0.90		mJ
R_{thJC}				0.17	°C/W
R_{thCS}			0.21		°C/W

TO-247 (IXXH) Outline



Terminals: 1 - Gate 2 - Collector
3 - Emitter

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.7	5.3	.185	.209
A_1	2.2	2.54	.087	.102
A_2	2.2	2.6	.059	.098
b	1.0	1.4	.040	.055
b_1	1.65	2.13	.065	.084
b_2	2.87	3.12	.113	.123
C	.4	.8	.016	.031
D	20.80	21.46	.819	.845
E	15.75	16.26	.610	.640
e	5.20	5.72	0.205	0.225
L	19.81	20.32	.780	.800
L1		4.50		.177
∅P	3.55	3.65	.140	.144
Q	5.89	6.40	0.232	0.252
R	4.32	5.49	.170	.216
S	6.15 BSC		242 BSC	

Notes:

1. Pulse test, t ≤ 300µs, duty cycle, d ≤ 2%.
2. Switching times & energy losses may increase for higher V_{CE}(clamp), T_J or R_G.

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,860,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2 7,005,734 B2 7,063,975 B2 7,071,537 7,157,338B2

Fig. 1. Output Characteristics @ T_J = 25ºC




Fig. 2. Extended Output Characteristics @ T_J = 25ºC




Fig. 3. Output Characteristics @ T_J = 150ºC




Fig. 4. Dependence of $V_{CE(sat)}$ on Junction Temperature




Fig. 5. Collector-to-Emitter Voltage vs. Gate-to-Emitter Voltage





Fig. 6. Input Admittance



© 2016 IXYS CORPORATION, All Rights Reserved

Fig. 7. Transconductance




Fig. 8. Gate Charge




Fig. 9. Capacitance




Fig. 10. Reverse-Bias Safe Operating Area





Fig. 11. Maximum Transient thermal Impedance



IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

Fig. 12. Inductive Switching Energy Loss vs. Gate Resistance




Fig. 13. Inductive Switching Energy Loss vs. Collector Current




Fig. 14. Inductive Switching Energy Loss vs. Junction Temperature




Fig. 15. Inductive Turn-off Switching Times vs. Gate Resistance




Fig. 16. Inductive Turn-off Switching Times vs. Collector Current





Fig. 17. Inductive Turn-off Switching Times vs. Junction Temperature



© 2016 IXYS CORPORATION, All Rights Reserved

Fig. 18. Inductive Turn-on Switching Times vs. Gate Resistance




Fig. 19. Inductive Turn-on Switching Times vs. Collector Current





Fig. 20. Inductive Turn-on Switching Times vs. Junction Temperature



IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.