

HiPerFRED

$$V_{RRM} = 400 \text{ V}$$

$$I_{FAV} = 2 \times 120 \text{ A}$$

$$t_{rr} = 30 \text{ ns}$$

High Performance Fast Recovery Diode
 Low Loss and Soft Recovery
 Parallel legs


Part number

DPF240X400NA



Backside: isolated

 E72873



Features / Advantages:

- Planar passivated chips
- Very low leakage current
- Very short recovery time
- Improved thermal behaviour
- Very low I_{rm} -values
- Very soft recovery behaviour
- Avalanche voltage rated for reliable operation
- Soft reverse recovery for low EMI/RFI
- Low I_{rm} reduces:
 - Power dissipation within the diode
 - Turn-on loss in the commutating switch

Applications:

- Antiparallel diode for high frequency switching devices
- Antisaturation diode
- Snubber diode
- Free wheeling diode
- Rectifiers in switch mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)

Package: SOT-227B (minibloc)

- Isolation Voltage: 3000 V~
- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0
- Base plate: Copper internally DCB isolated
- Advanced power cycling

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

Fast Diode				Ratings				
Symbol	Definition	Conditions		min.	typ.	max.	Unit	
V _{RSM}	max. non-repetitive reverse blocking voltage	T _{VJ} = 25°C				400	V	
V _{RRM}	max. repetitive reverse blocking voltage	T _{VJ} = 25°C				400	V	
I _R	reverse current, drain current	V _R = 400 V	T _{VJ} = 25°C			10	μA	
		V _R = 400 V	T _{VJ} = 150°C			0.5	mA	
V _F	forward voltage drop	I _F = 120 A	T _{VJ} = 25°C			1.25	V	
		I _F = 240 A				1.54	V	
		I _F = 120 A	T _{VJ} = 150°C			1.06	V	
		I _F = 240 A				1.42	V	
I _{FAV}	average forward current	T _C = 70°C rectangular d = 0.5	T _{VJ} = 150°C			120	A	
V _{F0}	threshold voltage	} for power loss calculation only		T _{VJ} = 150°C		0.71	V	
r _F	slope resistance					2.9	mΩ	
R _{thJC}	thermal resistance junction to case					0.5	K/W	
R _{thCH}	thermal resistance case to heatsink				0.1		K/W	
P _{tot}	total power dissipation	T _C = 25°C				250	W	
I _{FSM}	max. forward surge current	t = 10 ms; (50 Hz), sine; V _R = 0 V		T _{VJ} = 45°C		1.20	kA	
C _J	junction capacitance	V _R = 200 V f = 1 MHz		T _{VJ} = 25°C	187		pF	
I _{RM}	max. reverse recovery current	} I _F = 120 A; V _R = 240 V -di _F /dt = 200 A/μs		T _{VJ} = 25 °C	7		A	
				T _{VJ} = 125 °C	18		A	
t _{rr}	reverse recovery time			T _{VJ} = 25 °C	30		ns	
				T _{VJ} = 125 °C	140		ns	

Package SOT-227B (minibloc)				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
I_{RMS}	RMS current	per terminal				150	A
T_{VJ}	virtual junction temperature			-40		150	°C
T_{op}	operation temperature			-40		125	°C
T_{stg}	storage temperature			-40		150	°C
Weight					30		g
M_D	mounting torque			1.1		1.5	Nm
M_T	terminal torque			1.1		1.5	Nm
$d_{Spp/App}$	creepage distance on surface striking distance through air	terminal to terminal	10.5	3.2			mm
$d_{Spb/Apb}$		terminal to backside	8.6	6.8			mm
V_{ISOL}	isolation voltage	t = 1 second	50/60 Hz, RMS; $I_{ISOL} \leq 1$ mA	3000			V
		t = 1 minute		2500			V



Part description


D = Diode
 P = HiPerFRED
 F = ultra fast
 240 = Current Rating [A]
 X = Parallel legs
 400 = Reverse Voltage [V]
 NA = SOT-227B (minibloc)

Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	DPF240X400NA	DPF240X400NA	Tube	10	499554

Equivalent Circuits for Simulation

* on die level

$T_{VJ} = 150^{\circ}\text{C}$



Outlines SOT-227B (minibloc)


Dim.	Millimeter		Inches	
	min	max	min	max
A	31.50	31.88	1.240	1.255
B	7.80	8.20	0.307	0.323
C	4.09	4.29	0.161	0.169
D	4.09	4.29	0.161	0.169
E	4.09	4.29	0.161	0.169
F	14.91	15.11	0.587	0.595
G	30.12	30.30	1.186	1.193
H	37.80	38.23	1.488	1.505
J	11.68	12.22	0.460	0.481
K	8.92	9.60	0.351	0.378
L	0.74	0.84	0.029	0.033
M	12.50	13.10	0.492	0.516
N	25.15	25.42	0.990	1.001
O	1.95	2.13	0.077	0.084
P	4.95	6.20	0.195	0.244
Q	26.54	26.90	1.045	1.059
R	3.94	4.42	0.155	0.167
S	4.55	4.85	0.179	0.191
T	24.59	25.25	0.968	0.994
U	-0.05	0.10	-0.002	0.004
V	3.20	5.50	0.126	0.217
W	19.81	21.08	0.780	0.830
Z	2.50	2.70	0.098	0.106




Fast Diode


Fig. 1 Forward current
 I_F vs. V_F




Fig. 2 Typ. reverse recovery charge
 Q_{rr} vs. $-di_F/dt$




Fig. 3 Typ. reverse recovery current
 I_{RM} vs. $-di_F/dt$




Fig. 4 Typ. dynamic parameters
 Q_{rr} , I_{RM} vs. T_{VJ}




Fig. 5 Typ. reverse recovery time
 t_{rr} vs. $-di_F/dt$




Fig. 6 Typ. forward recovery voltage
 V_{FR} & t_{fr} vs. di_F/dt




Fig. 7 Typ. recovery energy
 E_{rec} vs. $-di_F/dt$




Fig. 8 Transient thermal impedance junction to case