IXYS

HiPerFET™ Power MOSFETs Q-CLASS


IXFK 27N80Q
IXFX 27N80Q

V_{DSS} = 800 V
I_{D25} = 27 A
$R_{DS(on)}$ = 320 mΩ

$t_{rr} \leq$ 250 ns


Single MOSFET Die

N-Channel Enhancement Mode
Avalanche Rated, Low Qg,
High dV/dt, Low t_{rr}




Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 150°C	800	V
V_{DGR}	T_J = 25°C to 150°C; R_{GS} = 1 MΩ	800	V
V_{GS}	Continuous	±20	V
V_{GSM}	Transient	±30	V
I_{D25}	T_C = 25°C	27	A
I_{DM}	T_C = 25°C, pulse width limited by T_{JM}	108	A
I_{AR}	T_C = 25°C	27	A
E_{AR}	T_C = 25°C	60	mJ
E_{AS}	T_C = 25°C	2.5	J
dv/dt	$I_S \leq I_{DM}$, di/dt ≤ 100 A/μs, $V_{DD} \leq V_{DSS}$ $T_J \leq$ 150°C, R_G = 2 Ω	5	V/ns
P_D	T_C = 25°C	500	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
T_L	1.6 mm (0.063 in.) from case for 10 s	300	°C
M_d	Mounting torque TO-264	0.4/6	Nm/lb.in.
Weight	PLUS 247	6	g
	TO-264	10	g

PLUS 247™ (IXFX)



TO-264 AA (IXFK)



G = Gate D = Drain
S = Source TAB = Drain

Features
- IXYS advanced low Q_g process
- Low gate charge and capacitances
  - easier to drive
  - faster switching
- International standard packages
- Low $R_{DS\ (on)}$
- Rated for unclamped Inductive load switching (UIS) rated
- Molding epoxies meet UL 94 V-0 flammability classification

Applications
- DC-DC converters
- Battery chargers
- Switched-mode and resonant-mode power supplies
- DC choppers
- AC motor control
- Temperature and lighting controls

Advantages
- PLUS 247™ package for clip or spring mounting
- Space savings
- High power density

Symbol	Test Conditions	Characteristic Values (T_J = 25°C, unless otherwise specified) min.	typ.	max.
V_{DSS}	V_{GS} = 0 V, I_D = 1mA	800		V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 4mA	2.0		4.5 V
I_{GSS}	V_{GS} = ±20 V, V_{DS} = 0			±100 nA
I_{DSS}	$V_{DS} = V_{DSS}$			100 μA
	V_{GS} = 0 V T_J = 125°C			2 mA
$R_{DS(on)}$	V_{GS} = 10 V, $I_D = 0.5 \bullet I_{D25}$ Note 1			320 mΩ

© 2002 IXYS All rights reserved


Symbol	Test Conditions (T$_J$ = 25°C, unless otherwise specified)		Characteristic Values min.	typ.	max.	
g_{fs}	V_{DS} = 10 V; I_D = 0.5 • I_{D25}	Note 1	20	27		S
C_{iss}	V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz			7600		pF
C_{oss}				750		pF
C_{rss}				120		pF
$t_{d(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25} R_G = 1 Ω (External),			20		ns
t_r				28		ns
$t_{d(off)}$				50		ns
t_f				13		ns
$Q_{g(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25}			170		nC
Q_{gs}				47		nC
Q_{gd}				65		nC
R_{thJC}					0.26	K/W
R_{thCK}				0.15		K/W

Source-Drain Diode

Symbol	Test Conditions (T$_J$ = 25°C, unless otherwise specified)	Characteristic Values min.	typ.	max.	
I_S	V_{GS} = 0 V			27	A
I_{SM}	Repetitive; pulse width limited by T_{JM}			108	A
V_{SD}	$I_F = I_S$, V_{GS} = 0 V, Note 1			1.5	V
t_{rr}	$I_F = I_S$,-di/dt = 100 A/µs, V_R = 100 V			250	ns
Q_{RM}			1.3		µC
I_{RM}			8		A

Note: 1. Pulse test, t ≤ 300 µs, duty cycle d ≤ 2 %


PLUS 247™ Outline



Terminals: 1 - Gate
2 - Drain (Collector)
3 - Source (Emitter)
4 - Drain (Collector)

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.83	5.21	.190	.205
A_1	2.29	2.54	.090	.100
A_2	1.91	2.16	.075	.085
b	1.14	1.40	.045	.055
b_1	1.91	2.13	.075	.084
b_2	2.92	3.12	.115	.123
C	0.61	0.80	.024	.031
D	20.80	21.34	.819	.840
E	15.75	16.13	.620	.635
e	5.45 BSC		.215 BSC	
L	19.81	20.32	.780	.800
L1	3.81	4.32	.150	.170
Q	5.59	6.20	.220	0.244
R	4.32	4.83	.170	.190

TO-264 AA Outline



Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.82	5.13	.190	.202
A1	2.54	2.89	.100	.114
A2	2.00	2.10	.079	.083
b	1.12	1.42	.044	.056
b1	2.39	2.69	.094	.106
b2	2.90	3.09	.114	.122
c	0.53	0.83	.021	.033
D	25.91	26.16	1.020	1.030
E	19.81	19.96	.780	.786
e	5.46 BSC		.215 BSC	
J	0.00	0.25	.000	.010
K	0.00	0.25	.000	.010
L	20.32	20.83	.800	.820
L1	2.29	2.59	.090	.102
P	3.17	3.66	.125	.144
Q	6.07	6.27	.239	.247
Q1	8.38	8.69	.330	.342
R	3.81	4.32	.150	.170
R1	1.78	2.29	.070	.090
S	6.04	6.30	.238	.248
T	1.57	1.83	.062	.072

IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETS and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,881,106 5,017,508 5,049,961 5,187,117 5,486,715 6,306,728B1 4,850,072 4,931,844 5,034,796 5,063,307 5,237,481 5,381,025



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.