

AQHVxx-01LTG-C Series

300W Discrete Bidirectional TVS Diode



Web Resources




Download ECAD models, order samples, and find technical resources at www.littelfuse.com

Pinout



This component is bidirectional

Functional Block Diagram



Description

This AQHVxx-01LTG-C series provides a highly effective ESD, EFT, and lightning surge protection component. It is ideally suited for power interfaces, passenger charging interfaces, LED lighting modules, and low speed I/Os.

Its rating of $\pm 30\text{kV}$ ESD exceeds the maximum ESD rating requirements as defined in the IEC 61000-4-2 international standard without suffering any performance degradation. The AQHV12-C can withstand up to 10A of surge current as defined by IEC 61000-4-5 2nd edition providing low voltage clamping levels during lightning induced events.

Features & Benefits

- ESD, IEC 61000-4-2, $\pm 30\text{kV}$ contact, $\pm 30\text{kV}$ air
- EFT, IEC 61000-4-4, 40A (5/50ns)
- Lightning, 10A (8/20 μs as defined in IEC 61000-4-5 2nd edition) for AQHV12-C
- Low clamping voltage
- PPAP capable
- Low leakage current
- AEC-Q101 qualified
- Moisture Sensitivity Level (MSL -1)
- Halogen free, lead free and RoHS compliant

Applications

- LED Lighting Modules
- Portable Instrumentation
- General Purpose I/O
- RS232 / RS485
- CAN and LIN Bus
- Automotive application

Life Support Note:

Not Intended for Use in Life Support or Life Saving Applications

The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.

AQHVxx-01LTG-C Series

300W Discrete Bidirectional TVS Diode

Absolute Maximum Ratings

Symbol	Parameter	Value	Units
P_{pk}	Peak Pulse Power ($t_p=8/20\mu s$)	300	W
T_{OP}	Operating Temperature	-40 to 150	°C
T_{STOR}	Storage Temperature	-55 to 150	°C

Caution: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the component. This is a stress only rating and operation of the component at these or any other conditions above those indicated in the operational sections of this specification is not implied.

AQHV12-C Electrical Characteristics ($T_{OP}=25^\circ C$)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	V_{RWM}	$I_R=1\mu A$	-	-	12	V
Breakdown Voltage	V_{BR}	$I_R=1mA$	13.3	15	-	V
Reverse Leakage Current	I_{LEAK}	$V_R=12V$	-	5	50	nA
Clamp Voltage ¹	V_C	$I_{PP}=1A, t_p=8/20\mu s, I/O$ to I/O	-	18	21	V
		$I_{PP}=10A, t_p=8/20\mu s, I/O$ to I/O	-	27	30	V
Dynamic Resistance ²	R_{DYN}	TLP, $t_p=100ns, I/O$ to I/O	-	0.34	-	Ω
Peak Pulse Current ¹	I_{PP}	$t_p=8/20\mu s$	-	-	10	A
ESD Withstand Voltage ¹	V_{ESD}	IEC 61000-4-2 (Contact Discharge)	± 30	-	-	kV
		IEC 61000-4-2 (Air Discharge)	± 30	-	-	kV
Diode Capacitance ¹	$C_{I/O-I/O}$	Reverse Bias=0V, $f=1MHz$	-	27	30	pF

AQHV15-C Electrical Characteristics ($T_{OP}=25^\circ C$)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	V_{RWM}	$I_R=1\mu A$	-	-	15	V
Breakdown Voltage	V_{BR}	$I_R=1mA$	16.7	19.5	-	V
Reverse Leakage Current	I_{LEAK}	$V_R=15V$	-	5	50	nA
Clamp Voltage ¹	V_C	$I_{PP}=1A, t_p=8/20\mu s, I/O$ to I/O	-	23.5	27	V
		$I_{PP}=7A, t_p=8/20\mu s, I/O$ to I/O	-	33.5	37	V
Dynamic Resistance ²	R_{DYN}	TLP, $t_p=100ns, I/O$ to I/O	-	0.36	-	Ω
Peak Pulse Current ¹	I_{PP}	$t_p=8/20\mu s$	-	-	7	A
ESD Withstand Voltage ¹	V_{ESD}	IEC 61000-4-2 (Contact Discharge)	± 30	-	-	kV
		IEC 61000-4-2 (Air Discharge)	± 30	-	-	kV
Diode Capacitance ¹	$C_{I/O-I/O}$	Reverse Bias=0V, $f=1MHz$	-	21	24	pF

AQHV24-C Electrical Characteristics ($T_{OP}=25^\circ C$)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	V_{RWM}	$I_R=1\mu A$	-	-	24.0	V
Breakdown Voltage	V_{BR}	$I_R=1mA$	26.7	29.5	-	V
Reverse Leakage Current	I_{LEAK}	$V_R=24V$	-	5	50	nA
Clamp Voltage ¹	V_C	$I_{PP}=1A, t_p=8/20\mu s, I/O$ to I/O	-	35.5	40	V
		$I_{PP}=5A, t_p=8/20\mu s, I/O$ to I/O	-	49.5	55	V
Dynamic Resistance ²	R_{DYN}	TLP, $t_p=100ns, I/O$ to I/O	-	0.52	-	Ω
Peak Pulse Current ¹	I_{PP}	$t_p=8/20\mu s$	-	-	5.0	A
ESD Withstand Voltage ¹	V_{ESD}	IEC 61000-4-2 (Contact Discharge)	± 25	-	-	kV
		IEC 61000-4-2 (Air Discharge)	± 30	-	-	kV
Diode Capacitance ¹	$C_{I/O-I/O}$	Reverse Bias=0V, $f=1MHz$	-	15	17	pF

AQHVxx-01LTG-C Series

300W Discrete Bidirectional TVS Diode

AQHV36-C Electrical Characteristics ($T_{OP}=25^{\circ}\text{C}$)


Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	V_{RWM}	$I_R=1\mu\text{A}$			36.0	V
Breakdown Voltage	V_{BR}	$I_R=1\text{mA}$	40	43.5		V
Reverse Leakage Current	I_{LEAK}	$V_R=36\text{V}$		5	50	nA
Clamp Voltage ¹	V_C	$I_{PP}=1\text{A}$, $t_p=8/20\mu\text{s}$, I/O to I/O		52.5	58	V
		$I_{PP}=3\text{A}$, $t_p=8/20\mu\text{s}$, I/O to I/O		67	72	V
Dynamic Resistance ²	R_{DYN}	TLP, $t_p=100\text{ns}$, I/O to I/O		1.27		Ω
Peak Pulse Current ¹	I_{PP}	$t_p=8/20\mu\text{s}$			3.0	A
ESD Withstand Voltage ¹	V_{ESD}	IEC 61000-4-2 (Contact Discharge)	± 15			kV
		IEC 61000-4-2 (Air Discharge)	± 20			kV
Diode Capacitance ¹	$C_{I/O-I/O}$	Reverse Bias=0V, $f=1\text{MHz}$		11.5	13	pF

Notes:


1. Parameter is guaranteed by design and/or component characterization.

2. Transmission Line Pulse (TLP) with 100ns width, 2ns rise time, and average window $t_1=70\text{ns}$ to $t_2=90\text{ns}$


Capacitance vs. Reverse Bias




8/20 μs Pulse Waveform



AQHV12-C Positive Transmission Line Pulsing(TLP) Plot




AQHV12-C Negative Transmission Line Pulsing(TLP) Plot




AQHVxx-01LTG-C Series

300W Discrete Bidirectional TVS Diode


AQHV15-C Positive Transmission Line Pulsing(TLP) Plot




AQHV15-C Negative Transmission Line Pulsing(TLP) Plot




AQHV24-C Positive Transmission Line Pulsing(TLP) Plot




AQHV24-C Negative Transmission Line Pulsing(TLP) Plot



AQHV36-C Positive Transmission Line Pulsing(TLP) Plot



AQHV36-C Negative Transmission Line Pulsing(TLP) Plot



AQHVxx-01LTG-C Series

300W Discrete Bidirectional TVS Diode


AQHV12-C +8kV Contact ESD Clamping Voltage



AQHV12-C -8kV Contact ESD Clamping Voltage



AQHV15-C +8kV Contact ESD Clamping Voltage




AQHV15-C -8kV Contact ESD Clamping Voltage



AQHV24-C +8kV Contact ESD Clamping Voltage



AQHV24-C -8kV Contact ESD Clamping Voltage






AQHVxx-01LTG-C Series

300W Discrete Bidirectional TVS Diode


Part Numbering System



Ordering Information


Part Number	Package	Min. Order Qty.
AQHV12-01LTG-C	SOD523	5000
AQHV15-01LTG-C		
AQHV24-01LTG-C		
AQHV36-01LTG-C		

Package Dimensions — SOD-523



Symbol	Millimeters		Inches	
	Min	Max	Min	Max
A	0.51	0.77	0.020	0.030
A1	0.50	0.70	0.020	0.028
b	0.25	0.35	0.010	0.014
c	0.08	0.15	0.003	0.006
D	0.70	0.90	0.028	0.035
E	1.10	1.30	0.043	0.051
E1	1.50	1.70	0.059	0.067
E2	0.20 REF		0.001 REF	
L	0.01	0.07	0.000	0.003
Θ	7° REF		7° REF	

Embossed Carrier Tape & Reel Specification — SOD-523



Symbol	Millimeters		Inches	
	Min	Max	Min	Max
A0	0.91	1.01	0.036	0.040
B0	1.89	1.99	0.074	0.078
D0	1.50	1.60	0.059	0.063
D1	0.40	0.60	0.016	0.024
E1	1.65	1.85	0.065	0.073
F	3.40	3.60	0.134	0.142
P0	3.90	4.10	0.154	0.161
P	1.90	2.10	0.075	0.083
P1	1.95	2.05	0.077	0.081
K0	0.68	0.78	0.027	0.031
T	0.17	0.23	0.007	0.009
W	7.90	8.30	0.311	0.327

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.