Date:- 11 Dec, 2018

Data Sheet Issue:- 4

Insulated Gate Bi-Polar Transistor

Type T2400GB45E

Absolute Maximum Ratings

	VOLTAGE RATINGS	MAXIMUM LIMITS	UNITS
V_{CES}	Collector – emitter voltage	4500	V
$V_{DC\ link}$	Permanent DC voltage for 100 FIT failure rate.	2800	V
V_{GES}	Peak gate – emitter voltage	±20	V

	RATINGS	MAXIMUM LIMITS	UNITS
I_C	Continuous DC collector current, IGBT	2400	A
I_{CRM}	Repetitive peak collector current, t_p=1ms, IGBT	4800	A
I_{ECO}	Maximum reverse emitter current, t_p=100µs, (note 2 & 3)	2400	A
P_{MAX}	Maximum power dissipation, IGBT (note 2)	19	kW
$T_{j\ op}$	Operating temperature range	-40 to +125	°C
T_{stg}	Storage temperature range	-40 to +125	°C

Notes: -

1) Unless otherwise indicated T_j = 125ºC.
2) T_{sink} = 25°C, double side cooled.
3) Maximum commutation loop inductance 200nH.
4) Half-sinewave, 125°C T_j initial.

Characteristics

IGBT Characteristics

	PARAMETER	MIN	TYP	MAX	TEST CONDITIONS	UNITS
$V_{CE(sat)}$	Collector – emitter saturation voltage	-	2.8	3.2	I_C = 2400A, V_{GE} = 15V, T_j = 25°C	V
		-	3.6	4.0	I_C = 2400A, V_{GE} = 15V	V
V_{T0}	Threshold voltage	-	-	1.49	Current range: 800A – 2400A	V
r_T	Slope resistance	-	-	1.05		mΩ
$V_{GE(TH)}$	Gate threshold voltage	-	5.1	-	V_{CE} = V_{GE}, I_C = 250mA	V
I_{CES}	Collector – emitter cut-off current		45	70	V_{CE} = V_{CES}, V_{GE} = 0V	mA
I_{GES}	Gate leakage current	-	-	±30	V_{GE} = ±20V	µA
C_{ies}	Input capacitance	-	400	-	V_{CE} = 25V, V_{GE} = 0V, f = 1MHz	nF
$t_{d(on)}$	Turn-on delay time	-	1.8	-	I_C =2400A, V_{CE} =2800V, di/dt=4000A/µs V_{GE} = ±15V, L_s=200nH $R_{G(ON)}$= 2.2Ω, $R_{G(OFF)}$=8.2Ω, C_{GE}=267nF Freewheel diode type E2400EC45E at T_j=125°C. (Notes 3, 4 & 5)	µs
t_r(V)	Rise time	-	3.6	-		µs
$Q_{g(on)}$	Turn-on gate charge	-	18	-		µC
E_{on}	Turn-on energy	-	14	-		J
$t_{d(off)}$	Turn-off delay time	-	5.1	-		µs
t_f(I)	Fall time	-	2.4	-		µs
$Q_{g(off)}$	Turn-off gate charge	-	14	-		µC
E_{off}	Turn-off energy	-	13	-		J
I_{SC}	Short circuit current	-	9500	-	V_{GE}=+15V, V_{CC}=2800V, V_{CEmax}≤V_{CES}, t_p≤10µs	A

Thermal Characteristics

	PARAMETER	MIN	TYP	MAX	TEST CONDITIONS	UNITS
R_{thJK}	Thermal resistance junction to sink, IGBT	-	-	5.2	Double side cooled	K/kW
		-	-	8.5	Collector side cooled	K/kW
		-	-	13.5	Emitter side cooled	K/kW
F	Mounting force	50	-	70	Note 2	kN
W_t	Weight	-	2	-		kg

Notes:-
1) Unless otherwise indicated T_j=125°C.
2) Consult application note 2008AN01 for detailed mounting requirements.
3) C_{GE} is additional gate - emitter capacitance added to output of gate drive circuit.
4) E_{on} integration time 15µs from 10% rising I_G.
5) E_{off} integration time 15µs from 90% falling V_{GE}.
6) Freewheeling diode changed from E2400TC45C to E2400EC45E.

Curves

Figure 1 – Typical collector-emitter saturation voltage characteristics




Figure 2 – Typical output characteristic




Figure 3 – Typical output characteristic




Figure 4 – Typical turn-on delay time vs gate resistance




Figure 5 – Typical turn-off delay time vs. gate resistance




Figure 6 – Typical turn-on energy vs. collector current




Figure 7 – Typical turn-on energy vs. di/dt




Figure 8 – Typical turn-off energy vs. collector current




Figure 9 – Turn-off energy vs voltage




Figure 10 – Safe operating area






Figure 11 – Transient thermal impedance



Outline Drawing & Ordering Information



ORDERING INFORMATION			(Please quote 10 digit code as below)
T2400	**GB**	**45**	**E**
Fixed type Code	Fixed Outline Code	Voltage Grade V_{CES}/100 45	Fixed format code
Typical order code: T2400GB45E (V_{CES} = 4500V)			

IXYS Semiconductor GmbH
Edisonstraße 15
D-68623 Lampertheim
Tel: +49 6206 503-0
Fax: +49 6206 503-627
E-mail: marcom@ixys.de

IXYS UK Westcode Ltd
Langley Park Way, Langley Park,
Chippenham, Wiltshire, SN15 1GE.
Tel: +44 (0)1249 444524
E-mail: sales@ixysuk.com

IXYS Corporation
1590 Buckeye Drive
Milpitas CA 95035-7418
Tel: +1 (408) 457 9000
Fax: +1 (408) 496 0670
E-mail: sales@ixys.net

www.littelfuse.com
www.ixysuk.com
www.ixys.net

IXYS Long Beach
IXYS Long Beach, Inc
2500 Mira Mar Ave, Long Beach
CA 90815
Tel: +1 (562) 296 6584
Fax: +1 (562) 296 6585
E-mail: service@ixyslongbeach.com

The information contained herein is confidential and is protected by Copyright. The information may not be used or disclosed except with the written permission of and in the manner permitted by the proprietors IXYS UK Westcode Ltd.

© IXYS UK Westcode Ltd.

In the interest of product improvement, IXYS UK Westcode Ltd reserves the right to change specifications at any time without prior notice.

Devices with a suffix code (2-letter, 3-letter or letter/digit/letter combination) added to their generic code are not necessarily subject to the conditions and limits contained in this report.



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.