


# Low $V_{CE(sat)}$ IGBT High Speed IGBT


**IXGH 12N100**  
**IXGH 12N100A**

| $V_{CES}$ | $I_{C25}$ | $V_{CE(sat)}$ |
|-----------|-----------|---------------|
| 1000 V    | 24 A      | 3.5 V         |
| 1000 V    | 24 A      | 4.0 V         |



| Symbol                                                                          | Test Conditions                                                                                                               | Maximum Ratings                  |                  |
|---------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|----------------------------------|------------------|
| $V_{CES}$                                                                       | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$                                                                               | 1000                             | V                |
| $V_{CGR}$                                                                       | $T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$ ; $R_{GE} = 1\text{ M}\Omega$                                                 | 1000                             | V                |
| $V_{GES}$                                                                       | Continuous                                                                                                                    | $\pm 20$                         | V                |
| $V_{GEM}$                                                                       | Transient                                                                                                                     | $\pm 30$                         | V                |
| $I_{C25}$                                                                       | $T_C = 25^\circ\text{C}$                                                                                                      | 24                               | A                |
| $I_{C90}$                                                                       | $T_C = 90^\circ\text{C}$                                                                                                      | 12                               | A                |
| $I_{CM}$                                                                        | $T_C = 25^\circ\text{C}$ , 1 ms                                                                                               | 48                               | A                |
| <b>SSOA (RBSOA)</b>                                                             | $V_{GE} = 15\text{ V}$ , $T_{VJ} = 125^\circ\text{C}$ , $R_G = 150\ \Omega$<br>Clamped inductive load, $L = 300\ \mu\text{H}$ | $I_{CM} = 24$<br>@ $0.8 V_{CES}$ | A                |
| $P_C$                                                                           | $T_C = 25^\circ\text{C}$                                                                                                      | 100                              | W                |
| $T_J$                                                                           |                                                                                                                               | -55 ... +150                     | $^\circ\text{C}$ |
| $T_{JM}$                                                                        |                                                                                                                               | 150                              | $^\circ\text{C}$ |
| $T_{stg}$                                                                       |                                                                                                                               | -55 ... +150                     | $^\circ\text{C}$ |
| $M_d$                                                                           | Mounting torque (M3)                                                                                                          | 1.13/10                          | Nm/lb.in.        |
| <b>Weight</b>                                                                   |                                                                                                                               | 6                                | g                |
| Maximum lead temperature for soldering<br>1.6 mm (0.062 in.) from case for 10 s |                                                                                                                               | 300                              | $^\circ\text{C}$ |

TO-247AD



G = Gate      C = Collector  
E = Emitter    TAB = Collector

| Symbol        | Test Conditions                                                                                        | Characteristic Values<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified) |        |                           |
|---------------|--------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|--------|---------------------------|
|               |                                                                                                        | Min.                                                                              | Typ.   | Max.                      |
| $BV_{CES}$    | $I_C = 3\text{ mA}$ , $V_{GE} = 0\text{ V}$<br>$BV_{CES}$ temperature coefficient                      | 1000                                                                              | 0.072  | V<br>%/K                  |
| $V_{GE(th)}$  | $I_C = 500\ \mu\text{A}$ , $V_{GE} = V_{GE}$<br>$V_{GE(th)}$ temperature coefficient                   | 2.5                                                                               | -0.192 | V<br>%/K                  |
| $I_{CES}$     | $V_{CE} = 0.8 V_{CES}$ , $T_J = 25^\circ\text{C}$<br>$V_{GE} = 0\text{ V}$ , $T_J = 125^\circ\text{C}$ |                                                                                   |        | 250 $\mu\text{A}$<br>1 mA |
| $I_{GES}$     | $V_{CE} = 0\text{ V}$ , $V_{GE} = \pm 20\text{ V}$                                                     |                                                                                   |        | $\pm 100\text{ nA}$       |
| $V_{CE(sat)}$ | $I_C = I_{C90}$ , $V_{GE} = 15\text{ V}$                                                               | 12N100<br>12N100A                                                                 |        | 3.5 V<br>4.0 V            |

## Features

- International standard package JEDEC TO-247 AD
- 2nd generation HDMOS™ process
- Low  $V_{CE(sat)}$ 
  - for low on-state conduction losses
- High current handling capability
- MOS Gate turn-on
  - drive simplicity
- Voltage rating guaranteed at high temperature ( $125^\circ\text{C}$ )

## Applications


- AC motor speed control
- DC servo and robot drives
- DC choppers
- Uninterruptible power supplies (UPS)
- Switch-mode and resonant-mode power supplies

## Advantages

- Easy to mount with 1 screw (isolated mounting screw hole)
- High power density

| Symbol                    | Test Conditions                                                                                                                                                                                                                                                                                                                                              | Characteristic Values<br>(T <sub>J</sub> = 25°C, unless otherwise specified) |      |          |
|---------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------|------|----------|
|                           |                                                                                                                                                                                                                                                                                                                                                              | Min.                                                                         | Typ. | Max.     |
| <b>g<sub>fs</sub></b>     | I <sub>C</sub> = I <sub>C90</sub> , V <sub>CE</sub> = 10 V,<br>Pulse test, t ≤ 300 μs, duty cycle ≤ 2 %                                                                                                                                                                                                                                                      | 6                                                                            | 10   | S        |
| <b>C<sub>ies</sub></b>    | V <sub>CE</sub> = 25 V, V <sub>GE</sub> = 0 V, f = 1 MHz                                                                                                                                                                                                                                                                                                     |                                                                              | 750  | pF       |
| <b>C<sub>oes</sub></b>    |                                                                                                                                                                                                                                                                                                                                                              |                                                                              | 80   | pF       |
| <b>C<sub>res</sub></b>    |                                                                                                                                                                                                                                                                                                                                                              |                                                                              | 30   | pF       |
| <b>Q<sub>g</sub></b>      | I <sub>C</sub> = I <sub>C90</sub> , V <sub>GE</sub> = 15 V, V <sub>CE</sub> = 0.5 V <sub>CES</sub>                                                                                                                                                                                                                                                           |                                                                              | 65   | nC       |
| <b>Q<sub>ge</sub></b>     |                                                                                                                                                                                                                                                                                                                                                              |                                                                              | 8    | nC       |
| <b>Q<sub>gc</sub></b>     |                                                                                                                                                                                                                                                                                                                                                              |                                                                              | 24   | nC       |
| <b>t<sub>d(on)</sub></b>  | <b>Inductive load, T<sub>J</sub> = 25°C</b><br>I <sub>C</sub> = I <sub>C90</sub> , V <sub>GE</sub> = 15 V, L = 300 μH,<br>V <sub>CE</sub> = 0.8 V <sub>CES</sub> , R <sub>G</sub> = R <sub>off</sub> = 120 Ω<br>Remarks: Switching times may increase for V <sub>CE</sub> (Clamp) > 0.8 V <sub>CES</sub> , higher T <sub>J</sub> or increased R <sub>G</sub> |                                                                              | 100  | ns       |
| <b>t<sub>ri</sub></b>     |                                                                                                                                                                                                                                                                                                                                                              |                                                                              | 200  | ns       |
| <b>t<sub>d(off)</sub></b> |                                                                                                                                                                                                                                                                                                                                                              |                                                                              | 850  | 1000 ns  |
| <b>t<sub>fi</sub></b>     |                                                                                                                                                                                                                                                                                                                                                              |                                                                              | 800  | 1000 ns  |
| <b>E<sub>off</sub></b>    |                                                                                                                                                                                                                                                                                                                                                              |                                                                              | 500  | 700 ns   |
|                           |                                                                                                                                                                                                                                                                                                                                                              | 12N100                                                                       | 2.5  | mJ       |
|                           |                                                                                                                                                                                                                                                                                                                                                              | 12N100A                                                                      | 1.5  | 3.0 mJ   |
| <b>t<sub>d(on)</sub></b>  | <b>Inductive load, T<sub>J</sub> = 125°C</b><br>I <sub>C</sub> = I <sub>C90</sub> , V <sub>GE</sub> = 15 V, L = 300 μH<br>V <sub>CE</sub> = 0.8 V <sub>CES</sub> , R <sub>G</sub> = R <sub>off</sub> = 120 Ω<br>Remarks: Switching times may increase for V <sub>CE</sub> (Clamp) > 0.8 V <sub>CES</sub> , higher T <sub>J</sub> or increased R <sub>G</sub> |                                                                              | 100  | ns       |
| <b>t<sub>ri</sub></b>     |                                                                                                                                                                                                                                                                                                                                                              |                                                                              | 200  | ns       |
| <b>E<sub>on</sub></b>     |                                                                                                                                                                                                                                                                                                                                                              |                                                                              | 1.1  | mJ       |
| <b>t<sub>d(off)</sub></b> |                                                                                                                                                                                                                                                                                                                                                              |                                                                              | 900  | ns       |
| <b>t<sub>fi</sub></b>     |                                                                                                                                                                                                                                                                                                                                                              |                                                                              | 1250 | ns       |
|                           |                                                                                                                                                                                                                                                                                                                                                              | 12N100                                                                       | 950  | ns       |
|                           |                                                                                                                                                                                                                                                                                                                                                              | 12N100A                                                                      | 3.5  | mJ       |
|                           |                                                                                                                                                                                                                                                                                                                                                              | 12N100A                                                                      | 2.2  | mJ       |
| <b>R<sub>thJC</sub></b>   |                                                                                                                                                                                                                                                                                                                                                              |                                                                              |      | 1.25 K/W |
| <b>R<sub>thCK</sub></b>   |                                                                                                                                                                                                                                                                                                                                                              |                                                                              | 0.25 | K/W      |

TO-247 AD (IXGH) Outline



| Dim. | Millimeter |       | Inches |       |
|------|------------|-------|--------|-------|
|      | Min.       | Max.  | Min.   | Max.  |
| A    | 19.81      | 20.32 | 0.780  | 0.800 |
| B    | 20.80      | 21.46 | 0.819  | 0.845 |
| C    | 15.75      | 16.26 | 0.610  | 0.640 |
| D    | 3.55       | 3.65  | 0.140  | 0.144 |
| E    | 4.32       | 5.49  | 0.170  | 0.216 |
| F    | 5.4        | 6.2   | 0.212  | 0.244 |
| G    | 1.65       | 2.13  | 0.065  | 0.084 |
| H    | -          | 4.5   | -      | 0.177 |
| J    | 1.0        | 1.4   | 0.040  | 0.055 |
| K    | 10.8       | 11.0  | 0.426  | 0.433 |
| L    | 4.7        | 5.3   | 0.185  | 0.209 |
| M    | 0.4        | 0.8   | 0.016  | 0.031 |
| N    | 1.5        | 2.49  | 0.087  | 0.102 |

IXGH12N100/A characteristic curves may be found in the IXGH12N100U/AU1 data sheet.



---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).