
IXYS

Polar™ HiPerFET™ Power MOSFET


IXFK250N10P
IXFX250N10P

V_{DSS} = 100V
I_{D25} = 250A
$R_{DS(on)}$ ≤ 6.5mΩ
t_{rr} ≤ 200ns


N-Channel Enhancement Mode
Avalanche Rated
Fast Intrinsic Diode



TO-264 (IXFK)



PLUS247 (IXFX)



G = Gate D = Drain
S = Source Tab = Drain

Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 175°C	100	V
V_{DGR}	T_J = 25°C to 175°C, R_{GS} = 1MΩ	100	V
V_{GSS}	Continuous	± 20	V
V_{GSM}	Transient	± 30	V
I_{D25}	T_C = 25°C (Chip Capability)	250	A
I_{LRMS}	Lead Current Limit, RMS	160	A
I_{DM}	T_C = 25°C, Pulse Width Limited by T_{JM}	700	A
I_A	T_C = 25°C	125	A
E_{AS}	T_C = 25°C	3	J
P_D	T_C = 25°C	1250	W
dv/dt	$I_S \le I_{DM}$, $V_{DD} \le V_{DSS}$, $T_J \le 175°C$	20	V/ns
T_J		-55 ... +175	°C
T_{JM}		175	°C
T_{stg}		-55 ... +175	°C
T_L	1.6mm (0.062 in.) from Case for 10s	300	°C
T_{SOLD}	Plastic Body for 10s	260	°C
M_d	Mounting Torque (TO-264)	1.13/10	Nm/lb.in.
F_C	Mounting Force (PLUS247)	20..120 /4.5..27	N/lb.
Weight	TO-264	10	g
	PLUS247	6	g

Symbol	Test Conditions (T_J = 25°C Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0V, I_D = 3mA	100			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 1mA	3.0		5.0	V
I_{GSS}	V_{GS} = ± 20V, V_{DS} = 0V			± 200	nA
I_{DSS}	$V_{DS} = V_{DSS}$, V_{GS}= 0V			50	μA
	T_J = 150°C			1	mA
$R_{DS(on)}$	V_{GS} = 10V, I_D = 50A, Note 1			6.5	mΩ

Features

- Dynamic dv/dt Rating
- Avalanche Rated
- Fast Intrinsic Diode
- Low Q_G and $R_{DS(on)}$
- Low Package Inductance

Advantages

- Easy to Mount
- Space Savings

Applications

- DC-DC Converters
- Battery Chargers
- Switch-Mode and Resonant-Mode Power Supplies
- Uninterrupted Power Supplies
- AC Motor Drives
- High Speed Power Switching Applications

© 2010 IXYS CORPORATION, All Rights Reserved


Symbol	Test Conditions (T_J = 25°C Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	V_{DS} = 10V, I_D = 60A, Note 1	50	83		S
C_{iss}	V_{GS} = 0V, V_{DS} = 25V, f = 1MHz		16		nF
C_{oss}			4470		pF
C_{rss}			290		pF
$t_{d(on)}$	**Resistive Switching Times**		25		ns
t_r	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25}		30		ns
$t_{d(off)}$	R_G = 1Ω (External)		50		ns
t_f			18		ns
$Q_{g(on)}$	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25}		205		nC
Q_{gs}			77		nC
Q_{gd}			80		nC
R_{thJC}				0.12	°C/W
R_{thCS}			0.15		°C/W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
I_S	V_{GS} = 0V			250	A
I_{SM}	Repetitive, Pulse Width Limited by T_{JM}			750	A
V_{SD}	I_F = 100A, V_{GS} = 0V, Note 1			1.3	V
t_{rr}	I_F = 125A, -di/dt = 100A/μs			200	ns
Q_{RM}	V_R = 50V, V_{GS} = 0V		0.7		μC
I_{RM}			10.4		A

Note 1. Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.


TO-264 Outline



Terminals: 1 - Gate
2 - Drain
3 - Source
4 - Drain

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.82	5.13	.190	.202
A1	2.54	2.89	.100	.114
A2	2.00	2.10	.079	.083
b	1.12	1.42	.044	.056
b1	2.39	2.69	.094	.106
b2	2.90	3.09	.114	.122
c	0.53	0.83	.021	.033
D	25.91	26.16	1.020	1.030
E	19.81	19.96	.780	.786
e	5.46 BSC		.215 BSC	
J	0.00	0.25	.000	.010
K	0.00	0.25	.000	.010
L	20.32	20.83	.800	.820
L1	2.29	2.59	.090	.102
P	3.17	3.66	.125	.144
Q	6.07	6.27	.239	.247
Q1	8.38	8.69	.330	.342
R	3.81	4.32	.150	.170
R1	1.78	2.29	.070	.090
S	6.04	6.30	.238	.248
T	1.57	1.83	.062	.072

PLUS247™ Outline



Terminals: 1 - Gate
2 - Drain
3 - Source

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.83	5.21	.190	.205
A_1	2.29	2.54	.090	.100
A_2	1.91	2.16	.075	.085
b	1.14	1.40	.045	.055
b_1	1.91	2.13	.075	.084
b_2	2.92	3.12	.115	.123
C	0.61	0.80	.024	.031
D	20.80	21.34	.819	.840
E	15.75	16.13	.620	.635
e	5.45 BSC		.215 BSC	
L	19.81	20.32	.780	.800
L1	3.81	4.32	.150	.170
Q	5.59	6.20	.220	0.244
R	4.32	4.83	.170	.190

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,850,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2 7,005,734 B2 7,063,975 B2 7,071,537 7,157,338B2

Fig. 1. Output Characteristics @ T_J = 25ºC




Fig. 2. Extended Output Characteristics @ T_J = 25ºC




Fig. 3. Output Characteristics @ T_J = 150ºC




Fig. 4. $R_{DS(on)}$ Normalized to I_D = 125A Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to I_D = 125A Value vs. Drain Current





Fig. 6. Maximum Drain Current vs. Case Temperature



© 2010 IXYS CORPORATION, All Rights Reserved

Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Forward Voltage Drop of Intrinsic Diode




Fig. 10. Gate Charge




Fig. 11. Capacitance






Fig. 12. Forward-Bias Safe Operating Area



IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

Fig. 13. Maximum Transient Thermal Impedance



© 2010 IXYS CORPORATION, All Rights Reserved



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.