
IXYS

PolarHV™ HiPerFET Power MOSFETs

IXFH 140N10P
IXFT 140N10P


V_{DSS} = 100 V
I_{D25} = 140 A
$R_{DS(on)}$ ≤ 11 mΩ
t_{rr} ≤ 150 ns

N-Channel Enhancement Mode
Fast Intrinsic Diode
Avalanche Rated




Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 175°C	100	V
V_{DGR}	T_J = 25°C to 175°C; R_{GS} = 1 MΩ	100	V
V_{GS}	Continuous	±20	V
V_{GSM}	Transient	±30	V
I_{D25}	T_C = 25°C	140	A
$I_{D(RMS)}$	External lead current limit	75	A
I_{DM}	T_C = 25°C, pulse width limited by T_{JM}	300	A
I_{AR}	T_C = 25°C	60	A
E_{AR}	T_C = 25°C	80	mJ
E_{AS}	T_C = 25°C	2.5	J
dv/dt	$I_S \le I_{DM}$, di/dt ≤100 A/μs, $V_{DD} \le V_{DSS}$, $T_J \le 150°C$, R_G = 4 Ω	10	V/ns
P_D	T_C = 25°C	600	W
T_J		-55 ... +175	°C
T_{JM}		175	°C
T_{stg}		-55 ... +150	°C
T_L	1.6 mm (0.062 in.) from case for 10 s	300	°C
T_{SOLD}	Plastic body for 10s	260	°C
M_d	Mounting torque (TO-247)	1.13/10	Nm/lb.in.
Weight	TO-247	6.0	g
	TO-268	5.0	g

TO-247 (IXFH)



TO-268 (IXFT)



G = Gate D = Drain
S = Source TAB = Drain

Features

- International standard packages
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
  - easy to drive and to protect

Advantages

- Easy to mount
- Space savings
- High power density

Symbol	Test Conditions (T_J = 25°C, unless otherwise specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0 V, I_D = 250 μA	100			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 4.0 mA	3.0		5.0	V
I_{GSS}	V_{GS} = ±20 V_{DC}, V_{DS} = 0			±100	nA
I_{DSS}	$V_{DS} = V_{DSS}$			25	μA
	V_{GS} = 0 V, T_J = 175°C			500	μA
$R_{DS(on)}$	V_{GS} = 10 V, $I_D = 0.5\ I_{D25}$			11	mΩ
	V_{GS} = 15 V, I_D = 300 A, Note 1		9		mΩ

© 2006 IXYS All rights reserved


Symbol	Test Conditions	Characteristic Values (T_J = 25° C, unless otherwise specified) Min.	Typ.	Max.	
g_{fs}	V_{DS}= 10 V; I_D = 0.5 I_{D25}, Note 1	45	65		S
C_{iss}	V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz		4700		pF
C_{oss}			1850		pF
C_{rss}			600		pF
$t_{d(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 V_{DSS}, I_D = 60 A R_G = 4 Ω (External)		35		ns
t_r			50		ns
$t_{d(off)}$			85		ns
t_f			26		ns
$Q_{g(on)}$	V_{GS}= 10 V, V_{DS} = 0.5 V_{DSS}, I_D = 0.5 I_{D25}		155		nC
Q_{gs}			33		nC
Q_{gd}			85		nC
R_{thJC}					0.25° C/W
R_{thCS}	(TO-247)		0.21		° C/W

Source-Drain Diode

Symbol	Test Conditions	Characteristic Values (T_J = 25° C, unless otherwise specified) Min.	Typ.	Max.	
I_S	V_{GS} = 0 V			140	A
I_{SM}	Repetitive			300	A
V_{SD}	I_F = I_S, V_{GS} = 0 V, Pulse test, t ≤300 μs, duty cycle d≤ 2 %			1.5	V
t_{rr}	I_F = 25 A, -di/dt = 100 A/μs		150	200	ns
Q_{RM}	V_R = 50 V, V_{GS} = 0 V		0.8		μC
I_{RM}			6		A

Note 1: Pulse test, t ≤300 μs, duty cycle d ≤ 2 %


TO-247 AD Outline



Terminals: 1 - Gate 2 - Drain
3 - Source Tab - Drain

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.7	5.3	.185	.209
A_1	2.2	2.54	.087	.102
A_2	2.2	2.6	.059	.098
b	1.0	1.4	.040	.055
b_1	1.65	2.13	.065	.084
b_2	2.87	3.12	.113	.123
C	.4	.8	.016	.031
D	20.80	21.46	.819	.845
E	15.75	16.26	.610	.640
e	5.20	5.72	0.205	0.225
L	19.81	20.32	.780	.800
L1		4.50		.177
ØP	3.55	3.65	.140	.144
Q	5.89	6.40	0.232	0.252
R	4.32	5.49	.170	.216
S	6.15 BSC		242 BSC	

TO-268 Outline



SYM	INCHES MIN	MAX	MILLIMETERS MIN	MAX
A	.193	.201	4.90	5.10
A1	.106	.114	2.70	2.90
A2	.001	.010	0.02	0.25
b	.045	.057	1.15	1.45
b2	.075	.083	1.90	2.10
C	.016	.026	0.40	0.65
C2	.057	.063	1.45	1.60
D	.543	.551	13.80	14.00
D1	.488	.500	12.40	12.70
E	.624	.632	15.85	16.05
E1	.524	.535	13.30	13.60
e	.215 BSC		5.45 BSC	
H	.736	.752	18.70	19.10
L	.094	.106	2.40	2.70
L1	.047	.055	1.20	1.40
L2	.039	.045	1.00	1.15
L3	.010 BSC		0.25 BSC	
L4	.150	.161	3.80	4.10

IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETs and IGBTs are covered by one or moreof the following U.S. patents: 4,835,592 4,850,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405B2 6,710,463 6,727,585 6,759,692 6,771,478 B2

Fig. 1. Output Characteristics @ 25ºC




Fig. 2. Extended Output Characteristics @ 25ºC




Fig. 3. Output Characteristics @ 150ºC




Fig. 4. $R_{DS(on)}$ Normalized to 0.5 I_{D25} Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to 0.5 I_{D25} Value vs. Drain Current





Fig. 6. Drain Current vs. Case Temperature



© 2006 IXYS All rights reserved

Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Source Current vs. Source-To-Drain Voltage




Fig. 10. Gate Charge




Fig. 11. Capacitance






Fig. 12. Forward-Bias Safe Operating Area



IXYS reserves the right to change limits, test conditions, and dimensions.

Fig. 13. Maximum Transient Thermal Resistance



© 2006 IXYS All rights reserved



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.